

ACCESSORIES

EXTERNAL SHUNT 2215, 2216, 2217

Model	Rating
2215	01 1 A
	02 1.5 A
	03 2 A
	04 3 A
	05 5 A
	06 7.5 A
	07 10 A
	08 15 A
	09 20 A
	10 30 A
	11 50 A
	12 75 A
	13 100 A
	14 150 A
	15 200 A
	16 300 A
2216	01 500 A
	02 750 A
	03 1000 A
2217	01 1500 A
	02 2000 A
	03 3000 A
	04 5000 A

Class: Class 0.2
Rated voltage drop: 50 mV

EXTERNAL MULTIPLIER 2224, 2225, 2226, 2228

Model	Rating	Current Consumption
2224	01 50 V	1 mA
	02 75 V	
	03 100 V	
	04 150 V	
	05 300 V	
	06 500 V	
	07 750 V	
2225	00 1 kV	1 mA
2226	01 1.5 kV	
	02 2 kV	
	03 3 kV	1 mA
2228	01 5 kV	
	02 7.5 kV	

Accuracy: $\pm 0.5\%$ of rated value
Measuring method: 2224...2 terminal type
2225, 2226, 2228...3 terminal type

EXTERNAL VT

Model	2267	2268
Rated Burden	15 VA	50 VA
Primary	Secondary	—
220 V	110 V	2267 01
440 V		2267 02
1100 V		2267 03
2200 V		2267 04
3300 V		2267 05
6600 V		2268 01
		2268 02

Class: Equivalent to JIS C1731 Class 1.0
Structure: Epoxy mold type

EXTERNAL CT 2248, 2255

Model	Primary	Secondary
2248	00 10 mA to 50 A	10 mA (2 VA max.)
	01 30 A	5 A (2 VA max.)
	02 50 A	
	03 75 A	
	04 100 A	
	05 150 A	
2255	01 10 A	5 A (15 VA max.)
	02 15 A	
	03 20 A	
	04 30 A	
	05 50 A	
	06 75 A	
	07 100 A	
	08 150 A	
	09 200 A	
	10 250 A	
	11 300 A	
	12 500 A	

Class: Equivalent to JIS C1731 Class 1.0 But
2248 is an accuracy of $\pm 1.5\%$.
Structure: Epoxy mold type (Excludes 2248)
Dielectric Strength: less than 250V for 2248,
less than 3450V for 2255


OTHER

Shunt lead: B9068MX (1.5 m, 0.05 Ω)
Window mounting bracket: B9010AX (100 pcs)


DIMENSIONS FOR ACCESSORIES

(unit: mm)


2215 (1 to 7.5 A)




2215 (10 to 300 A)



2216 (500 to 1000 A)




2217 (1,500 to 3,000 A)




* Dashed line is for 1,500 A

Rating	W	Q	H	C	D
1,500 A	92	—	74	35	12
2,000 A	110	50	81	35	12
3,000 A	120	70	117	53	20


2217 (5,000 A)




2224 (50 to 750 V)




2225 (1 kV)




2226 (1.5, 2, 3 kV)




2228 (5, 7.5 kV)




2248 (10 mA to 50 A/10 mA, 30 A/5 A, 50 A/5 A)



2248 (75 to 150 A/5 A)




2255 (10 to 500 A/5 A)



Rating	A	B	P	b	d	t
10 to 150 A	170	45	12	25	7	4
200, 250 A	180	50	15	25	9	4
300, 500 A	200	60	20	40	11	5

2267 (220 to 3300 V/110 V)



2268 (3.3 to 6.6 kV/110 V)

