

New Adapters for the 700929 Isolation Probe







Use with the DL750, DL750P, DL 850 series, SL1000, and SL1400 ScopeCoders

- Take advantage of the 700929 isolation probe's 10:1 attenuation when making high voltage measurements with Yokogawa's ScopeCorder family of instruments.
- Safety probe adapters offer protection when making high voltage measurements. Refer to the ScopeCorder module specifications for voltage limits when using the 700929 probe.

Adapters offer flexibility!

- Clip on to bigger test points using the large jaw adapters
- Connect directly to banana plug receptacles
- Banana plug adapters provide additional connection choices

DL750, 750P, DL850 series, SL1000 & SL1400 Isolated Input Modules

 <p>High-speed 10MS/s 12-bit resolution 701250</p> <p>High-resolution 1 MS/s 16-bit resolution 701251</p> <p>High-voltage, RMS, 100kS/s 16-bit resolution 701261</p> <p>Frequency module 701281</p>	 <p>Isolation Probe 700929</p> <p>Standard: small hook probe tip with a small alligator clip reference lead</p>	<p>Probe Tip Adapters (H Side)</p>  <p>Push-on Large Jaw Safety Clip M1223WN-A</p>  <p>Push-on Safety Male Banana Plug * M1223WP-A</p> <p>Reference Lead & Adapter (L Side)</p>  <p>Banana Plug Reference Lead * M1223WQ-A</p>  <p>Large Jaw Safety Reference Clip M1223WR-A <small>(requires M1223WQ-A also)</small></p>
---	--	--

* Compatible with the banana plug adapters shown below

Banana Plug Adapters



Large Alligator Clips
(Dolphin Type)
701954



Safety Mini Clips
(Hook Type)
701959



Large Alligator Clips
758929



Fork Terminal
Adapters
758921



Small Alligator Clips
758922

