

300 Series and CL Series of Clamp-on Testers



Leakage Clamp-on Tester with a sharp low pass filter function Leakage Clamp-on Tester capable of measuring from 1 mA AC



Yokogawa Test & Measurement Corporation

Selection Guide

■ For Leakage Current

Model		30031A	30032A	CL320	CL340	CL345	CL360
Diameter of measurable conduct	tor	ø40mm	ø40mm	ø24mm	ø40mm	ø40mm	ø68mm
Method of detection		Mean value	Mean value	Mean value	Mean value	True RMS	Mean value
Frequency characteristics		50/60Hz	50/60Hz	40Hz to 400Hz	20Hz to 1kHz	20Hz to 1kHz	40Hz to 1kHz
AC current	Range	3/30mA, 30/60A	3/30mA, 30/60A	20/200mA,200A	40/400mA,400A	40/400mA,400A	200mA/2/20/200/1000A
	Resolution	0.001mA	0.001mA	0.01mA	0.01mA	0.01mA	0.1mA
Other measurement	AC voltage	_	_	_	_	_	_
functions	DC voltage	_	_	_	_	_	_
	Continuity check	_	_	_	_	_	_
	Frequency	_	_	_	_	_	_
	Data hold	0	0	0	0	0	0
	Peak hold	_	_	_	0	0	0
	Recorder output	_	_	_	_	_	0
	Mean value display	_	0*	_	_	_	_
	Filter Switch	_	0	0	0	0	0
	Waveform monitor output	_		_	_	_	0
Page		2	2	7	8	8	9

^{*}Page1: Description of Harmonic Filter Function

■ For AC Current

Model		CL120	CL150	CL155
Diameter of measurable conductor	r	ø 24mm	Ø 54mm	ø 54mm
Method of detection		Mean value	Mean value	True RMS
Frequency characteristics		40Hz to 1kHz	40Hz to 1kHz	40Hz to 1kHz
AC current	Range	20/200A	400/2000A	400/2000A
	Resolution	0.01A	0.1A	0.1A
DC current	Range	_	_	_
	Resolution	_	_	_
Other measurement	AC voltage	_	0	0
functions	DC voltage	_	0	0
	Continuity check	_	0	0
	Frequency	_	_	_
	Data hold	0	0	0
	Peak hold	_	0	0
	Recorder output	_	0	0
	Waveform monitor output	_	_	_
Page		3	4	5

■ For AC/DC Currents

Model		CL220	CL235	CL250	CL255
Diameter of measurable conductor		ø 24mm	Ø 33mm	Ø 55mm	Ø 55mm
Method of detection		Mean value	True RMS	Mean value	True RMS
Frequency characteristics		20Hz to 1kHz	40Hz to 1kHz	40Hz to 1kHz	30Hz to 1kHz
AC current	Range	40/300A	400/600A	400/2000A	400/2000A
	Resolution	0.01A	0.1A	0.1A	0.1A
DC current	Range	40/300A	400/1000A	400/2000A	400/2000A
	Resolution	0.01A	0.1A	0.1A	0.1A
Other measurement	AC voltage	_	0	0	0
functions	DC voltage	_	0	0	0
	Continuity check	_	0	0	0
	Frequency	_	0	-	0
	Data hold	0	0	0	0
	Peak hold	_	0	_	0
	Recorder output	_	-	0	0
	Waveform monitor output	_	<u> </u>	_	_
Page		5	6	6	7

■ For DC Current

Model		CL420
Diameter of measurable conductor		ø6mm
DC current	Range	20/100mA
	Resolution	0.01mA
Other measurement	Data hold	0
functions	Recoder output	0
Page		9

Description of Harmonic Filter Function

● Harmonic Filter Function (Only Available in the 30032A)

1. What is a Harmonic?

Harmonic refers to sinusoidal quantity having a frequency that is an integral multiple of the fundamental frequency (for example, the commercial frequency). When a harmonic is superimposed on the fundamental frequency, the waveform is distorted.


2. Why is it Necessary to Accurately Measure the Leakage Current of the Fundamental Frequency (Commercial Frequency)?

One problem when measuring the leakage current to check the isolation of electrical circuits in power distribution equipment is that the electrical isolation cannot be correctly understood due to the influence of a harmonic current. That is, the leakage current flowing from the electrical circuit to ground is very small so that, in order to check the isolation of electrical circuits by means of the leakage current, it is necessary to remove the harmonic component of the leak current and measure only the current of the fundamental frequency (commercial frequency).

3. The 30032A Employs a Harmonic Filter

Conventional leakage clamp-on testers could not sufficiently remove harmonic current components so measured leakage current values were often larger than the specified value due to the influence of a harmonic current. In

this case, retesting with an insulation tester was required, resulting in increased effort and cost for the test. Under these circumstances, Yokogawa Meters & Instruments Corporation has developed the leakage clamp-on tester 30032A, which employs a high-performance harmonic filter that can accurately measure just the fundamental frequency component of the leakage current.




*Waveforms obtained when measuring a distribution board of a Yokogawa Meters & Instruments Corporation office

Characteristics of Harmonic Filter

1. Filter Characteristic of the 30032A

When the frequency is more than 60 Hz, the sharp filter removes the harmonic component, leaving the fundamental frequency. For example, the level of 100 Hz is attenated to approx. 1%. <Reference Figure 1: Harmonic Filter Characteristic 1>

Figure 1: Harmonic Filter Characteristic 1




2. Filter Comparison (between the On and Off States)

This is the filter characteristic in the On and Off states. <Reference Figure 2: Harmonic Filter Characteristic 2>

<Reference> When the filter is in the On or Off state

Amplitude ratios in the range between the fundamental frequency and the third frequency <Fundamental frequency: 60 Hz>

Filter state Harmonic	On	Off
Fundamental	0 dB	0 dB
Second	-56 dB	-1.3 dB
Third	-80 dB or more	-6.7 dB




Measurement Example


Measurement method of leakage current



A: Measurement of the grounding wire for the transformer class B grounding work B: Measurement of the electrical circuit C: Measurement of the grounding wire of electrical equipment



In the case of load current



Leakage Clamp-on Testers



AC Leakage

Ø40

AC/3mA~60A

Filter



AC Leakage

Ø40

AC/3mA~60A

30032A

- Can measure leakage AC currents of 1mA
- Filter function can cut off harmonics-currents components from 2nd order
- Filter function select on or off

AC current measurement

Filter function OFF

Accuracy: \pm (% of reading + digits)

Range	Resolution	Accuracy	Maximum Allowable Current
3mA	0.001mA	0.010 <i td="" ≤32.70ma:<=""><td>3.270mA</td></i>	3.270mA
30mA	0.01mA	1.0%+5	32.70mA
30A	0.01A	0.05 <i td="" ≤50.0a:1.0%+5<=""><td>32.70A</td></i>	32.70A
60A	0.1A	50.0 <i td="" ≤60.6a:5.0%+5<=""><td>60.6A</td></i>	60.6A

Filter function ON

Range	Resolution	Accuracy	Maximum Allowable Current
3mA	0.001mA	0.010 <i td="" ≤32.70ma:<=""><td>3.270mA</td></i>	3.270mA
30mA	0.01mA	1.5%+5	32.70mA
30A	0.01A	0.05 <i td="" ≤50.0a:1.5%+5<=""><td>32.70A</td></i>	32.70A
60A	0.1A	50.0 <i td="" ≤60.6a:5.5%+5<=""><td>60.6A</td></i>	60.6A

Note: Input current of 2nd-order and higher harmonics : 150 mA rms maximum in the 3 mA/30 mA range : 62 A rms maximum in the 30 A/60 A range

Filter specifications (3 mA and 30 mA ranges and 30 A and 60 A ranges)
Amplitude ratio at 100 Hz: -38 dB (1.26%) or less (typical: -41 dB)
Amplitude ratio at 120 Hz: -53 dB (0.22%) or less (typical: -56 dB)

Zero correction

3 mA range: Displays 0.000 mA (zero) when 0.010 mA < I 30 A range: Displays 0.00 A (zero) when 0.05 A < I

■General Specifications

Parameter	Specification
Method	Mean-value detection and rms-value calibration
Display	LCD (Digital reading 3200 counts)
	Bar graph (32 segments)
Range switching	Range selection Auto or Manual
Data Hold	On all Range
Operating temperature and humidity	0 to 50°C, 80% RH or less (no condensation)
Temperature coefficient	Following values must be added in the temperature
	range of either 0 to 18°C or 28 to 50°C
	$0 \le I \le 50.0A$: $\pm (0.08\% \text{ of reading/}^{\circ}C + 0.5 \text{ digits/}^{\circ}C)$
	$50.0 < I \le 60.6A$: $\pm (0.3\% \text{ of reading/}^{\circ}\text{C} + 0.5 \text{ digits/}^{\circ}\text{ C})$
Effect of external magnetic fields	0.0005%typical value (in terms of the magnitude of
	current in adjacent wires)
Safety standard	Conforms EN 61010-1, EN 61010-2-032
	CAT. III 300V
Circuit voltage	300 Vrms or less
Withstanding voltage	3.7 kV AC for one minute
Power supply	CR2032 lithium battery × 1
Power consumption	6mW maximum
Battery life	Approx. 90 hours
Automatic power-off	Power approx. 10 minutes after the last switch operation.
Dimensions	Approx 70 (W) \times 178 (H) \times 25 (D) (mm)
Weight	Approx 200 g (including the battery)
Accessories	User's manual, Battery, Soft carrying case (RB057)

30031A

- Can measure leakage AC currents of 1mA
- Standard AC Leakage model

AC current measurement

Accuracy: \pm (% of reading + digits)

Range	Resolution	Accuracy	Maximum Allowable Current
3mA	0.001mA	0.010 <i td="" ≤32.70ma:<=""><td>3.270mA</td></i>	3.270mA
30mA	0.01mA	1.0%+5	32.70mA
30A	0.01A	0.05 <i td="" ≤50.0a:1.0%+5<=""><td>32.70A</td></i>	32.70A
60A	0.1A	50.0 <i td="" ≤60.6a:5.0%+5<=""><td>60.6A</td></i>	60.6A

Zero correction

3 mA range: Displays 0.000 mA (zero) when 0.010 mA < I 30 A range: Displays 0.00 A (zero) when 0.05 A < I

Parameter	Specification
Method	Mean-value detection and rms-value calibration
Display	LCD (Digital reading 3200 counts)
	Bar graph (32 segments)
Range swiching	Range selection Auto or Manual
Data Hold	On all Range
Operating temperature and humidity	0 to 50°C, 80% RH or less (no condensation)
Temperature coefficient	Following values must be added in the temperature
	range of either 0 to 18°C or 28 to 50°C
	$0 \le I \le 50.0A$: $\pm (0.08\% \text{ of reading/}^{\circ}\text{C} + 0.5 \text{ digits/}^{\circ}\text{C})$
	$50.0 < I \le 60.6A$: $\pm (0.3\% \text{ of reading/}^{\circ}\text{C} + 0.5 \text{ digits/}^{\circ}\text{ C})$
Effect of external magnetic fields:	0.0005%typical value (in terms of the magnitude of
	current in adjacent wires)
Safety standards	Conforms EN 61010-1, EN 61010-2-032
	CAT. III 300V
Circuit voltage	300 Vrms or less
Withstanding voltage	3.7 kV AC for one minute
Power supply	CR2032 lithium battery \times 1
Power consumption	6mW maximum
Battery life	Approx. 90 hours
Automatic power-off	Power approx. 10 minutes after the last switch operation.
Dimensions	Approx 70 (W) \times 178 (H) \times 25 (D) (mm)
Weight	Approx 200 g (including the battery)
Accessories	User's manual, Battery, Soft carrying case (RB057)





Ø**24**

AC/20~200A





Ø 54

AC/400~2000A

AC V/DC V/Ω

CL120

- Light weight & compact design
- Mean value display
- Data hold function
- Approved for comformity to safety standards EN61010-1, EN61010-2-032 (CAT. III 300 V)

■Specifications

At 23 °C ± 5 °C, 75 %RH or less Accuracy: \pm (% of reading + digits)

Parameter	Range	Accuracy
AC current	20A	2.0+7 (50~1kHz)
	3004	2.0+5 (50/60Hz)
	200A	3.0+10 (40~1kHz)

■General Specifications

Parameter	Specification
Method of detection	Mean value
Display	LCD(Digital display:1999 counts)
Response time	Approx. 2 seconds
Range switching	Manual-range
Data hold	On all range
Operating temperature and humidity	0-40℃, 85% RH or less (no condensation)
Temperature coefficient	_
Effect of external magnetic field	0.8A or less at 400A/m
Effect of conductor position	±2% or less
Safety standard	Conforms EN 61010-1, EN61010-2-032
Circuit voltage	300Vrms or less
Withstanding voltage	4240V AC for 5 sec
Power supply	LR-44×2(3V) or SR-44×2
Battery life	Approx. 100 hours (continuous)
Consumed current	Approx. 1mA
Auto power-off	Approx. 10 minutes
Diameter of measurable conductor	24mm diameter max.
Dimensions	Approx. 59(W)×148(H)×26(D)mm
Weight	Approx. 100g
Accessories	User's manual, batteries, carrying case(93033)

CL150

- Mean value display
- DC output function
- Data hold function
- Sleep function
- Approved for comformity to safety standards EN61010-1, EN61010-2-031, EN61010-2-032 (CAT. III 600 V, CAT. II 1000 V)

■Specifications

At $23\%\pm5\%$, 75%RH or less Accuracy: $\pm(\%$ of reading + digits)

		Accuracy. ± (% of reading + digits)
Parameter	Range	Accuracy
AC current	400A	1.0+3 (50/60Hz)
	400A	2.0+3 (40~1kHz)
	2000A(0~1500A)	1.0+3 (50/60Hz)
	2000A(0 -1300A)	3.0+3 (40~1kHz)
	2000A(1500~2000A)	3.0(50/60Hz)
AC voltage	40/400/750V	1.0+2 (50/60Hz)
	40/400/730 V	1.5+3 (40~1kHz)
DC voltage	40/400/1000V	1.0+2
Resistance	400/4k/40k/400kΩ	1.5+2, Beeps at below 50±35Ω(continuity check)
DC output	400 4 (0 400 17)	±1.5% rdg ±0.5mV (50/60Hz)
	400A(0~400mV)	±2.5% rdg ±0.5mV (40~1kHz)
	2000 4 (0 150 140 1500 4)	±1.5% rdg ±0.5mV (50/60Hz)
	2000A(0~150mV/0~1500A)	±3.5% rdg ±0.5mV (40~1kHz)
	2000A(150~200mV/1500~2000A)	±3.5% rdg (50/60Hz)

Parameter	Specification
Method of detection	Mean value
Display	LCD(Digital display:4000 counts)
Response time	Approx. 2 seconds
Range switching	Manual-range(on AC current range)/
	Auto-range(on AC voltage range, resistance range)
Data hold	On all range
Peak hold	On AC current range
Operating temperature and humidity	0-40°C, 85% RH or less (no condensation)
Temperature coefficient	_
Effect of external magnetic field	1A or less at 400A/m
Effect of conductor position	$\pm (2.0\% \text{ rdg} + 3\text{dgt}) \text{ or less}$
Safety standard	Conforms EN61010-1, EN61010-2-031, EN61010-2-032
Circuit voltage	1000Vrms or less
Withstanding voltage	6300V AC for 5 sec
Power supply	R6P(SUM-3) \times 2 or LR6 \times 2
Battery life	Approx. 150 hours (continuous)
Consumed current	Approx. 5mA
Sleep function	Automatically powered down in about 10 minutes
	after the last switch operation
Diameter of measurable conductor	54.5mm at maximum
Dimensions	Approx. $105(W) \times 247(H) \times 49(D)$ mm
Weight	Approx. 470g
Accessories	User's manual, batteries, carrying case (93034),
110000001100	





AC/400~2000A

RMS

 \bigcirc AC V/DC V/ Ω



AC A/DC A

Ø24

AC/40~300A

DC/40~300A

CL155

- True RMS display
- DC output function
- Data hold function
- Sleep function
- Approved for comformity to safety standards EN61010-1, EN61010-2-031, EN61010-2-032 (CAT. IV 300 V, CAT. III 600 V, CAT. II 1000 V)

■Specifications

At 23 $\mathbb{C}\pm5\mathbb{C}$, 75%RH or less Accuracy: \pm (% of reading + digits)

Parameter	Range	Accuracy
AC current	400A	1.0+3 (50/60Hz)
	400A	2.0+3 (40~1kHz)
	2000A(0~1500A)	1.0+3 (50/60Hz)
	2000A(0 -1300A)	3.0+3 (40~1kHz)
	2000A(1500~2000A)	3.0(50/60Hz)
AC voltage	40/400/750V	1.0+2 (50/60Hz)
	40/400/730 V	1.5+3 (40∼1kHz)
DC voltage	40/400/1000V	1.0+2
Resistance	400/4k/40k/400kΩ	1.5+2, Beeps at below 50±35Ω(continuity check)
DC output	1001/0 100 11	±1.5% rdg ±0.5mV (50/60Hz)
	400A(0~400mV)	±2.5% rdg ±0.5mV (40~1kHz)
	2000 1 (0 150 170 1500 1)	±1.5% rdg ±0.5mV (50/60Hz)
	2000A(0~150mV/0~1500A)	±3.5% rdg ±0.5mV (40~1kHz)
	2000A(150~200mV/1500~2000A)	±3.5% rdg (50/60Hz)

■General Specifications

·	
Parameter	Specification
Method of detection	True RMS
Display	LCD(Digital display:4000 counts)
Response time	Approx. 2 seconds
Range switching	Manual-range(on AC current range)/
	Auto-range(on AC voltage range, resistance range)
Data hold	On all range
Peak hold	On AC current range
Operating temperature and humidity	0-40°C, 85% RH or less (no condensation)
Temperature coefficient	_
Effect of external magnetic field	1A or less at 400A/m
Effect of conductor position	$\pm (2.0\% \text{ rdg} + 3\text{dgt}) \text{ or less}$
Safety standard	Conforms EN61010-1, EN61010-2-031, EN61010-2-032
Circuit voltage	1000Vrms or less
Withstanding voltage	6300V AC for 5 sec
Power supply	R6P(SUM-3) \times 2 or LR6 \times 2
Battery life	Approx. 80 hours (continuous)
Consumed current	Approx. 7mA
Sleep function	Automatically powered down in about 10 minutes
	after the last switch operation
Diameter of measurable conductor	54mm at maximum
Dimensions	Approx. 105(W)×247(H)×49(D)mm
Weight	Approx. 470g
Accessories	User's manual, batteries, carrying case (93034),
	Output plug (98012), Test Lead (98072)

- Light weight & compact design
- Mean value display
- Sleep function
- Approved for comformity to safety standards EN61010-1, EN61010-2-032 (CAT. III 300 V)

■Specifications

At 23°C \pm 5°C, 75%RH or less

		Accuracy: ±(% of reading + digits)
Parameter	Range	Accuracy
DC current	40A	1.0+4
	300A(±20~±200A)	1.5+4
	300A(±200~±300A)	3.0
AC current	40A	1.0+4 (50/60Hz)
		2.5+4 (20~1kHz)
	300A(20~200A)	1.5+4 (50/60Hz)
		2.5+4 (20~1kHz)
	300A(200~300A)	3.5 (50/60Hz)
		4.0 (20~1kHz)

Parameter	Specification
Method of detection	Mean value
Display	LCD(Digital display:4000 counts)
Response time	Approx. 2 seconds
Range switching	Auto-range
Data hold	On all range
Operating temperature and humidity	0-40℃, 85% RH or less (no condensation)
Temperature coefficient	_
Effect of external magnetic field	1A or less at 400A/m
Effect of conductor position	$\pm (2.0\% \text{ rdg} + 5 \text{dgt}) \text{ or less}$
Safety standard	Conforms EN61010-1, EN61010-2-032
Circuit voltage	300Vrms or less
Withstanding voltage	4240V AC for 5 sec
Power supply	LR-44×2(3V) or SR-44×2
Battery life	Approx. 11 hours (continuous)
Consumed current	Approx. 9mA
Sleep function	Automatically powered down in about
	5 minutes after the last switch operation
Diameter of measurable conductor	24mm at maximum
Dimensions	Approx. 59(W)×147(H)×25(D)mm
Weight	Approx. 100g
Accessories	User's manual, batteries, carrying case(93033)





Ø33

AC/400~600A

RMS

DC/400~1000A

DC V/AC V/ Ω/Hz



AC A/DC A





DC/400~2000A

O AC V/DC V/Ω

- True RMS display
- Sleep function
- Data hold function
- Approved for comformity to safety standards EN61010-1, EN61010-2-031, EN61010-2-032 (CAT. III 600 V)

■Specifications

At 23°C ± 5 °C, 75%RH or less Accuracy: \pm (% of reading + digits)

Parameter	Range	Accuracy
AC current	400/600A	1.5+5 (50/60Hz)
	400/000A	3.5+5 (40~1kHz)
DC current	400/1000A	1.0+5
AC voltage	40/400/600V	1.5+5 (50/60Hz)
		3.5+5 (40~1kHz)
DC voltage	40/400/600V	1.0+5
Crest factor		≦3
Resistance	400/4000Ω	1.0+5, Beeps at below 20Ω(continuity check)
Frequency	10~3000Hz	1.5+5

■General Specifications

Parameter	Specification
Method of detection	True RMS
Display	LCD(Digital display:3999 counts)
Response time	Approx. 2 second
Range switching	Auto-range
Data hold	On all range
Peak hold	On AC/DC current range, AC/DC voltage range
Average measurement	_
Operating temperature and humidity	0-40°C, 90% RH or less (no condensation)
Temperture coefficient	_
Effect of external magnetic field	_
Effect of conductor position	±2% or less
Safety standard	Conforms EN61010-1, EN61010-2-031, EN61010-2-032
Circuit voltage	600Vrms or less
Withstanding voltage	6300V AC for 5 sec
Power supply	6F22(006P)9V×1 or 6LR61×1
Battery life	Approx. 15 hours (continuous)
Consumed current	Approx. 15mA
Sleep function	Automatically powered down in about
	30 minutes after the last switch operation
Diameter of measurable conductor	33mm at maximum
Dimensions	Approx. 91(W)×210(H)×40(D)mm
Weight	Approx. 450g
Accessories	User's manual, batteries, carrying case(93032),
	Test Lead (98071)

CL250

- Mean value display
- Sleep function
- Data hold function
- Approved for comformity to safety standards EN61010-1, EN61010-2-031, EN61010-2-032 (CAT. IV 600 V, CAT. III 1000 V)

■Specifications

At 23°C±5°C, 75%RH or less Accuracy:±(% of reading + digits)

		Accuracy: ±(% of reading + digits)
Parameter	Range	Accuracy
DC current	400/2000A	1.5+2
AC current		1.5+2 (50/60Hz)
	400A/2000A(0~1000A)	3.0+4 (40~500Hz)
		5.0+4 (500~1kHz)
	2000A(1001~2000A)	3.0+2 (50/60Hz)
DC voltage	400/1000V	1.0+2
AC voltage	400/750V	1.5+2 (50/60Hz)
	400/730 V	1.5+4 (40~1kHz)
Resistance	$400/4000\Omega$	1.5+2, Beeps at below 50±35Ω(continuity check)
DC output	DC400A(0~400mV)	±1.5% rdg ±3mV
	DC2000A(0~200mV)	±1.5% rdg ±3mV
	AC400A(0~400mV)	±1.5% rdg ±3mV (50/60Hz)
	, ,	±3.0% rdg ±3mV (40~500Hz)
	AC2000A(0~100mV/0~1000A)	±5.0% rdg ±3mV (500~1kHz)
	AC2000A(100.1~200mV/1001~2000A)	±3.0% rdg ±3mV (50/60Hz)

Parameter	Specification
Method of detection	Mean value
	Tream raide
Display	LCD(Digital display:3999 counts)
Response time	Approx. 2 seconds
Range switching	Manual-range(on current, voltage range)
	/Auto-range(on resistance range)
Peak hold	On all range
Max hold	On current/voltage range
Operating temperature and humidity	0-40°C, 85% RH or less (no condensation)
Temperature coefficient	_
Effect of external magnetic field	4A or less at 400A/m
Effect of conductor position	$\pm (1.5\% \text{ rdg} + 3\text{dgt}) \text{ or less}$
Safety standard	Conforms EN61010-1, EN61010-2-031, EN61010-2-032
Circuit voltage	1000Vrms or less
Withstanding voltage	8200V AC for 5 sec
Power supply	R6P(SUM-3) \times 2 or LR6 \times 2
Battery life	Approx. 100 hours (continuous)
Consumed current	Approx. 9mA
Sleep function	Automatically powered down in about
	10 minutes after the last switch operation
Diameter of measurable conductor	55mm at maximum
Dimensions	Approx. 105(W)×250(H)×49(D)mm
Weight	Approx. 530g
Accessories	User's manual, Test Lead(98072),
	Output plug(98012), batteries, carrying case(93034)



AC A/DC A

Ø55

AC/400~2000A

DC/400~2000A

RMS

AC V/DC V/ Ω/Hz

Leakage Clamp-on Testers



AC Leakage

Ø24

AC/20mA~200A

- True RMS display
- Sleep function
- Data hold function
- Approved for comformity to safety standards EN61010-1, EN61010-2-031, EN61010-2-032 (CAT. III 600 V, CAT. II 1000 V)

■Specifications

At 23℃±5℃, 75%RH or less Accuracy: ±(% of reading + digits)

Parameter	Range	Accuracy
DC current	400/2000A	1.5+2
AC current	400A/2000A(150~1700A)	1.5+3 (50/60Hz)
	400A/2000A(130 1700A)	3.0+4 (30~1kHz)
	2000A(1701~2000A)	3.5+3 (50/60Hz)
DC voltage	40/400/1000V	1.0+2
AC voltage	40/400/750V	1.5+3 (50/60Hz)
	40/400/730 V	2.0+4 (30~1kHz)
Crest factor		≤3
Resistance	$400/4000\Omega$	1.5+2, Beeps at below 20Ω(continuity check)
Frequency	10∼3999Hz	1.5+5
DC output	DC400A(0~400mV)	±1.5% rdg ±3mV
	DC2000A(15~200mV)	±1.5% rdg ±3mV
	AC400A(0~400mV)	±1.5% rdg ±3mV (50/60Hz)
	/AC2000A(15~170mV/150~1700A)	$\pm 3.0\% \text{ rdg } \pm 3\text{mV } (40 \sim 1\text{kHz})$
	AC2000A(170.1~200mV/1701~2000A)	±3.5% rdg ±3mV (50/60Hz)

■General Specifications

Parameter	Specification
Method of detection	True RMS
Display	LCD(Digital display:3999 counts)
Response time	Approx. 1 second(on DC current/voltage range),
	Approx. 2 seconds(AC current/voltage range, resistance range)
Range switching	Auto-range
Data hold	On all range (without peak hold)
Peak hold	On current/voltage range
Average Measeurement	On current/voltage range
Operating temperature and humidity	0-40℃, 85% RH or less (no condensation)
Temperature coefficient	_
Effect of external magnetic field	4A or less at 400A/m
Effect of conductorposition	$\pm (1.5\% \text{ rdg} + 3\text{dgt}) \text{ or less}$
Safety standard	Conforms EN61010-1, EN61010-2-031, EN61010-2-032
Circuit voltage	1000Vrms or less
Withstanding voltage	6300V AC for 5 sec
Power supply	6F22(006P)9V×1 or 6LR61×1
Battery life	Approx. 15 hours (continuous)
Consumed current	Approx. 15mA
Sleep function	Automatically powered down in about
	10 minutes after the last switch operation
Diameter of measurable conductor	55mm at maximum
Dimensions	Approx. $105(W) \times 250(H) \times 49(D)mm$
Weight	Approx. 540g
Accessories	User's manual, Test Lead(98072),
	Output plug(98012), batteries, carrying case(93034)

- Mean value display
- ullet Auto power-off
- Manual range switching
- Approved for comformity to safety standards EN61010-1, EN61010-2-032 (CAT. III 300 V)

Range

20mA/200mA

200A(0~100A)

200A(100.1~200A)

■Specifications

Parameter

AC current

At 23°C±5°C, 75%RH or less Accuracy: ±(% of reading + digits)

5.0+5 (50/60Hz)

Accuracy WIDE(40~400Hz) 50/60Hz 2.0+4 (50/60Hz) 3.0+5 (50/60Hz)

5.0+6 (40~400Hz)

5.0+4 (50/60Hz)

Parameter	Specification	
Method of detection	Mean value	
Display	LCD(Digital display:1999 counts)	
Response time	Approx. 2 seconds	
Range switching	Manual-range	
Data hold	On all range	
Operating temperature and humidity	0-40°C, 85% RH or less (no condensation)	
Temperature coefficient	_	
Effect of external magnetic field	10mA or less in proximity to a 14.4mm-dia	
	conductor carrying 100A	
Effect of conductor position	Within 5dgt for 0 to 50A, or 2% for 50 to 200A	
	(10mm-dia conductor at inside the jaw)	
Effect of residual current	10mA or less in proximity to a 10mm-dia	
	conductor carrying 50A	
Safety standard	Conforms EN61010-1, EN61010-2-032	
Circuit voltage	300Vrms or less	
Withstanding voltage	4240V AC for 5 sec	
Power supply	LR-44 \times 2(3V) or SR-44 \times 2	
Battery life	Approx. 15 hours (continuous)	
Consumed current	Approx. 5mA	
Auto power-off	Approx. 10 minutes	
Diameter of measurable conductor	24mm at maximum	
Dimensions	Approx. 60(W)×149(H)×26(D)mm	
Weight	Approx. 120g	
Accessories	User's manual, batteries, carrying case(93033)	

Leakage Clamp-on Testers





Ø40

AC/40mA~400A



AC Leakage

 $\emptyset 40$

AC/40mA~400A

RMS

CL340

- Mean value display
- Auto power-off
- Manual range switching
- Approved for comformity to safety standards EN61010-1, EN61010-2-032 (CAT. III 300 V)

■Specifications

At 23°C±5°C, 75%RH or less Accuracy: ±(% of reading + digits)

Parameter	Range	Accuracy	
		WIDE(20Hz∼)	50/60Hz
AC current	40mA/400mA	2.5+10 (20~1kHz)	1.0+5 (50/60Hz)
	400A(0~350A)	2.5+10 (40~1kHz)	1.0+5 (50/60Hz)
	400A(350~400A)	5.0 (40~1kHz)	2.0 (50/60Hz)

■General Specifications

acriciai opecinications	9 19 1	
Parameter	Specification	
Method of detection	Mean value	
Display	LCD(Digital display:3999 counts)*	
Response time	Approx. 2 seconds	
Range switching	Manual-range	
Data hold	On all range	
Peak hold	On all range	
Operating temperature and humidity	0-40°C, 85% RH or less (no condensation)	
Temperature coefficient	_	
Effect of external magnetic field	10mA or less in proximity to a 15mm-dia	
	conductor carrying 100A	
Effect of conductor position	40/400mA range:Within 5dgt	
	at every part inside the jaw400A range,	
	0 to 250A:Within $\pm 0.5\%$ rdg ± 5 dgt	
	at every part inside the jaw section	
Effect of residual current	12mA or less in proximity to a	
	10mm-dia conductor carrying 100A	
Safety standard	Conforms EN61010-1, EN61010-2-032	
Circuit voltage	300Vrms or less	
Withstanding voltage	4240V AC for 5 sec	
Power supply	$R0-3(UM-4) \times 2 \text{ or } LR03 \times 2$	
Battery life	Approx. 40 hours (continuous)	
Consumed current	Approx. 13mA	
Auto power-off	Approx. 10 minutes	
Diameter of measurable conductor	40mm at maximum	
Dimensions	Approx. $81(W) \times 185(H) \times 40(D)$ mm	
Weight	Approx. 270g	
Accessories	User's manual, batteries, carrying case(93030)	

*6000 counts (40/400mA range)

- True RMS display
- Auto power-off
- Manual range switching
- Approved for comformity to safety standards EN61010-1, EN61010-2-032 (CAT. III 300 V)

■Specifications

At 23°C±5°C, 75%RH or less Accuracy: ±(% of reading + digits)

Parameter Range Accuracy WIDE(20Hz∼) 50/60Hz AC current 2.5+10 (20~1kHz) 1.0+5 (50/60Hz) 40mA/400mA 400A(0~300A) 2.5+10 (40~1kHz) 1.0+5 (50/60Hz) 400A(300~400A) 5.0 (40~1kHz) 2.0 (50/60Hz)


■General Specifications

Parameter	Specification	
Method of detection	True RMS	
Display	LCD(Digital display:4200 counts)*	
Response time	Approx. 2 seconds	
Range switching	Manual-range	
Data hold	On all range	
Peak hold	On all range	
Operating temperature and humidity	0-40°C, 85% RH or less (no condensation)	
Temperature coefficient	_	
Effect of external magnetic field	10mA or less in proximity to a 15mm-dia	
	conductor carrying 100A	
Effect of conductor position	40/400mA range:Within 5dgt	
	at every part inside the jaw400A range,	
	0 to 250A:Within ±0.5%rdg ±5dgt	
	at every part inside the jaw section	
Effect of residual current	12mA or less in proximity to a	
	10mm-dia conductor carrying 100A	
Safety standard	Conforms EN61010-1, EN61010-2-032	
Circuit voltage	300Vrms or less	
Withstanding voltage	4240V AC for 5 sec	
Power supply	R0-3(UM-4) × 2 or LR03 × 2	
Battery life	Approx. 24 hours (continuous)	
Consumed current	Approx. 21mA	
Auto power-off	Approx. 10 minutes	
Diameter of measurable conductor	40mm at maximum	
Dimensions	Approx. 81(W)×185(H)×40(D)mm	
Weight	Approx. 270g	
Accessories	User's manual, batteries, carrying case(93030)	
	*6000 counts (40/400mA range)	

*6000 counts (40/400mA range)

Leakage Clamp-on Testers





Ø68

AC/200mA~1000A

Clamp-on Process Meter



DC20/100mA

Ø6





• Approved for conformity to safety standards EN 61010-1, EN 61010-2-032 (CAT. III 300 V, CAT. II 600 V)

■Specifications

At 23℃±5℃, 75%RH or less

		Accuracy:±(% of reading + digits)
Parameter	Range Accuracy		
		WIDE(40~1kHz)	50/60Hz
AC current	200 4 /2 4 /20 4	1.0+2 (50/60Hz)	1.5.0
	200mA/2A/20A	3.0+2 (40~1kHz)	1.5+2
	2004	1.5+2 (50/60Hz)	202
	200A	3.5+2 (40~1kHz)	2.0+2
	1000 4 (0 500 4)	1.5+2 (50/60Hz)	20.2
	1000A(0~500A)	3.5+2 (40~1kHz)	2.0+2
	1000 4 (501 - 1000 4)*	5.0 (50/60Hz)	5.5
	1000A(501~1000A)*	10.0 (40~1kHz)	5.5
AC output	200mA/2A/20A(0~200mV)	2.0	2.0
	200A(0~200mV)	2.5	2.5
	1000A/(0~50mV/0~500A)	3.0	3.0
	1000A/(50~100mV/501~1000A)	5.0	5.0
DC output	200mA/2A/20A(0~200mV)	3.0	3.5
	200A(0~200mV)	3.5	4.0
	1000A/(0~50mV/0~500A)	5.0	5.5
	1000A/(50~100mV/501~1000A)	7.0	7.5

*Measurement of 501 to 1000A can be performed within 10 minutes.

■General Specifications

Parameter	Specification	
Method of detection	Mean value	
Display	LCD(Digital display:1999 counts)	
Response time	Approx. 1 second	
Range switching	Manual-range	
Data hold	On all range	
Peak hold	On all range	
Operating temperature and humidity	-10-50℃, 80% RH or less (no condensation)	
Temperature coefficient	_	
Effect of external magnetic field	15mA or less in proximity to a	
	10mm-dia conductor carrying 100A	
Effect of conductor position	2% or less	
Effect of residual current	10mA or less in proximity to a	
	10mm-dia conductor carrying 100A	
Safety standard	Conforms EN61010-1, EN61010-2-032	
Circuit voltage	600Vrms or less	
Withstanding voltage	4240V AC for 5 sec	
Power supply	6F22(006P)9V×1 or 6LR61×1	
Battery life	Approx. 60 hours (continuous)	
Consumed current	Approx. 5mA	
Diameter of measurable conductor	68mm at maximum	
Dimensions	Approx. 129(W)×248(H)×55(D)mm	
Weight	Approx. 570g	
Accessories	User's manual, batteries, carrying case(93031)	

CL420


- Measure 4 to 20mA DC signals without breaking the loop
- Dual Display
- LED Torch Light, Backlight Display

■Specifications

Parameter	Specification		
Diameter of measurable conductor	6mm diameter max.		
DC Current	Range and resolution [Range]	Accuracy*1	
	20 mA: 0.00 to ±21.49mA	±(0.2%rdg+5dgt)*2	
	100 mA: ±21.0 to ±126.0mA	\pm (1.0%rdg+5dgt)	
DC Voltage OUTPUT [10mV/mA]	20 mA: 0.0 to ±214.9mV	(DCA Accuracy)+(±0.5mV)	
	100 mA: ±210 to ±1260mV	(DCA Accuracy)+(±3mV)	
Display	4-digit LCD Numeric display		
Response time	Approx. 1.5 seconds (2.5 seconds when across the range)		
Range switching	Auto range		
Operating temperature and humidity	-10℃ to +50℃ 80% RH or less (no condensation)		
Safety Standards	EN61010-1, EN61010-2-030, EN61010-2-032		
Withstanding voltage	2.21kV AC for 5 seconds (between the core and the case)		
Power supply	Four AA-size alkaline batteries (1.5V LR6)		
Battery life	Approx. 60hrs (continuous) backlight off and LED light off		
Other functions	Data hold, Zero adjust function, Auto power off,		
	LED Torch light, Back light display, Illuminant panel		
External dimensions and weight	61 (W) × 111 (H) × 40 (D) mm		
	Approx. 290g (including batteries)		
Standard accessories	User's Manual, Batteries, Soft case (93045)		
*1 A+ 22°C +5°C 45% to 75% DH			

^{*1} At 23°C ±5°C, 45% to 75%RH

■Examples of Analog Output Application



■Product Model Code

Name	Model
Clamp-on Process Meter	CL420

■Standard Accessories (supplied)

Name	Model
Soft case (for CL420)	93045

■Optional Accessories (sold separately)

Name	Model
Output cable	98076
Output cable (for screw terminal)	98077

Measurement accuracy: ±(% of reading + digits)
Terms of accuracy: Open and close the clamp sensor after power on and perform zero adjustment.
*2 The 20mA range accuracy assurance is the average of 5 times measuring.

Supplementary Products

■ Supplementary Products

- ouppromornary : roundto			
Item	Model	Specification	Applicable model
Test Lead	98071	Angle Plug type	CL235
Test Lead	98072	Straight Plug type	CL150,CL155,CL250,CL255
Output Pllug	98012	3pcs/set	CL150,CL155,CL250,CL255
Carrying Case	93030	Hard type	CL340,CL345
Carrying Case	93031	Soft type	CL360
Carrying Case	93032	Soft type	CL235
Carrying Case	93033	Soft type	CL120,CL220,CL320
Carrying Case	93034	Soft type	CL150,CL155,CL250,CL255
Carrying Case	93035	Hard type	99025
Soft Case (for CL420)	93045	Soft type	CL420
Carrying Case	RB057	Soft type	30031A/30032A

















Accessories

■ Optional Accessories


Item	Model	Specification	Applicable model
Clamp Adapter	99025	Ratio/Range = 10:1/3000A	CL120,CL150, CL155,CL220,CL235,CL250, CL255,CL320,CL340,CL345
Output Cable with Banana Plug	91020	Cable length: approx.2m	CL360
Output Cable	98076	Cable length: approx.1m	CL150,CL155,CL250, CL255,CL420
Output Cable for screw terminal	98077	Cable length: approx.1m	CL150,CL155,CL250, CL255,CL420


■ 99025 Specifications

Item	Specifications
Measuring Range	0~AC3000A
Ratio/Range	10:1 (input to output)
Accuracy	$\pm 2\%$ of input ± 0.5 A
Allowable Measurement Time	0~1000A(continuous),1000~1500A(10 minutes max.), 3000A(30 seconds max.)
Conductor Size	φ100mm max. (100×150mm)
Frequency Response	50Hz/60Hz
Safety Standard	EN61010-1 CAT.III300V Pollution Degree 2
Withstand Voltage	AC3700V for 1 minute
Dimensions	150(W)×317(H)×33(D)mm 40(W)×45(H)×10(D)mm Output coil
Weight	Approx. 750g
Accessories	93035(Carrying Case)











https://tmi.yokogawa.com/

YMI-KS-MI-SE08

[Ed: 13/b]

YOKOGAWA TEST & MEASUREMENT CORPORATION

Facsimile: +81-42-690-8826

YOKOGAWA CORPORATION OF AMERICA YOKOGAWA EUROPE B.V. YOKOGAWA TEST & MEASUREMENT (SHANGHAI) CO., LTD. Phone: +86-21-6239-6363 E-mail: tmi@cs.cn.yokogawa.com YOKOGAWA ELECTRIC KOREA CO., LTD. YOKOGAWA ENGINEERING ASIA PTE. LTD. YOKOGAWA INDIA LTD.

YOKOGAWA ELECTRIC CIS LTD. YOKOGAWA AMERICA DO SUL LTDA. YOKOGAWA MIDDLE EAST & AFRICA B.S.C(c) Phone: +1-800-888-6400 Phone: +31-88-4641429 Phone: +82-2-2628-3810

Phone: +65-6241-9933

Phone: +973-17-358100

E-mail: tmi@us.yokogawa.com E-mail: tmi@nl.yokogawa.com E-mail: TMI@kr.yokogawa.com E-mail: TMI@sg.yokogawa.com Phone: +91-80-4158-6396 E-mail: tmi@in.yokogawa.com Phone: +7-495-737-7868 E-mail: info@ru.yokogawa.com

Facsimile: +86-21-6880-4987 Facsimile: +82-2-2628-3899 Facsimile: +65-6241-9919 Facsimile: +91-80-2852-1442 Facsimile: +7-495-737-7869 Phone: +55-11-3513-1300 E-mail: eproc@br.yokogawa.com

E-mail: help.ymatmi@bh.yokogawa.com Facsimile: +973-17-336100

The contents are as of March 2021. Subject to change without notice. Copyright © 1996, Yokogawa Test & Measurement Corporation