


Drawings

3226 UNIVERSAL LEAKAGE CURRENT TESTER

UNIT: mm



No.	Name
①	Power on-off/ battery check switch
②	Panel
③	Range Selector
④	Carrying handle
⑤	Case
⑥	Input terminals
⑦	Measurement lead
⑧	Clip

Unless otherwise specified here, all dimensions should be applied tolerance of $\pm 3\%$ ($\pm 0.3\text{mm}$ in case less than 10 mm.).

WEIGHT APPROX.

1 kg