
Test&Measurement







Flexible & reliable

WT1800E Series
High performance
Power Analyzers

Precision Making

Bulletin WT1800E-01EN

To curb global warming, greater efforts are being made to generate and use power more efficiently. The use of renewable energy sources like solar and wind power is growing and there is accelerated development of environmentally-friendly cars and energy-efficient machines and devices.

Developing these technologies requires accurate measurements to validate even the smallest changes in energy consumption. In the WT1800E high performance power analyzer, engineers have the ideal tool to accurately measure power, its quality and efficiency.

Whether analyzing multiphase inputs during motor and drive design or meeting the stringent efficiency standards of photovoltaic inverters, the WT1800E provides the versatility to help engineers bring their product concepts successfully to market

The WT1800E delivers:

Accuracy – The WT1800E is the only instrument in its class that guarantees a power accuracy of 0.05% of reading plus 0.05% of range and is capable of harmonics analysis up to the 500th order of a 50/60 Hz fundamental frequency.

Reliability – Measurements need to be repeatable as well as accurate. The stability of the WT1800E ensures that precision measurements can be made today and over the long term.

Flexibility – With up to 6 input channels, a wide range of display and analysis features, and PC connectivity, the WT1800E is the measurement solution for a broad range of power efficiency and harmonic analysis requirements.



Features and benefits

6 inputs on a high resolution display

Make simultaneous measurements on up to 6 inputs at 2 MS/s (16 bits). The high resolution 8.4 inch XGA display of the WT1800E allows split screen viewing of up to 6 waveforms and can display up to 12 pages of diverse measurement parameters making it ideal for efficiency tests of inverter driven motors, renewable energy technologies and traction applications like pumps, fans and hybrid/electric vehicles. The unit can also display measurements in vector format or trending in time.



Guaranteed accuracy across a wide range

Measure accurately at a wide range of voltage, current and frequency conditions. The basic power accuracy of the WT1800E is guaranteed between 1% to 110% of the selected voltage and current range. This equates to voltages from 15 mV to 1100 Vrms and currents from 0.1 mA to 5.5 Arms (for a 5 A input element) and 10 mA to 55 Arms (for a 50 A input element). The unit is also accurate during large phase shifts and high frequencies thanks to the minimized influence of the low power factor error (±0.07% of apparent power).

Range configuration

Track signal changes faster by eliminating unnecessary range changes. The WT1800E's range configuration function allows users to select input ranges based on their specific use cases so that optimal range settings are achieved quicker. This reduces the time during repetitive production tests, such as setting to OFF, 100 V, OFF and so on, which is performed frequently on the production line.

Harmonic analyses

Analyze harmonics up to the 500th order for a 50/60 Hz fundamental even at a data update interval of 50 milliseconds. The WT1800E features two options for analyzing harmonics in addition to power parameters,

- Harmonic measurement mode (/G5 option) for fundamental wave, harmonic components and total harmonic distortion (THD)
- Dual Harmonic option (/G6 option) for side by side measurement of harmonics on two different sources for example input and output of inverters, variable speed motors, lighting ballasts, UPS, etc.



Power integration and auto ranging


Measure energy bought and sold in grid connections or charged and discharged in batteries. The WT1800E's Power integration function integrates instantaneous values for both positive and negative readings. It also measures total energy (Wh) and current (Ah) when load conditions vary widely like in devices transitioning from standby to operation mode. Should an input signal start to fall out of the expected range, this function can automatically adjust the range while continuing to integrate the measured values.

High speed data capture

The High Speed data capturing function can measure Sigma-Urms, Sigma-Irms and Sigma-P from DC signal and three phase devices every 5 ms when External Synchronization is OFF or, 1 ms to 100 ms when External Synchronization is ON depending on the frequency of the clock signal.

Flexible & automatic data updates

Manually or automatically set measurement intervals. The WT1800E offers 9 data update interval between 50 ms to 20 s but can also follow fluctuating input frequencies by changing the data update rate automatically. This is useful when measuring devices like motors whose input signal frequency varies with RPM.





DC power supply for AC/DC current sensors (/PD2 option)

The WT1800E can be equipped with a DC power supply for the CT series of AC/DC current sensors. By using dedicated connection cables and shunt resistors, the WT1800E can measure large currents. Improved S/N ratio and noise immunity is achieved by connecting the sensors in this way.

 $^*\!/\!\text{EX1}$ to /EX6 options must be installed in the WT1800E to be able to use the Shunt Resistor Box.

Motor evaluation function

Measure more than just electrical parameters. The motor evaluation function enables measurement of rotation speed and direction, torque, mechanical power, synchronous speed, slip, electrical angle, motor efficiency and total system efficiency from the analog or pulse outputs of rotation and torque sensors.





WTViewerE application software

Easily view, control and download measurements from your PC. The WTViewerE is a powerful software connects up to four WT1800Es to a PC via a communications interface making numeric, waveform, trend and harmonic data from the unit easily accessible via PC.

User defined events and computations

The WT1800E's event trigger function allows users to set limits for capture of readings that fall into or out of a specific range of power, current or other parameters. Data that meets the trigger conditions are stored, printed, saved to a USB memory device etc. Users can also define and use up to 20 expressions for custom calculations.

The WT1800E in detail



- 1 External media slot
- 2 Element setting
- 3 U/I range display
- 4 Display settings
- 5 Measurement item selection
- 6 Integration settings
- 7 Data saving
- 8 Built-in printer (/B5 Option)
- 9 Current Sensor Power (/PD2 Option)



- 1 Voltage input terminals
- 2 Current input terminals
- 3 GP-IB port
- 4 BNC connector for two-system synchronized measurement
- 5 Ethernet port (1000BASE-T/100BASE-TX)
- 6 USB port (PC)

- 7 External current sensor input terminals (/EX Option)
- 8 Torque and speed input terminals (/MTR Option)
- 9 D/A output (/DA Option)
- 10 RGB port (/V1 Option)

Two types of input element

Basic Power Accuracy: ±(0.05% of reading + 0.05% of range)*1

Measurement Bandwidth: DC, 0.1 Hz to 1 MHz

Low Power Factor Error: Power factor influence when $\cos \emptyset = 0$

0.07% of S

S is reading value of apparent power ø is phase angle between voltage and

current

Temperature range: 23 ±5°C

Current Range

• Direct Input: 1/2/5/10/20/50 A*2

10/20/50/100/200/500 mA, 1/2/5 A*2

(50 A and 5 A input element can be installed together)

• External Input: 50/100/200/500 mV, 1/2/5/10 V*2

Voltage Range: 1.5/3/6/10/15/30/60/100/150/300/600/1000 V*2

Effective input range: 1% to 110% Data Update Interval: 50 ms to 20 s or Auto

*1 Please refer to "specifications" in detail

*2 Voltage range and current range are for crest factor 3

5 A input element


50 A input element






Both 5 A and 50 A input elements can be installed in a single unit. This enables engineers to use a single WT1800E for multiple applications such as standby power measurement and the evaluation of various operating modes of the device under test.


Example of basic characteristics showing the WT1800E's high precision and excellent stability




Example of frequency versus power accuracy characteristic at unity power factor



Example of effect of common mode voltage on readings



Total power error with rated range input for an arbitrary power factor (50/60 Hz)



Example of frequency versus power accuracy at zero power factor

Applications

The WT1800E is a versatile instrument, unlocking precision power measurement capabilities for researchers, designers and engineers working on a wide variety of applications in energy efficiency and conservation and renewable energy. Whether it is for the manufacture of energy efficient devices and appliances, hybrid/electric vehicles or renewable energy technologies, the WT1800E is a universal meter for power electronic measurements and energy analysis. Key applications include:

- Plug-in Hybrid and Electric Vehicles
- Industrial equipment such as Inverters, Motors and Pumps
- Renewable energy technologies such as Solar and Wind power
- Office and Home appliances like Air conditioners and Refrigerators
- IT Data center equipment like Servers, Routers and Switches
- Battery charging and Portable devices
- · Ballasts, LEDs & Fluorescent lighting
- Aircraft Power systems

The following pages cover some typical applications for the WT1800E.











Inverter and motor testing



Overview

Electric and hybrid vehicles have many electrical and mechanical components and therefore an overall performance evaluation requires the efficiency measurement of both. With 6 channels of power inputs, flexible operation and a wide bandwidth, the WT1800E is ideal for efficiency tests between the input and output of inverters. An optional motor evaluation function enables the measurement of rotation speed and changes in torque.






Figure 1 Line voltage/phase current

Figure 2 Delta-star conversion

Delta computation

Obtain the line and phase voltages from the sums and differences of the instantaneous values of voltage and current in each element.

- Line voltages and phase currents that are not measured are computed in the three-phase three-wire system (Figure 1).
- Star-delta conversion: Line voltage is computed from the phase voltage using the three-phase four-wire system data
- Delta-star conversion: Phase voltage is computed from the line voltage in the three-phase three-wire system (3V3A system) (Figure 2).

The WT1800E advantages

Wide bandwidth and High speed sampling

The WT1800E is capable of 16-bit high resolution and 2 MHz sampling making it possible to measure faster signals with higher precision.

Motor evaluation: Electrical angle/rotation/direction

Measure rotation speed, torque, and output (mechanical power) of motors from analog/pulse inputs of rotation or torque sensors.

Harmonics and dual harmonics

Simultaneously measure distortion factors like THD, fundamental and harmonic components. Harmonics up to the 500th order can be measured even at 50 ms data update rate. Users can also measure harmonics on two different sources simultaneously.


Battery charge/discharge measurements

In integrated measurement, the battery charge and discharge can be evaluated. Instantaneous positive and negative values captured at a high-speed sampling rate of 2 MS/s are integrated.

Line filter to remove high frequency components


In the power evaluation of inverter waveforms, measurement values are affected by high frequency components. A digital filter function makes it possible to remove unnecessary high frequency components superimposed on signals. The filter can be independently set for each input element. An analog filter for 1 MHz/300 kHz, and a digital filter that can be set from 100 Hz to 100 kHz in increments of 100 Hz are available as standard.

Efficiency of renewable energy systems



Overview

Energy generated by photovoltaic cell modules and wind turbines is converted from DC to AC by a power conditioner. Minimizing losses in these conversions improves the efficiency in the overall energy system. The WT1800E provides up to 6 power inputs per unit for measuring voltage, current, power, and frequency (for AC) before and after each converter, as well as the converter and charging efficiencies.



Measuring instantaneous peak power

In photovoltaic power generation, an MPPT control varies the voltage to maximize energy harvested from the solar panel. The WT1800E is capable of measuring not only the voltage, current, and power but also the voltage, current, and power peak values for both plus (+) and minus (–) sides.

The WT1800E advantages

Multiple channels and wide input range

Evaluate Power conditioner efficiency using 6 input channels for simultaneous measurements from the inputs and outputs of boost converter, inverter, and storage battery. Direct input terminals (voltage range: 1.5 V to 1000 V and current range: 10 mA to 5 A or 1 A to 50 A) make it possible to perform high-precision measurements without using a current sensor.

Harmonic distortion factor measurement

Voltage fluctuations and harmonics flow into the power system due to reverse power flow. A harmonic measurement function enables measurement of harmonic components to compute and display total harmonic distortion factor (THD).

Ripple factor and power loss measurements

A user-defined function makes it possible to compute power loss, DC voltage and DC current ripple factors between the input and output. Up to 20 arithmetic expressions can be set. Display names for the arithmetic operations F1, F2, and so on can be freely changed.


Typical arithmetic expressions

- 1. DC voltage ripple factor = [(Voltage peak value (+) Voltage peak value (-))/2 × DC voltage value (mean)] × 100
- 2. Power loss = Output power Input power

Energy bought/sold and charged/discharged

Measure the amount of power sold/bought in grid interconnection and of battery charge/discharge. Measure the amount of power sold/bought in grid interconnections and in battery charge/discharges. The WT1800E enables the integration of current (q), apparent power (WS), reactive power (WQ), as well as the effective power integration in sold/bought power and charge/discharge modes. Furthermore, a user-defined function makes it possible to calculate the Average active power within the integration period.


Efficiency of inverter-motor in electric vehicles



Overview

The WT1800E supports power measurements on up to 6 input channels making it ideal for evaluating the efficiency between the input and output of an electric vehicle. A motor evaluation function (option) makes it possible to simultaneously monitor voltage, current, and power changes, as well as changes in rotation speed, torque and mechanical power.

Typical repetitive high-speed charging and discharging signals



Charge current amount Ah (power amount Wh) and discharge current amount-Ah (power amount-Wh) can be integrated.

Battery charge/discharge measurements

In integrated measurement, the battery charge and discharge can be evaluated. Instantaneous positive and negative values captured at 2 MS/s high-speed sampling rate are integrated, and each of the total values is displayed.

The WT1800E advantage

Wide bandwidth and High speed sampling

The WT1800E is capable of 16-bit high resolution and 2 MHz sampling making it possible to measure faster signals with greater precision.

Harmonics and dual harmonics

Motor testing is performed at various rotation speeds. The WT1800E supports a lower limit frequency of 0.1 Hz to enable measurement of harmonics at a very low motor rotation speed without using an external sampling clock.

Motor evaluation: Electrical angle/rotation/direction

Measure rotation speed, torque, and output (mechanical) power of motors from analog/pulse outputs of rotation or torque sensors.

Individual null function: Offset correction for each input

A common problem when testing inverter motors is the presence of ambient noise that can mean test values are non zero even before testing begins. The WT1800E's null function allows users to enable, disable or reset the offset values for voltage, current and motor input signals of each element separately.

DA output and remote control

Sometimes users may want to check changes in data, along with other measurement data (temperature, etc.) at the same time that communication data, such as voltage, current, power, and efficiency is required. A DA output function allows users to generate analog signals on up to 20 channels.

Specifications

Voltage Plug-in terminal (safety terminal) Current Direct input: Large binding post External current sensor input: Insulated BNC connector Input type Voltage Floating input, resistive potential method Current Floating input, shunt input method 1.5 V, 3 V, 6 V, 10 V, 15 V, 30 V, 60 V, 100 V, 150 V, 300 V, 600 V, 1000 V (for Crest factor CF3) 0.75 V, 1.5 V, 3 V, 5 V, 7.5 V, 15 V, 30 V, 50 V, 75 V, 150 V, 300 V, 500 V (for Crest factor CF6/CF6A) Current Direct input 50 A input element A, 2 A, 5 A, 10 A, 20 A, 50 A (for Crest factor CF3) 500 mA, 1 A, 2.5 A, 5 A, 10 A, 25 A (for Crest factor CF6/CF6A) 10 mA, 20 mA, 50 mA, 100 mA, 200 mA, 500 mA, 1 A, 2 A, 5 A input element 5 A (for Crest factor CF3) 5 mA,10 mA, 25 mA, 50 mA, 100 mA, 250 mA, 500 mA, 1 A, 2.5 A (for Crest factor CF6/CF6A) External current sensor input 50 mV, 100 mV, 200 mV, 10 V, 2 V, 5 V, 10 V (for Crest factor CF3) 25 mV, 50 mV, 100 mV, 250 mV, 500 mV, 1 V, 2.5 V, 5 V (for Crest factor CF6/CF6A) Voltage Input resistance: Approximately 2 MΩ Input capacitance: Approximately 10 pF Current Direct input 50 A input element Approximately 2 m Ω + approximately 0.07 μ H 5 A input element Approximately 100 m Ω + approximately 0.07 μH External current sensor input Approximately 1 $M\Omega$ Instantaneous maximum allowable input (20 ms or less) Voltage Peak voltage of 4 kV or RMS of 2 kV, whichever is lower Current Direct input 50 A input element Peak current of 450 A or RMS of 300 A, whichever is lower 5 A input element Peak current of 30 A or RMS of 15 A, whichever is lower External current sensor input Peak current is less than 10 times the range Instantaneous maximum allowable input (1 second or less) Voltage Peak voltage of 3 kV or RMS of 1.5 kV, whichever is lower Current Direct input 50 A input element Peak current of 150 A or RMS of 55 A, whichever is lower 5 A input element Peak current of 10 A or RMS of 7 A, whichever is lower External current sensor input Peak current is less than 10 times the range Continuous maximum allowable input Peak voltage of 2 kV or RMS of 1.1 kV, whichever is lowe If the frequency of the input voltage exceeds 100 kHz, (1200 - f) Vrms or less The letter f indicates the frequency of the input voltage and the unit is kHz. Current Direct input 50 A input element Peak current of 150 A or RMS of 55 A, whichever is lower 5 A input element Peak current of 10 A or RMS of 7 A, whichever is lower External current sensor input Peak current is less than 5 times the range Continuous maximum common mode voltage (50/60 Hz) Voltage input terminals: 1000 Vrms Current input with /EX option 1000 Vrms (Maximum allowable voltage that can be measured) 600 Vrms (Rated voltage of EN61010-2-030 standard) terminals without /EX option 1000 Vrms External current sensor input connector: 600 Vrms Important Safety Note: Do not touch the inside of the BNC connector of the External Current Sensor input for safety reasons. Rated voltage to ground Voltage input terminals: 1000 V Current input with /EX option 1000 V (Maximum allowable voltage that can be measured) 600 V (Rated voltage of EN61010-2-030 standard) without /EX option 1000 V External current sensor input connector: 600 V Important Safety Note: Do not touch the inside of the BNC connector of the External Current Sensor input for safety reasons Influence from common voltage Apply 1000 Vrms for input terminal and case with the voltage input terminals shorted, the current input terminals open, and the external current sensor input terminals shorted. • 50/60 Hz: ±0.01% of range or less Reference value up to 100 kHz: ±((maximum rated range) / (rated range) × 0.001 x f% of range) or less. For external current sensor input, add ±(maximum rated range / rated range × [0.0125 × log (f × 1000) – 0.021]% of range}. However, 0.01% or more The unit of f is kHz. The maximum rated range within the equation is 1000 V or 50 A or 5 A or 10 V. Line filter Select OFF, 100 Hz to 100 kHz (in increments of 100 Hz), 300 kHz, or 1 MHz Under condition of other than Auto data update interval Select OFF, 100 Hz, or 1 kHz Frequency filter Under condition of Auto data update interval OFF, 100 Hz, 200 Hz, 400 Hz, 800 Hz, 1.6 kHz, 3.2 kHz, 6.4 kHz, 12.8 kHz and 25.6 kHz A/D converter Simultaneous voltage and current input conversion Resolution: 16-bit Conversion speed (sampling period): Approximately 500 ns. See harmonic measurement items for harmonic measurement Range switching A range can be set for each input element

Auto range functions

- Range up

 When the measured values of Urms and Irms exceed 110% of the range (exceed 220% when crest factor is set to CF6A)
 - When the peak value of the input signal exceeds approximately 330% of the range (or approximately 660% for crest factor CF6/CF6A)

Range down: When the following conditions are met, the range setting switches down.

- When the measured values of Urms and Irms fall to 30% or less of the range
- When the measured values of Urms and Irms fall to 105% or less of the lower range (range to which the range setting switches down)
- When the measured values of Upeak and Ipeak fall to 300% or less of the lower range (600% or less for crest factor CF6/CF6A)

Display

Display 8.4-inch color TFT LCD display

Total number of pixels*

1024 (horizontal) × 768 (vertical) dots

*Up to approximately 0.002% of the pixels on the LCD may be defective

Display update rate

Same as the data update rate

- 1) The display update interval of numeric display alone is 200 ms to 500 ms (which varies depending on the number of display items) when the data update rate is 50 ms, 100 ms, and 200 ms
- 2) The display update interval of display items other than numeric display (including custom displays) is approximately 1 s when the data update interval is 50 ms, 100 ms, 200 ms, and 500 ms.
- 3) If the measurement mode display is set to Normal Mode (Trg), measurement takes place from when a trigger is detected over the data update interval.

 The following amount of time is required for the WT1800E to compute the measured

data, process it for displaying, and so on, and become ready for the next trigger.

- When the data update interval is 50 ms to 500 ms: Approximately 1 s
- When the data update interval is 1 s to 5 s: Data update interval + 500 ms

In this case, storage, communication output, and D/A output operate in sync with the triggers. If the measurement mode display is set to Normal Mode, storage, communication output, and D/A output operate in sync with the data update interval.

4) The display update interval is more than 200 ms in the case of numerical value indication

when update interval is set to Auto. In addition, the interval is more than 1 s in case of other display indications including Custom screen excepting the numerical value.

Display Items

Calculation Function	ons						
Measurement Function		Single-phase 3-wire	3-phase 3-wire	3-phase 3-wire (3-voltage 3-current measurement)	3-phase 4-wire		
Voltage UΣ [V]		(U1+U2)/2		(U1+U2+U3)/3			
Current I∑ [A]		(11+12)/2		(11+12+13)/3			
Active power P∑	[W]	P1+P2		P1+P2+P3			
Apparent Power SΣ [VA]	TYPE1 TYPE2	-S1+S2	$\frac{\sqrt{3}}{2}$ (S1+S2)	$\frac{\sqrt{3}}{3}$ (S1+S2+S3)	S1+S2+S3		
	TYPE3	$\sqrt{P\Sigma^2 + Q\Sigma^2}$	$\sqrt{P\Sigma^2 + Q\Sigma^2}$				
Reactive Power	TYPE1	Q1+Q2			Q1+Q2+Q3		
QΣ [var]	TYPE2	$\sqrt{S\Sigma^2 - P\Sigma^2}$					
	TYPE3	Q1+Q2			Q1+Q2+Q3		
Corrected Power	PcΣ [W]	Pc1+Pc2			Pc1+Pc2+Pc3		
Integrated Power \	WPΣ [Wh]	WP1+WP2			WP1+WP2+WP3		
Integrated Power		WP+1+WP+2			WP+1+WP+2+WP+5		
(Positive) WP+Σ [Wh]	When WPTYPE is set to CHARGE/DISCHARGE					
		WP Σ is added This item is not calculated when Data update interval is set to Auto					
Integrated Power		WP-1+WP-2 WP-1+WP-3					
(Negative) WP-∑	[Wh]	When WPTYPE is set to CHARGE/DISCHARGE					
		When WPTYPE is set to SOLD/BOUGHT Whenever data is updated, only the negative value of active power WP∑ is adde This item is not calculated when Data update interval is set to Auto					
Integrated Current q∑ [Ah]		q1+q2			q1+q2+q3		
Integrated Current (Positive) q+Σ [Ah]		q+1+q+2			q+1+q+2+q+3		
Integrated Current (Negative) q-∑ [Ah]		q-1+q-2			q-1+q-2+q-3		
Integrated reactive Power WQ∑ [varh]		$ \frac{1}{N} \sum_{n=1}^{N} Q\Sigma(n) \times Time $					
		$\begin{split} &Q\Sigma(n) \text{ indicates the }\Sigma \text{ function of the } n^{th} \text{ reactive power, N indicates the number of data updates, and the unit of Time is h} \\ &This item is not calculated when Data update interval is set to Auto \end{split}$					
Integrated apparent Power WS∑ [VAh]		$\frac{1}{N} \sum_{r=1}^{N} S\Sigma(r) \times Time$					
WS∑ [VAh]			$S\Sigma(n)$ indicates the Σ function of the n^{th} apparent power, N indicates the number of data updates, and the unit of Time is h . This item is not calculated when Data update interval is set to Auto				
WSΣ [VAh]							
WSΣ [VAh] Power Factor Σ							

Note 1) The instrument's apparent power (S), reactive power (O), power factor (A), and phase difference (O) are calculated using measured values of voltage, current, and active power.

(However, reactive power is calculated directly from sampled data when TYPE3 is selected.) Therefore, when distorted waveforms are input, these values may be different from those of other measuring instruments based on different measuring principals.

Note 2) The value of Q for each phase in the $Q\Sigma$ calculation is calculated with a preceding minus sign (–) when the current input leads the voltage input, and a plus sign when it lags the voltage input, so the value of $Q\Sigma$ may be negative.

Nur

Har

	Q∑ may be negative.	
me	erical Display	
		obtained for each input element] Urms: True RMS value, Urm: Rectified mean value calibrated to the RMS value, Udc: Simple mean value, Urmn: Rectified mean value, Uac: AC component
	Current (A)	Urms: True RMS value, Irm: Rectified mean value calibrated to the RMS value, Idc: Simple mean value, Irmn: Rectified mean value, Iac: AC component
	Active power (W)	P
	Apparent power (VA)	S
	Reactive power (var)	Q
	Power factor	λ
	Phase angle (°)	<u></u>
	Frequency (Hz)	fU (FreqU): Voltage frequency, fl (FreqI): Current frequency
	Maximum and minim	um vortage values (v) U+peak: Maximum voltage value, U-peak: Minimum voltage value
	Maximum and minimi	um current values (A) I+peak: Maximum current value, I-peak: Minimum current value
	Maximum and minimi	um power values (W) P+peak: Maximum power value, P-peak: Minimum power value
	Crest factor	CfU: Voltage crest factor, Cfl: Current crest factor
	Corrected power (W)	
	Integration	Applicable standards IEC76-1 (1976), IEC76-1 (1993)
	Integration	Time: Integration time WP: Sum of the amount of both positive and negative power WP+: Sum of positive P (amount of power consumed) WP-: Sum of negative P (amount of power returned to the grid) q: Sum of the amount of both positive and negative current q+: Sum of positive I (amount of current) q-: Sum of negative I (amount of current) WS*: Amount of apparent power WQ*: Amount of reactive power However, the amount of current is integrated by selecting any one of Irms, Inn, Idc, Iac, and Irmn depending on the setting of the current mode.
		*Excepting when data update interval is set to Auto.
[M	leasurement function () Voltage (V)	Eunction) obtained for each connected unit (ΣΑ, ΣΒ, ΣC)] UrmsΣ: True RMS value, UrmsΣ: Rectified mean value calibrated to the RMS value, UdcΣ: Simple mean value, Urmn: Rectified mean value, UacΣ: AC component
	Current (A)	Irms∑: True RMS value, Imn∑: Rectified mean value calibrated to the
		RMS value, Idc∑: Simple mean value, Irmn∑: Rectified mean value, Iac∑: AC component
	Active power (W)	
	Active power (W) Apparent power (VA)	Imm Σ : Rectified mean value, Iac Σ : AC component P Σ
	Apparent power (VA)	Imm Σ : Rectified mean value, Iac Σ : AC component P Σ
	Apparent power (VA) Reactive power (var)	Imn Σ : Rectified mean value, Iac Σ : AC component $P\Sigma$ $S\Sigma$ $Q\Sigma$
	Apparent power (VA) Reactive power (var) Power factor	Imm Σ : Rectified mean value, Iac Σ : AC component P Σ S Σ Q Σ
	Apparent power (VA) Reactive power (var)	Imm Σ : Rectified mean value, Iac Σ : AC component P Σ S Σ Q Σ
	Apparent power (VA) Reactive power (var) Power factor	Irmn Σ : Rectified mean value, Iac Σ : AC component $P\Sigma$ $S\Sigma$ $Q\Sigma$ $\lambda\Sigma$ $Pc\Sigma$
rm	Apparent power (VA) Reactive power (var) Power factor Corrected power (W)	IrmnΣ: Rectified mean value, $IacΣ: AC$ component $PΣ$ $SΣ$ $QΣ$ $λΣ$ $PcΣ$ Applicable standards IEC76-1 (1976), IEC76-1 (1993) TimeΣ: Integration time WPΣ: Sum of the amount of both positive and negative power WP+Σ: Sum of positive P (amount of power consumed) WP-Σ: Sum of negative P (amount of power returned to the grid) $qΣ: Sum of the amount of both positive and negative current q+Σ: Sum of positive I (amount of current) q-Σ: Sum of negative I (amount of current) WSΣ: Integration of SΣ WQΣ: Integration of QΣ$
	Apparent power (VA) Reactive power (var) Power factor Corrected power (W) Integration	IrmnΣ: Rectified mean value, $IacΣ: AC$ component $PΣ$ $SΣ$ $QΣ$ $λΣ$ $PcΣ$ Applicable standards IEC76-1 (1976), IEC76-1 (1993) TimeΣ: Integration time WPΣ: Sum of the amount of both positive and negative power WP+Σ: Sum of positive P (amount of power consumed) WP-Σ: Sum of negative P (amount of power returned to the grid) $qΣ: Sum of the amount of both positive and negative current q+Σ: Sum of positive I (amount of current) q-Σ: Sum of negative I (amount of current) WSΣ: Integration of SΣ WQΣ: Integration of QΣ$
	Apparent power (VA) Reactive power (var) Power factor Corrected power (W) Integration onic Measurement (Ceasurement function of	Irmn Σ : Rectified mean value, Iac Σ : AC component P Σ S Σ Q Σ Q Σ $\lambda \Sigma$ Pc Σ Applicable standards IEC76-1 (1976), IEC76-1 (1993) Time Σ : Integration time WP Σ : Sum of the amount of both positive and negative power WP+ Σ : Sum of positive P (amount of power consumed) WP- Σ : Sum of negative P (amount of power returned to the grid) q Σ : Sum of the amount of both positive and negative current q+ Σ : Sum of positive I (amount of current) WS Σ : Integration of S Σ WQ Σ : Integration of Q Σ Detained for each input element] U (k): RMS value of the harmonic voltage of order k'1,
	Apparent power (VA) Reactive power (var) Power factor Corrected power (W) Integration onic Measurement (Cleasurement function of Voltage (V)	IrmnΣ: Rectified mean value, $IacΣ: AC$ component $PΣ$ $SΣ$ $QΣ$ $λΣ$ $AΣ$ $PcΣ$ $Applicable standards IEC76-1 (1976), IEC76-1 (1993) TimeΣ: Integration time WPΣ: Sum of the amount of both positive and negative power WP+Σ: Sum of positive P (amount of power consumed) WP-Σ: Sum of negative P (amount of power returned to the grid) qΣ: Sum of the amount of both positive and negative current q+Σ: Sum of positive I (amount of current) q-Σ: Sum of the amount of both positive and negative current q+Σ: Sum of positive I (amount of current) WSΣ: Integration of SΣ: Sum of negative I (amount of current) SVΣ: Integration of SΣ: Sum of negative I (amount of current) SVΣ: Integration of SΣ: Sum of negative I (amount of current) Ditained for each input element] U (k): RMS value of the harmonic voltage of order k'1, U: Voltage RMS value of the harmonic current of order k,$
	Apparent power (VA) Reactive power (var) Power factor Corrected power (W) Integration onic Measurement (Ceasurement function of Voltage (V) Current (A) Active power (W)	IrmnΣ: Rectified mean value, $IacΣ: AC$ component $PΣ$ $SΣ$ $QΣ$ $λΣ$ $PcΣ$ $Applicable standards IEC76-1 (1976), IEC76-1 (1993) TimeΣ: Integration time WPΣ: Sum of the amount of both positive and negative power WPΣ: Sum of positive P (amount of power consumed) WPΣ: Sum of positive P (amount of power returned to the grid) qΣ: Sum of the amount of both positive and negative current qΣ: Sum of positive P (amount of current) qΣ: Sum of positive P (amount of current) VPΣ: Sum of positive P (amount of current) VPΣ: Sum of positive P (amount of current) VPΣ: Sum of negative P (amount of current) VPΣ: Sum $
	Apparent power (VA) Reactive power (var) Power factor Corrected power (W) Integration onic Measurement (Ceasurement function of Voltage (V) Current (A) Active power (W)	Irmn Σ : Rectified mean value, lac Σ : AC component P Σ S Σ Q Σ N Σ Pe Σ Applicable standards IEC76-1 (1976), IEC76-1 (1993) Time Σ : Integration time WP Σ : Sum of the amount of both positive and negative power WP+ Σ : Sum of positive P (amount of power consumed) WP- Σ : Sum of negative P (amount of power returned to the grid) q Σ : Sum of the amount of both positive and negative current q- Σ : Sum of positive I (amount of current) WS Σ : Integration of S Σ WQ Σ : Integration of S Σ WQ Σ : Integration of Q Σ Ditained for each input element] U (k): RMS value of the harmonic voltage of order k $^{+}$, U: Voltage RMS value (Total value 2) I (k): RMS value of the harmonic current of order k, I: Current RMS value (Total value 2) P (k): Active power of the harmonic of order k, P: Active power (Total value 2)
	Apparent power (VA) Reactive power (var) Power factor Corrected power (W) Integration onic Measurement (Ceasurement function of Voltage (V) Current (A) Active power (W) Apparent power (VA)	IrmnΣ: Rectified mean value, IacΣ: AC component PΣ SΣ QΣ λΣ PcΩ Applicable standards IEC76-1 (1976), IEC76-1 (1993) TimeΣ: Integration time WPΣ: Sum of the amount of both positive and negative power WP+Σ: Sum of positive P (amount of power consumed) WP-Σ: Sum of negative P (amount of power returned to the grid) qΣ: Sum of the amount of both positive and negative current q+Σ: Sum of positive I (amount of current) q-Σ: Sum of negative I (amount of current) WSΣ: Integration of SΣ WQΣ: Integration of SΣ WQΣ: Integration of QΣ Option) It (k): RMS value of the harmonic voltage of order k¹, U: Voltage RMS value (Total value²) I (k): RMS value of the harmonic current of order k, I: Current RMS value (Total value²) P (k): Active power of the harmonic of order k, S: Total apparent power of the harmonic of order k, S: Total apparent power of the harmonic of order k, S: Total apparent power (Total value²)
	Apparent power (VA) Reactive power (var) Power factor Corrected power (W) Integration onic Measurement (Cleasurement function of Voltage (V) Current (A) Active power (W) Reactive power (VA)	IrmnΣ: Rectified mean value, IacΣ: AC component PΣ SΣ QΣ λΣ PcΣ Applicable standards IEC76-1 (1976), IEC76-1 (1993) TimeΣ: Integration time WPΣ: Sum of the amount of both positive and negative power WP+Σ: Sum of positive P (amount of power consumed) WP-Σ: Sum of negative P (amount of power returned to the grid) qΣ: Sum of the amount of both positive and negative current q+Σ: Sum of positive I (amount of current) q-Σ: Sum of negative I (amount of current) WSΣ: Integration of SΣ WQΣ: Integration of QΣ Potion) Id(k): RMS value of the harmonic voltage of order k¹, U: Voltage RMS value (Total value²) I (k): RMS value of the harmonic of order k, E: Current RMS value (Total value²) S (k): Active power (Total value²) S (k): Apparent power of the harmonic of order k, S: Total apparent power (Total value²) Q (k): Reactive power of the harmonic of order k, C: Total reactive power (Total value²) A (k): Power factor of the harmonic of order k, Total power factor (Total value²) Q (k): Phase angle between the harmonic voltage and current of order k, C: Total phase angle of each harmonic voltage U (k) relative to the fundamental wave U (1) Q (k): Phase angle of each harmonic current I (k) relative to the fundamental wave U (1)

Resistance and reactance of	the load circuit (Ω)	
	Rs (k): Resistance of the load circuit to the harmonic of order k when the resistance R, the inductance L, and the capacitor C are connected in series Xs (k): Resactance of the load circuit to the harmonic of order k when the resistance R, the inductance L, and the capacitor C are connected in series Rp (k): Resistance of the load circuit to the harmonic of order k when the resistance R, the inductance L, and the capacitor C are connected in parallel Xp (k): Reactance of the load circuit to the harmonic of order k when the resistance R, the inductance L, and the capacitor C are connected in parallel	
Harmonic content [%]	Uhdf (k): Ratio of the harmonic voltage U (k) to U (1) or U Ihdf (k): Ratio of the harmonic current I (k) to I (1) or I Phdf (k): Ratio of the active harmonic power P (k) to P (1) or F	
Total harmonic distortion [%]	Uthd: Ratio of the total harmonic ⁻³ voltage to U (1) or U lthd: Ratio of the total harmonic ⁻³ current to I (1) or I Pthd: Ratio of the total harmonic ⁻³ active power to P (1) or P	
Telephone harmonic factor	Uthf: Voltage telephone harmonic factor, lthf: Current telephone harmonic factor Applicable standard: IEC34-1 (1996)	
Telephone influence factor	Utif: Voltage telephone influence factor, Itif: Current telephone influence factor Applicable standard: IEEE Std 100 (1996)	
Harmonic voltage factor*4	hvf: harmonic voltage factor	
Harmonic current factor*4	hcf: harmonic current factor	
K-factor	Ratio of the sum of the squares of weighted harmonic components to the sum of the squares of the orders of harmonic current	

- order is a DC current component (dc). The upper limit value for the measured order is automatically determined up to the 500th order depending on the frequency of the PLL source.
- *2: The total value is calculated by obtaining the fundamental wave (the 1st order) and all harmonic components (from the 2nd order to the upper limit value for the measured order). Also, the DC component (dc) can be added to the equation.
- *3: The total harmonic is calculated by obtaining the total harmonic component (from the 2nd order to the upper limit value for the measured order)
- *4 : The equations may vary depending on the definitions in the standards, etc. Check the standards for

[Measurement function indicating the phase difference of the fundamental wave between the voltage and current between input elements]

This is a measurement function indicating the phase angle of the fundamental wave U (1) or I (1) of another element to the fundamental wave U (1) of the element with the smallest number among input elements assigned to the connected unit. The following table shows measurement functions for the connected unit with a combination of the elements 1, 2, and 3.

Phase angle U1-U2 (°)

ØU1–U2: Phase angle of the fundamental wave (U2 (1)) of the voltage of the element 2 to the fundamental wave (U1 (1)) of the voltage of the element 1

Phase angle U1-U3 (°)

ØU1-U3: Phase angle of the fundamental wave (U3 (1)) of the voltage of the element 3

Phase angle U1-I1 (°)

to U1 (1)

ØU1-I1: Phase angle of the fundamental wave (I1 (1)) of the current of the element 1 to U1 (1)

Phase angle U2-I2 (°)

ØU2-I2: Phase angle of the fundamental wave (I2 (1)) of the current of the element 2 to U2 (1) Phase angle U3-I3 (°)

ØU3-I3: Phase angle of the fundamental wave (I3 (1)) of the current of the element 3 to U3 (1)

EaU1 to EaU6 (°), EaI1 to EaI6 (°) Phase angle Ø of the fundamental waves of U1 to I6 based on the rise of the Z terminal

input in the motor evaluation function (option).

N is the set value for the number of poles in the motor evaluation function.

[Measurement function (Σ function) obtained for each connected unit (Σ A, Σ B, Σ C)]

 $U\Sigma$ (1): RMS of the harmonic voltage of order 1, $U\Sigma$: RMS of the voltage (Total value*)

IS (1): RMS of the harmonic current of order 1, IS: RMS of the current (Total value*)

Active power (W)

 $P\Sigma$ (1): Harmonic active power of order 1, $P\Sigma$: Total active power (Total value*)

Apparent power (VA)

SΣ (1): Harmonic apparent power of order 1, SΣ: Total apparent power (Total value*)

 $Q\Sigma$ (1): Harmonic reactive power of order 1, $Q\Sigma$: Total reactive power (Total value*)

 $\lambda \Sigma$ (1): Harmonic power factor of order 1, $\lambda \Sigma$: Total power factor (Total value*)

*The total value is calculated by obtaining the fundamental wave (the 1st order) and all harmonic components (from the 2nd order to the upper limit value for the measured order). Also, the DC component (dc) can be added to the equation.

Delta Calculation

Voltage (V)	difference	$\Delta \text{U1:}$ Differential voltage between U1 and U2 determined by computation
	3P3W->3V3A	$\Delta \text{U1:}$ Line voltage that is not measured but can be computed for a three-phase, three-wire system
	DELTA->STAR	$\Delta U1,\Delta U2,\Delta U3$: Phase voltage that can be computed by a three-phase, three-wire (3V3A) system $\Delta U\Sigma = (\Delta U1 + \Delta U2 + \Delta U3)/3$
	STAR->DFLTA	AU1, AU2, AU3: Line voltage that can be computed for a three-

phase, four-wire system $\Delta U \Sigma = (\Delta U 1 + \Delta U 2 + \Delta U 3)/3$

	Current (A) difference		ce	$\Delta \text{I1:}$ Differential current between I1 and I2 determined by computation		
	3P3W->3V3		-3V3A	ΔI: Phase current that is not measured		
		DELTA-:	>STAR	ΔI: Neutral line current		
		STAR->	DELTA	ΔI: Neutral line current		
	Power (W)	difference	ce	-		
		3P3W->	-3V3A	_		
		DELTA-:	>STAR	Δ P1, Δ P2, Δ P3: Phase power determined by computation for a three-phase, three-line (3V3A) system Δ P $\Sigma = \Delta$ P1 + Δ P2 + Δ P3		
		STAR->	DELTA	_		
W	aveform/Tre	nd				
				ys the waveforms of the voltage and current from elements 1 yh 6, torque, speed, AUX1, and AUX2.		
	seque		seque	ys trends in numerical data of the measurement functions in a ntial line graph. er of measurement channels: Up to 16 parameters		
В	ar Graph/Ved	ctor (/G5	/G6 O	ption)		
			Displa	ys the size of each harmonic in a bar graph.		
				ys the vector of the phase difference in the fundamental waves of e and current.		

Accuracy

Voltage and Current: Accuracy (six-month)
Conditions Temperature: 23±5°C, Humidity: 30 to 75%RH, Input waveform: Sine wave, Power factor (\(\lambda\): 1, Common mode voltage: 0 V, Crest factor: CF3, Line filter: OFF Frequency filter: 1 kHz or less when ON, after warm-up. After zero level compensation or range value changed while wired. The unit of f

within the accuracy equation is kHz.

Voltage

Frequency	Accuracy ±(Measurement reading error + Setting range error)
DC	±(0.05% of reading + 0.05% of range)
0.1 Hz ≤ f < 10 Hz	±(0.03% of reading + 0.05% of range)
10 Hz ≤ f < 45 Hz	±(0.03% of reading + 0.05% of range)
45 Hz ≤ f ≤ 66 Hz	±(0.03% of reading + 0.05% of range)*
66 Hz < f ≤ 1 kHz	±(0.1% of reading + 0.1% of range)
1 kHz < f ≤ 50 kHz	±(0.3% of reading + 0.1% of range)
50 kHz < f ≤ 100 kHz	±(0.6% of reading + 0.2% of range)
100 kHz < f ≤ 500 kHz	±[(0.006 × f)% of reading + 0.5% of range]
500 kHz < f ≤ 1 MHz	±[(0.022 × f - 8)% of reading + 1% of range]
Frequency bandwidth	5 MHz (-3 dB, typical)
*Add 0.02% of reading under	r condition of the 1000 V range.

Current

Frequency	Accuracy ±(Measurement reading error + Setting range error)
DC	±(0.05% of reading + 0.05% of range)
0.1 Hz ≤ f < 10 Hz	±(0.03% of reading + 0.05% of range)
10 Hz ≤ f < 45 Hz	±[(0.03% of reading + 0.05% of range) + (2 μA*)]
45 Hz ≤ f ≤ 66Hz	±[(0.03% of reading + 0.05% of range) + (2 μA*)]
66 Hz < f ≤ 1 kHz	±(0.1% of reading + 0.1% of range) Direct input of the 50 A input element ±(0.2% of reading + 0.1% of range)
1 kHz < f ≤ 50 kHz	$\begin{array}{l} \pm (0.3\% \ of \ reading + 0.1\% \ of \ range) \\ 50 \ mV, \ 100 \ mV, \ 200 \ mV \ range \ of \ the \ external \ current \\ sensor \ input \\ \pm (0.5\% \ of \ reading + 0.1\% \ of \ range) \\ Direct \ input \ of \ the \ 50 \ A \ input \ element \\ \pm [(0.1 \times f + 0.2)\% \ of \ reading + 0.1\% \ of \ range] \end{array}$
50 kHz < f ≤ 100 kHz	±(0.6% of reading + 0.2% of range) Direct input of the 50 A input element ±[(0.1 × f + 0.2)% of reading + 0.1% of range]
100 kHz < f ≤ 200 kHz	$ \begin{array}{l} \pm [(0.006 \times f)\% \text{ of reading} + 0.5\% \text{ of range}] \\ \text{Direct input of the 50 A input element} \\ \pm [(0.05 \times f + 5)\% \text{ of reading} + 0.5\% \text{ of range}] \end{array} $
200 kHz < f ≤ 500 kHz	±[(0.006 × f)% of reading + 0.5% of range] Direct input of the 50 A input element: It does not define accuracy.
500 kHz < f ≤ 1 MHz	±[(0.022 × f - 8)% of reading + 1% of range] Direct input of the 50 A input element: It does not define accuracy.
Frequency bandwidth	5 MHz (-3 dB, typical): 5 A input element, External current sensor input of the 50 A input element
*Not added under the Extern	al current sensor input setting

Power: Accuracy (six-month)

ocuracy of the voltage and current Conditions

Same as the accuracy of	the voltage and current
Frequency	Accuracy ±(Reading error + Measurement range error)
DC	±(0.05% of reading + 0.05% of range)
0.1 Hz ≤ f < 10 Hz	±(0.08% of reading + 0.1% of range)
10 Hz ≤ f < 45 Hz	±[(0.08% of reading + 0.1% of range) + (2 μA × U)*]
45 Hz ≤ f ≤ 66 Hz	±[(0.05% of reading + 0.05% of range) + (2 μA × U)*]
66 Hz < f ≤ 1 kHz	±(0.2% of reading + 0.1% of range)
1 kHz < f ≤ 50 kHz	±(0.3% of reading + 0.2% of range) 50 mV, 100 mV, 200 mV range of the external current sensor input ±(0.5% of reading + 0.2% of range) Direct input of the 50 A input element ±((0.1 × f + 0.2)% of reading + 0.2% of range)
50 kHz < f ≤ 100 kHz	±(0.7% of reading + 0.3% of range) Direct input of the 50 A input element ±[(0.3 × f - 9.5)% of reading + 0.3% of range]
100 kHz < f ≤ 200 kHz	±[(0.008 × f)% of reading + 1% of range] Direct input of the 50 A input element ±[(0.09 × f + 11)% of reading + 1% of range]
200 kHz < f ≤ 500 kHz	±[(0.008 × f)% of reading + 1% of range] Direct input of the 50 A input element: It does not define accuracy.
500 kHz < f ≤ 1 MHz	±((0.048 × f - 20)% of reading + 2% of range) Direct input of the 50 A input element: It does not define accuracy.
*Not added under the Extern	ol ourrant concer input catting

*Not added under the External current sensor input setting

 Add the following value to the above accuracy for the external current sensor range. Current DC accuracy: $\pm 50~\mu V$ Power DC accuracy: $\pm [(50~\mu V/External~current~sensor~range~rating) \times 100\%~of~range]$

Add the following value to the above accuracy for the direct current input range. 50 A input element

Current DC accuracy: ±1.5 mA

Power DC accuracy: \pm [(1 mA/Direct current input range rating) \times 100% of range] Current DC accuracy: ±(10 µA/Direct current input range rating) × 100% of range)

Power DC accuracy: ±(10 µA/Direct current input range rating) × 100% of range)

Accuracy of the waveform display data, Upeak and Ipeak Add the following value to the above accuracy (reference value). The effective input range is within ±300% of range (within ±600% for Crest factor CF6/CF6A)

Voltage input: $\pm \left[\left(1.5 \times \sqrt{\frac{15}{\text{range}}} + 0.5 \right) \% \text{ of range} \right]$

50 A input element: $\pm \left(3 \times \sqrt{\frac{1}{\text{range}}} \% \text{ of range} + 10 \text{ mA}\right)$ Direct current input

5 A input element: $\pm \left[\left(10 \times \sqrt{\frac{10 \text{ m}}{\text{range}}} + 0.5 \right) \% \text{ of range} \right]$

50 mV to 200 mV range: $\pm \left[\left(10 \times \sqrt{\frac{0.01}{\text{range}}} + 0.5 \right) \% \text{ of range} \right]$ External current sensor

500 mV to 10 V range: $\pm \left[\left(10 \times \sqrt{\frac{0.05}{\text{range}}} + 0.5 \right) \% \text{ of range} \right]$

Influence from a temperature change after zero level compensation or range change Add the following value to the above accuracy. Voltage DC accuracy; ±0.02% of range/°C DC accuracy of the direct current input

50 A input element: ±1 mA/°C 5 A input element: ±10 µA/°C

DC accuracy of the external current sensor input: ±50 µW°C DC power accuracy: Influence from the voltage × Influence from the current

Influence from the self-heating caused by voltage input
Add the following value to the voltage and power accuracy.
AC input signal: ±(0.0000001 × U[®] of reading)
DC input signal: ±(0.0000001 × U[®] of reading + 0.0000001 × U[®] of range) U is the voltage reading (V).

The influence from the self-heating continues until the temperature of the input resistor decreases, even if the voltage input changes to a small value

Influence from the self-heating caused by our of striath value.

Influence from the self-heating caused by our ent input.

Add the following value to the current and power accuracy of the 50 A element.

AC input signal: ±0.00006 x f% of reading

DC input signal: ±0.0006 x f% of reading + 0.004 x f* mA)

Add the following value to the current and power accuracy of the 5 A element.

AC input signal: ±0.006 x f% of reading

DC input signal: ±0.006 x f% of reading

DC input signal: ±0.006 x f% of reading

I is the current reading (A)

The influence from the self-heating continues until the temperature of the shunt resistor decreases, even if the current input changes to a small value.

Range of guaranteed accuracy by frequency, voltage, and current
All accuracies between 0.1 Hz to 10 Hz are reference values.

If the voltage exceeds 750 V at 30 kHz to 100 kHz, the voltage and power values are reference values.

If the current exceeds 20 A at DC, 10 Hz to 45 Hz, or 400 Hz to 100 kHz, the current and

power accuracies are reference values

Accuracy for Crest factor CF6/CF6A
 Same as the range accuracy of Crest factor CF3 for twice the range

When $\lambda = 0$

 $_{\rm H}$ (N) and the range of 45 Hz to 66 Hz For frequencies other than the above (Design values):

5 A input element and the external sensor input: \pm [Apparent power reading \times (0.07 + 0.05 \times f)%]

Direct input of the 50 A input element:

 \pm [Apparent power reading \times (0.07 + 0.3 \times f)%]

When 0 < λ < 1 $\,$ ±Power reading \times {(Power reading error %) + (Power range error %) > (Power range/Apparent power reading) + [tan $\emptyset \times$ (Influence % when $\lambda = 0$)]} Ø is the phase angle between the voltage and current. "Influence % when $\lambda=0$ " will be changed according to input frequency f of above expression.

Influence of line filter

When the cutoff frequency (fc) is 100 Hz to 100 kHz

Up to
$$\frac{\text{fc}}{2}$$
 Hz: Add $\pm \left\{ 2 \times \left[1 - \sqrt{\frac{1}{1 + \left(\frac{f}{\text{fc}}\right)^4}} \right] \times 100 + \left(20 \times \frac{f}{300 \text{ k}} \right) \% \right\}$ of reading

Applies to frequency less than or equal to 30 kHz

Power

Up to
$$\frac{\text{fc}}{2}$$
 Hz: Add $\pm \left\langle 4 \times \left[1 - \sqrt{\frac{1}{1 + \left(\frac{f}{\text{fc}}\right)^4}} \right] \times 100 + \left(40 \times \frac{f}{300 \text{ k}}\right) \% \right] \text{ of reading}$

Applies to frequency less than or equal to 30 kHz

When the cutoff frequency (fc) is 300 kHz and 1 MHz

Voltage/current Up to (fc/10) Hz: Add \pm (20 × f/fc)% of reading

Up to (fc/10) Hz: Add \pm (40 \times f/fc)% of reading

Lead/lag phase detection [D (LEAD)/G (LAG) of the phase angle]

The phase lead and lag can be detected correctly when the voltage and current input signals are as follows.

- Sine wave
- 50% or more of the measurement range (100% or more for crest factor CF6/CF6A)
- Frequency: 20 Hz to 10 kHz
- Phase angle: ±(5° to 175°)

Symbols for the reactive power Q∑ calculation

The symbols shows the lead/lag of each element, and "-" indicates leading.

Temperature coefficient

±0.03% of reading/°C at 5 to 18°C or 28 to 40°C

Effective input range

Udc and Idc: 0 to ±110% of the measurement range

Urms and Irms: 1 to 110% of the measurement range Umn and Imn: 10 to 110% of the measurement range

Urmn and Irmn: 10 to 110% of the measurement range Power (DC measurement): 0 to ±110%

(AC measurement): $\pm 110\%$ of the power range when the voltage and current range is 1 to 110%.

However, the synchronization source level shall meet the input signal level of frequency measurement. Each of the lower and higher limits are doubled for Crest factor CF6/CF6A.

Maximum display value

140% of the voltage and current range rating When Crest factor is set to CF6A, 280% of the voltage and current range rating

Displays the following values relative to the measurement range.

- Urms, Uac, Irms, Iac: Up to 0.3% (up to 0.6% for Crest factor CF6/CF6A)
- Umn, Umn, Imn. Imn: Up to 2% (up to 4% for Crest factor CF6/CF6A)
 When input level is lower than above, the display shows zero if zero-suppress setting is ON, otherwise measured value will be shown. Current integration value q depends on the current value as well

Measurement lower limit frequency

Data update rate	50 ms	100 ms	200 ms	500 ms		
Measurement lower limit frequency	45 Hz	25 Hz	12.5 Hz	5 Hz		
Data update rate	1 s	2 s	5 s	10 s	20 s	Auto
Measurement lower limit frequency	2.5 Hz	1 25 Hz	0.5 Hz	0.2 Hz	0.1 Hz	0 1 Hz

Accuracy of apparent power S

±(Voltage accuracy + Current accuracy)

Accuracy of reactive power O

 \pm [Accuracy of apparent power + ($\sqrt{1.0004 - \lambda^2} - \sqrt{1 - \lambda^2}$) × 100% of range]

Accuracy of power factor $\lambda = \pm [(\lambda - \lambda /1.0002) + |\cos \emptyset - \cos [\emptyset + \sin^{-1} (influence of power factor of power when$

\$\lambda = 0\%/100||\frac{1}{k} \text{ = 1 (with the state of points which is at rated input of the measurement range \$\mathrea{O}\$ is the phase difference of voltage and current.

Accuracy of phase angle Ø

 $\pm (| \emptyset - \{\cos^{-1}(\lambda/1.0002)| + \sin^{-1}[(\inf \text{luence of power factor of power when } \lambda = 0\%)/100]\})$ deg ±1 digit, when voltage and current is at the rated input of the measurement range

One-year accuracy

Multiply the reading error of the six-month accuracy by a factor of 1.5

Functions

easurement Functions and Conditions

Crest factor: 300 (relative to the minimum valid input) CF3: 3 (relative to the rated value of the mesurement range)

CF6/CF6A: 6 (relative to the rated value of the measurement range)

Measurement period

Interval for determining the measurement function and performing calculations.

- The measurement period is set by the zero crossing of the reference signal (synchronization source) excluding watt hour WP and ampere hour q during DC mode. Timing of Data update is different (minimum time resolution is 50 ms) among elements with different reference signals (synch sources) setting when the Data update interval is set to Auto. Timeout period can be selected from 1 s, 5 s, 10 s or 20 s. And full period of timeout becomes actual measurement period when synchronization source signal does not input any cycles during the timeout period.
- Harmonic display

The measurement period is from the beginning of the data update interval to 1024 or 8192 points at the harmonic sampling frequency.

Measurement period detection method

Analog signal zero cross detection method when Data update interval is set to other than Auto. In case of sampling data level detection method when Data update interval is set to Auto, data level can be set arbitrarily.

1P2W (single-phase, two-wire), 1P3W (single-phase, 3-wire), 3P3W (3-phase, 3-wire), 3P4W (3-phase, 4-wire), 3P3W (3V3A) (3-phase, 3-wire, 3-volt/3-amp measurement) However, the number of available wiring systems varies depending on the number of installed input elements.

Scaling When inputting output from external current sensors, VT, or CT, set the current sensor conversion ratio, VT ratio, CT ratio, and power coefficient in the range from 0.0001 to 99999,9999

CT ratio can be set automatically by selecting a model name of CT series. Current sensor conversion ratio can be set automatically by selecting a model name of dedicated shunt

- The average calculations below are performed on the normal measurement parameters of voltage U, current I, power P, apparent power S, and reactive power Q. Power factor λ and phase angle are determined by calculating the average of P and S.

 Select exponential or moving averaging.
 Exponential average: Select an attenuation constant from 2 through 64. Moving average: Select the number of averages from 8 through 64

Harmonic measurement

Only exponential averaging is available.

Data update interval

Select 50 ms, 100 ms, 200 ms, 500 ms, 1 s, 2 s, 5 s, 10 s, 20 s, or Auto.

Period detection method is different depending on update interval.

50 ms, 100 ms, 200 ms, 500 ms, 1 s, 2 s, 5 s, 10 s, 20 s: Analog signal zero cross detection method

Auto: Sampling data level detection method

Response time

At maximum, twice the data update interval (only during numerical display) When Data update interval is set to Auto, response time is signal cycle period and added 50 ms.

Holds the data display. Hold

Single Executes a single measurement during measurement hold.

When the Data update interval is set to Auto, single mesurement cannot be excuted

Zero level compensation/Null

Compensates the zero level. Null compensation range: ±10% of range Null can be set individually for each of the following input signals

- Voltage and current of each input element
- · Rotation speed and torque
- AUX1 and AUX2

Frequency Measurement

Number of measurement

The frequencies of voltages and currents for all input elements can

Reciprocal method Measurement method

Measurement range

Data update rate	Measuring range
50 ms	45 Hz ≤ f ≤ 1 MHz
100 ms	25 Hz ≤ f ≤ 1 MHz
200 ms	12.5 Hz ≤ f ≤ 500 kHz
500 ms	5 Hz ≤ f ≤ 200 kHz
1 s	2.5 Hz ≤ f ≤ 100 kHz
2 s	1.25 Hz ≤ f ≤ 50 kHz
5 s	0.5 Hz ≤ f ≤ 20 kHz
10 s	0.25 Hz ≤ f ≤ 10 kHz
20 s	0.15 Hz ≤ f ≤ 5 kHz
Auto	0.1 Hz < f ≤ 500 kHz

+0.06% of reading +0.1 mHz

When the input signal level is 30% or more of the measurement range

(60% or more for Crest factor CF6/CF6A)

• The input signal is 50% or more of the range.

The frequency is smaller or equal to 2 times of above lower frequency 10 mA range setting of 5 A input element

1 A range setting of 50 A input element

• When the Data update interval is set to other than Auto, the 100 Hz frequency filter is ON at 0.15 Hz to 100 Hz, and the 1 kHz frequency filter is ON at 100 Hz to 1 kHz.

• When the Data update interval is set to Auto, 100 Hz cutoff frequency filter is set to ON for 0.1 Hz to 100 Hz, and 1.6 kHz cutoff frequency filter is set to ON for 100 Hz to 1 kHz.

Display resolution 99999 Minimum frequency resolution 0.0001 Hz

Frequency measurement filter (the Data update interval is set to other than Auto) Select from OFF, 100 Hz or 1 kHz

(the Data update interval is set to Auto) Select from OFF, 100 Hz, 200 Hz, 400 Hz, 800 Hz, 1.6 kHz, 3.2 kHz, 6.4 kHz, 12.8 kHz or 25.6 kHz.

Integration Mode

Select a mode from Manual, Standard, Continuous (repeat), Real Time Control Standard, and Real Time Control Continuous (Repeat).

"When Data update interval is set to Auto, integration will executes in Manual mode and timer mode only. Other Integration modes like Continuous, Real Time Control Standard and Real Time Control Continuous are not supported.

Integration timer

Integration can be stopped automatically using the timer setting. 0000h00m00s to 10000h00m00s

If the integration time reaches the maximum integration time (10000 hours), or if the integration value reaches maximum/minimum display integration value ¹, the elapsed time and integration value is saved and the operation is stopped.

*1: WP: +999999 MWh q: ±999999 MAh WS: ±999999 MVAh WQ: ±999999 Mvarh

• Integration Resume Action after Recovery of Power Failure Even if a case of power supply loss due to instantaneous power failure while integration, integration can be continued after the recovery. When Data update interval is set to Auto, this feature is no supported. Integration state always becomes to "Error" after the recovery, and it does not continue the integration process.

Auto range Voltage and Current: Available (When the Data Update Interval is set to other than

- . Motor Inputs and Auxiliary Inputs: Not available
- When Element Independent is set to ON: Not available
- When S and Q Formula are set to Type 3: Not available

Accuracy ±(Normal measurement accuracy + 0.02% of reading)

Timer ±0.02% of reading

accuracy	
Measured source	urement (/G5, /G6 Option) All installed elements
Method	PLL synchronization method (without external sampling clock function)
Frequency range	When the Data update interval is set to other than Auto, or when the Data update interval is set to Auto and FFT data length is set to 8192, Fundamental frequency of the PLL source is in the range of 0.5 Hz to 2.6 kHz. When the Data update interval is set to Auto and FFT data length is set to 1024, Fundamental frequency of the PLL source is in the range of 0.1 Hz to 2.6 kHz.
PLL source	Select the voltage or current of each input element or the external clock. If the /G6 option is selected and if the Data update interval is set to other than Auto, two PLL sources can be selected, and dual harmonic measurement can be performed. If the /G5 option is selected, one PLL source is selectable. Input level 15 V or more of range for voltage input. 50 mA or more of range for direct current input. 200 mV or more of range for external current sensor input. 50% or more of the measurement range rating for crest factor CF3. 100% or more of the measurement range rating for crest factor CF6/CF6A. 20 Hz to 1 kHz for the 1 A or 2 A range of the 50 A input element. The frequency filter ON condition is the same as with frequency measurement.
FFT data length	1024 when the data update rate is 50 ms, 100 ms, or 200 ms 8192 when the data update rate is 500 ms, 1 s, 2 s, 5 s, 10 s, or 20 s Select from 1024 or 8192 when the Data update interval is set to Auto
Window function	Rectangular
Anti-aliasing filter	Set using a line filter

Sample rate, window width, and upper limit of the measured order

1024 FFT points (data update interval 50 ms. 100 ms. 200 ms)

		Window	Upper limit of measured order		
Fundamental frequency	Sampling rate	width	U, I, P, Ø, ØU, ØI	Other measured values	
15 Hz to 600 Hz	f × 1024	1	500	100	
600 Hz to 1200 Hz	f × 512	2	255	100	
1200 Hz to 2600 Hz	f × 256	4	100	100	

However, the maximum measured order is 100 at a date update rate of 50 ms.

8192 FFT points (data update interval 500 ms, 1 s, 2 s, 5 s, 10 s, 20 s)

		Window	Upper limit of measured order		
Fundamental frequency	Sampling rate	width	U, I, P, Ø, ØU, ØI	Other measured values	
0.5 Hz to 1.5 Hz	f × 8192	1	500	100	
1.5 Hz to 5Hz	f × 4096	2	500	100	
5 Hz to 10 Hz	f × 2048	4	500	100	
10 Hz to 600 Hz	f × 1024	8	500	100	
600 Hz to 1200 Hz	f × 512	16	255	100	
1200 Hz to 2600 Hz	f × 256	32	100	100	

FFT points 1024 (Data update interval Auto)

TT points Total (batta apatato interval / tato)						
		Window	Upper limit of measured order			
Fundamental frequency	Sampling rate	width	U, I, P, f, fU, fl	Other measured values		
0.1 Hz to 75 Hz	f × 1024	1	100	100		
75 Hz to 600 Hz	f × 1024	1	100	100		
600 Hz to 1200 Hz	f × 512	2	100	100		
1200 Hz to 2600 Hz	f × 256	4	100	100		

FFT points 8192 (Data update interval Auto)

TT points of the Character interval Auto)						
		Window	Upper limit of measured order			
Fundamental frequency	Sampling rate width		U, I, P, f, fU, fl	Other measured values		
0.5 Hz to 75 Hz	f × 1024	8	100	100		
75 Hz to 600 Hz	f × 1024	8	100	100		
600 Hz to 1200 Hz	f × 512	16	100	100		
1200 Hz to 2600 Hz	f × 256	32	100	100		

Accuracy

Add the following accuracy to the normal measurement accuracy.

When the line filter is set to OFF and Update interval is set to other than Auto

Frequency	Voltage	Current	Power
0.5 Hz ≤ f < 10 Hz	±(0.05% of reading	±(0.05% of reading	±(0.1% of reading
	+0.25% of range)	+0.25% of range)	+0.5% of range)
10 Hz ≤ f < 45 Hz	±(0.05% of reading	±(0.05% of reading	±(0.1% of reading
	+0.25% of range)	+0.25% of range)	+0.5% of range)
45 Hz ≤ f ≤ 66 Hz	±(0.05% of reading	±(0.05% of reading	±(0.1% of reading
	+0.25% of range)	+0.25% of range)	+0.5% of range)
66 Hz < f ≤ 440 Hz	±(0.05% of reading	±(0.05% of reading	±(0.1% of reading
	+0.25% of range)	+0.25% of range)	+0.5% of range)
440 Hz < f ≤ 1 kHz	±(0.05% of reading	±(0.05% of reading	±(0.1% of reading
	+0.25% of range)	+0.25% of range)	+0.5% of range)
1 kHz < f ≤ 10 kHz	±(0.5% of reading	±(0.5% of reading	±(1% of reading
	+0.25% of range)	+0.25% of range)	+0.5% of range)
10 kHz < f ≤ 100 kHz	±0.5% of range	±0.5% of range	±1% of range
100 kHz < f ≤ 260 kHz	±1% of range	±1% of range	±2% of range

• When the line filter is set to OFF and update interval is set to Auto

Frequency	Voltage	Current	Power
0.1 Hz ≤ f < 10 Hz	±(0.05% of reading	±(0.05% of reading	±(0.1% of reading
	+0.25% of range)	+0.25% of range)	+0.5% of range)
10 Hz ≤ f < 45 Hz	±(0.05% of reading	±(0.05% of reading	±(0.1% of reading
	+0.25% of range)	+0.25% of range)	+0.5% of range)
45 Hz ≤ f ≤ 66 Hz	±(0.05% of reading	±(0.05% of reading	±(0.1% of reading
	+0.25% of range)	+0.25% of range)	+0.5% of range)
66 Hz < f ≤ 440 Hz	±(0.05% of reading	±(0.05% of reading	±(0.1% of reading
	+0.25% of range)	+0.25% of range)	+0.5% of range)
440 Hz < f ≤ 1 kHz	±(0.05% of reading	±(0.05% of reading	±(0.1% of reading
	+0.25% of range)	+0.25% of range)	+0.5% of range)
1 kHz < f ≤ 10 kHz	±(0.5% of reading	±(0.5% of range	±(1% of reading
	+0.25% of range)	0.25% of range)	+0.5% of range)
10 kHz < f ≤ 100 kHz	±0.5% of range	±0.5% of range	±1% of range
100 kHz < f ≤ 260 kHz	±1% of range	±1% of range	±2% of range

When the line filter is ON

Add the accuracy of the line filter to the accuracy of when the line filter is OFF All the items below apply to any of the tables.

- When the Crest factor is set to CF3.
- When λ (power factor) = 1
- Power figures that exceed 2.6 kHz are reference values.
 For the voltage range, add the following values.

Voltage accuracy: $\pm 25\,\text{mV}$ Power accuracy: $\pm [(25\,\text{mV/voltage range rating}) \times 100\%\,\text{of range}]$

 For the direct current input range, add the following values. 5 A element

Current accuracy: $\pm 50~\mu A$ Power accuracy: $\pm [(50~\mu A/current~range~rating) \times 100\%~of~range]$ 50 A element

Current accuracy: ±4 mA

Power accuracy: ±[(4 mA/current range rating) × 100% of range]
• For the external current sensor range, add the following values.

Current accuracy: ±2 mV

Power accuracy: ±[(2 mV/external current sensor range rating) × 100% of range]

• Add ±[(n/500)% of reading] to the nth component of the voltage and current, and add ±[(n/250)% of reading] to the nth component of the power.

Accuracy when the Crest factor CF6/CF6A

Same as when the range is doubled for Crest factor CF3 $\,$

- The guaranteed accuracy range by frequency and voltage/current is the same as the guaranteed range of normal measurement.

 • The adjacent orders of the input order may be affected by the side rope
- Under the condition of Data update interval is set to other than Auto, or Data update interval is set to Auto and PPL points is 8192,
- For n^{ar} order component input when the PLL source frequency is 2 Hz or more, add ±([[n/(m+1)]/50}% of (the n^{ar} order reading)) to the (n+m)^{ar} order and (n-m)^{ar} order of the voltage and current, and add ±([[n/(m+1)]/25]% of (the nth order reading)) to the (n+m)th order and (n-m)th order of the power.
- For n^m order component input when the PLL source frequency is less than 2 Hz, add $\pm (([n/(m+1)]/20)\%)$ of (the n^m order reading)) to the $(n+m)^m$ order and $(n-m)^m$ order of the voltage and current, and add $\pm (\{[n/(m+1)]/10\}\%)$ of (the n^m order reading)) to the $(n+m)^m$ order and $(n-m)^m$ order of the power.
- Under the condition of Data update interval is set to Auto and PPL points is 1024.
 For nth order component input when the PLL source frequency is 75 Hz or more,
- add $\pm ([[n/(m+1)]/50])\%$ of (the nth order reading)) to the $(n+m)^m$ order and $(n-m)^m$ order of the voltage and current, and add $\pm ([[n/(m+1)]/25])\%$ of (the nth order reading)) to the $(n+m)^m$ order and (n-m)th order of the power.

For nth order component input when the PLL source frequency is less than 75 Hz, add $\pm ([[n/(m+1)]/10]\%$ of (the nth order reading)) to the $(n+m)^{th}$ order and $(n-m)^{th}$ order of the voltage and current, and add $\pm ([[n/(m+1)]/5]\%$ of (the nth order reading)) to the $(n+m)^{th}$ order and $(n-m)^{th}$ order of the power.

High Speed Data Capturing Function

Save setting information, waveform display data, numerical data, and screen image data

Read the saved setting information from media.

Motor Evaluation Function (/MTR Option)

Efficiency calculation

User-defined event

Up to 4 efficiencies can be displayed by setting measurement parameters

The functions triggered by the event are Auto Print, Store, and DA Output.

for the efficiency equations.

Event: Set conditions for measured values.

Input resistance	at range at range at range if liter if lit	1 V, 2 V, 5 V, 10 V, 20 V ±110% OFF, 100, 1 kHz ±22 V ±42 Vpeak Approximately 200 kS/s 16-bit ±(0.03% of reading + 0.03% of range) ±0.03% of range/*C terminal if the direction is not detected. If the e A and B phases of the rotary encoder are input s. The Z phase is input to the Z terminal of the rice angle measurement. ±12 Vpeak 2 Hz to 1 MHz ±42 Vpeak ±(0.03 + f/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + f/500)% of reading ±1 mHz The unit of f is kHz. ut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Cycle of data captur Data update rate Meas. parameter Wiring Line Filter Data output Data measured time Data capturing start Trigger HS filter Display Numerical Display Display digit (display items Waveform Display Display format Sampling rate Time axis	1 ms to 100 n signal from Mil 1 s (It displays Voltage, Curre Torque and sp 'select voltage/c Single phase 2 4 wire Always ON (C selected.) Internal RAM PC through G (Every 1 s data 1 to 10000000 Turn on STAR received I/F c Mode: AUTO/ Slope: Rising OFF, ON (Cut ay resolution) less than 6000 6000 or more Select 4, 8, 16 and Custom Peak-to-peak If the time axis	Is (When External Sync EAS START terminal) the last numeric data d nt., Power for each elemed /Pm (/MTR), AUX1 urrent measurement mode wire (DC signal), Three at off frequency is 300 k approximately 30 MB), eapproximately 30 MB), eapproximately 30 MB), or infinite If key of HS Setting merommand NORMAL/OFF, Source: adde/Falling Edge/both off: 1 Hz to 1000 Hz, 1 light of the start of the sta	uring the 1 s perionent and \$\S^* and AUX2 (/AUX) from DC /RMS /ME or phase 3 wire (3V3). The standard lower of the standard lower low	AN /R-MEAN
Input connector type Analog Input (Speed is input to the A terminal) A terminal) Pulse Input (TORQUE, SPEED) Pulse Input (TORQUE, SPEED) Pulse Input (TORQUE, SPEED) Pulse Input (TORQUE, SPEED) Accurate to the rotary Input (Frequess Maximode Accurate Maximode Accurate Input (Totary Input	alated BNC ge at range filter filt	±110% OFF, 100, 1 kHz ±22 V ±42 Vpeak Approximately 200 kS/s 16-bit ±(0.03% of reading + 0.03% of range) ±0.03% of range/°C terminal if the direction is not detected. If the e A and B phases of the rotary encoder are input s. The Z phase is input to the Z terminal of the ric angle measurement. ±12 Vpeak 2 Hz to 1 MHz ±42 Vpeak ±(0.03 + t/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + t/500)% of reading ±1 mHz The unit of f is kHz. uut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Meas. parameter Wiring Line Filter Data output Data measured time Data capturing start Trigger HS filter Display Numerical Display Display digit (display items) Waveform Display Display format	signal from Mi 1 s (It displays Voltage, Curre Torque and sp. *select voltage/C Single phase 2 4 wire Always ON (C selected.) Internal RAM I PC through G (Every 1 s date 1 to 1000000 Turn on STAR received VF c Mode: AUTO/ Slope: Rising OFF, ON (Cut ay resolution) less than 6000 6000 or more Select 4, 8, 16 and Custom Peak-to-peak If the time axis part lacking di	EAS START terminal) the last numeric data d nt, Power for each elem ead /Pm (/MTR), AUX1 urrent measurement mode 2 wire (DC signal), Three ut off frequency is 300 k approximately 30 MB), e approxima	uring the 1 s perionent and \$\S^* and AUX2 (/AUX) from DC /RMS /ME or phase 3 wire (3V3). The standard lower of the standard lower low	AN /R-MEAN
Analog Input (Speed is input to the A terminal) A terminal) Input Line f Continuous maximum allowable input Range [Input (Continuous maximum allowable input to the Continuous maximum allowable input [Input terminal AUX [Input type Anal Input type Anal Input trange ±22] [Input type Anal Input (AUX OFFICE Analogs Speedings of the Continuous maximum allowable input terminal 422]	ge It range If the range If	±110% OFF, 100, 1 kHz ±22 V ±42 Vpeak Approximately 200 kS/s 16-bit ±(0.03% of reading + 0.03% of range) ±0.03% of range/°C terminal if the direction is not detected. If the e A and B phases of the rotary encoder are input s. The Z phase is input to the Z terminal of the ric angle measurement. ±12 Vpeak 2 Hz to 1 MHz ±42 Vpeak ±(0.03 + t/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + t/500)% of reading ±1 mHz The unit of f is kHz. uut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Meas. parameter Wiring Line Filter Data output Data measured time Data capturing start Trigger HS filter Display Numerical Display Display digit (display items) Waveform Display Display format	1 s (It displays Voltage, Curre Torque and sp 'select voltage/C Single phase 2 4 wire Always ON (C selected.) Internal RAM I PC through G (Every 1 s date 1 to 1000000 Turn on STAR received I/F c Mode: AUTO/Slope: Rising OFF, ON (Cut ay resolution) less than 6000 6000 or more Select 4, 8, 16 and Custom Peak-to-peak If the time axis part lacking di	the last numeric data d nt, Power for each elem eed /Pm (/MTR), AUX1 urrent measurement mode wire (DC signal), Three ut off frequency is 300 k approximately 30 MB), e P-IB, Ethernet of USB or a block continuously) o, or infinite T key of HS Setting mer ommand NORMAL/OFF, Source: edge/Falling Edge/both off: 1 Hz to 1000 Hz, 1 I 00: 5 digits 4 digits 6, Matrix, ALL, Harmonic	nent and Σ* and AUX2 (/AUX) from DC /RMS /ME phase 3 wire (3V3 tHz and lower. 1 M external USB stora ommunication I/F in u Satisfy trigger co. U1 to U6/I1 to I6/ledges, Level: ±100 Hz unit setting)	AN /R-MEAN 3A), Three phase IHz cannot be ige onditions after EXT, 0.0%
(Speed is input to the A terminal) Input Line filter OFF Contiallow Maxir mode Samp. Resol Accur Temp Pulse Input (TORQUE, SPEED) Pulse Input (TORQUE, SPEED) Fall o Detect Pulse Harms measu Auxiliary Input (/AUX Option Input terminal AUX Input type Anal Input resistance App Input connector type Insu Range 50 in Input range ±111 Line filter OFF Continuous maximum allowable input terminal tine for the continuous maximum allowable input terminal tine filter OFF Continuous maximum allowable input terminal tine filter OFF Continuous maximum allowable input terminal tine filter tine filter OFF Continuous maximum allowable input tine filter tine filter tine filter tine filter OFF Continuous maximum allowable input tine filter tine filter tine filter OFF Continuous maximum allowable input tine filter tine	at range at range at range if liter if lit	±110% OFF, 100, 1 kHz ±22 V ±42 Vpeak Approximately 200 kS/s 16-bit ±(0.03% of reading + 0.03% of range) ±0.03% of range/°C terminal if the direction is not detected. If the e A and B phases of the rotary encoder are input s. The Z phase is input to the Z terminal of the ric angle measurement. ±12 Vpeak 2 Hz to 1 MHz ±42 Vpeak ±(0.03 + t/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + t/500)% of reading ±1 mHz The unit of f is kHz. uut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Meas. parameter Wiring Line Filter Data output Data measured time Data capturing start Trigger HS filter Display Numerical Display Display digit (display items) Waveform Display Display format	Voltage, Curre Torque and sp 'select voltage/C Single phase 2 4 wire Always ON (C selected.) Internal RAM I PC through G (Every 1 s date 1 to 1000000 Turn on STAR received I/F c Mode: AUTO/Slope: Rising OFF, ON (Cut ay resolution) less than 6000 6000 or more Select 4, 8, 16 and Custom Peak-to-peak If the time axis part lacking de	nt, Power for each elemed /Pm (/MTR), AUX1 urrent measurement mode wire (DC signal), Three ut off frequency is 300 k approximately 30 MB), e P-IB, Ethernet of USB or a block continuously) o, or infinite F key of HS Setting merommand NORMAL/OFF, Source: adge/Falling Edge/both off: 1 Hz to 1000 Hz, 1 I 00: 5 digits 4 digits 6, Matrix, ALL, Harmonic	nent and Σ* and AUX2 (/AUX) from DC /RMS /ME phase 3 wire (3V3 tHz and lower. 1 M external USB stora ommunication I/F in u Satisfy trigger co. U1 to U6/I1 to I6/ledges, Level: ±100 Hz unit setting)	AN /R-MEAN 3A), Three phase IHz cannot be ige onditions after EXT, 0.0%
A terminal) Line f Continuous maximum allowable input Line f Continual Line f Continual Auxiliary Input Line f Continuous maximum allowable input Line f Continual Line f Line f Continual Line f Line f Line f Continual Line f Line f Line f Continual Line f Line	in filter in filter intinuous maximum wable input kimum common de voltage inpling rate inpline rate inpling rate inpline rate inpling rate inpline rate inpline rate inpline rate inpline rate inpling rate inpline rate inplin	OFF, 100, 1 kHz ±22 V ±42 Vpeak Approximately 200 kS/s 16-bit ±(0.03% of reading + 0.03% of range) ±0.03% of range/°C terminal if the direction is not detected. If the e A and B phases of the rotary encoder are input s. The Z phase is input to the Z terminal of the ric angle measurement. ±12 Vpeak 2 Hz to 1 MHz ±42 Vpeak ±(0.03 + t/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + t/500)% of reading ±1 mHz The unit of f is kHz. uut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Line Filter Data output Data measured time Data capturing start Trigger HS filter Display Numerical Display Display digit (display items) Waveform Display Display format	Torque and sp *select voltage/e Single phase 2 4 wire Always ON (C selected.) Internal RAM I PC through G (Every 1 s date 1 to 1000000 Turn on STAR received I/F o Mode: AUTO/ Slope: Rising OFF, ON (Cut ay resolution) less than 6000 6000 or more Select 4, 8, 16 and Custom Peak-to-peak If the time axis part lacking di	eed /Pm (/MTR), AUX1 current measurement mode wire (DC signal), Three ut off frequency is 300 k approximately 30 MB), e p-IB, Ethernet of USB ca a block continuously) o, or infinite r key of HS Setting mer ommand NORMAL/OFF, Source: adge/Falling Edge/both off: 1 Hz to 1000 Hz, 1 l 00: 5 digits 4 digits 6, Matrix, ALL, Harmonic	and AUX2 (/AUX) If from DC /RMS /ME IP phase 3 wire (3V3 IHz and lower. 1 M External USB stora ommunication I/F In u Satisfy trigger co U1 to U6/I1 to I6/I edges, Level: ±100 Hz unit setting)	3A), Three phase IHz cannot be age onditions after EXT, 0.0%
Auxiliary Input (/AUX Option Input terminal AUX Input type Anal Input tresistance App Input connector type Insu Range 50 n Input trange ±11 Line filter OFF Continuous maximum allowable input terminal allowable input terminal allowable input terminal ±22 allowable input terminal te	ntinuous maximum wable input kimum common de voltage input voltage inpling rate inp	±22 V ±42 Vpeak Approximately 200 kS/s 16-bit ±(0.03% of reading + 0.03% of range) ±0.03% of range/°C terminal if the direction is not detected. If the e A and B phases of the rotary encoder are input s. The Z phase is input to the Z terminal of the ric angle measurement. ±12 Vpeak 2 Hz to 1 MHz ±42 Vpeak ±(0.03 + t/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + t/500)% of reading ±1 mHz The unit of f is kHz. uut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Line Filter Data output Data measured time Data capturing start Trigger HS filter Display Numerical Display Display digit (display items) Waveform Display Display format Sampling rate	Single phase 2 4 wire Always ON (C selected.) Internal RAM PC through G (Every 1 s date 1 to 1000000 Turn on STAR received I/F c Mode: AUTO/ Slope: Rising OFF, ON (Cut ay resolution) less than 6000 6000 or more Select 4, 8, 16 and Custom Peak-to-peak If the time axis part lacking di	wire (DC signal), Three thought off frequency is 300 k approximately 30 MB), e P-IB, Ethernet of USB or a block continuously) or, or infinite Fixey of HS Setting merormand NORMAL/OFF, Source: adge/Falling Edge/both off: 1 Hz to 1000 Hz, 1 k 00: 5 digits 4 digits 6, Matrix, ALL, Harmonic	that and lower. 1 M external USB stora ommunication I/F mu Satisfy trigger or U1 to U6/I1 to I6/ledges, Level: ±100 Hz unit setting)	3A), Three phase IHz cannot be age onditions after EXT, 0.0%
Maximode Samp Resol Accur Temp Pulse Input (TORQUE, SPEED) See direct to the rotary Input (Frequeness Maximode Accur Fall of Detect Pulse Harmoness Maximode Input terminal AUX Input type Anal Input tresistance App Input connector type Insu Range 50 nr Input range ±111 Line filter OFF Continuous maximum allowable input accurate the same seems of the sam	dinum common de voltage inpling rate ollution uracy inperature coefficient sed is input to the Action is detected, the A and B terminal ry encoder for elect at range guency assurement range dinum common de voltage uracy of the Z terminal inpection level se width monic measurement of surement.	Approximately 200 kS/s 16-bit ±(0.03% of reading + 0.03% of range) ±0.03% of range/°C terminal if the direction is not detected. If the e A and B phases of the rotary encoder are input s. The Z phase is input to the Z terminal of the ric angle measurement. ±12 Vpeak 2 Hz to 1 MHz ±42 Vpeak ±(0.03 + f/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + f/500)% of reading ±1 mHz The unit of f is kHz. ut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Data output Data measured time Data capturing start Trigger HS filter Display Numerical Display Display digit (display items) Waveform Display Display format Sampling rate	selected.) Internal RAM I PC through G (Every 1 s date 1 to 10000001 Turn on STAR received I/F or Mode: AUTO/ Slope: Rising OFF, ON (Cut ay resolution) less than 6006 6000 or more. Select 4, 8, 16 and Custom Peak-to-peak If the time axis part lacking di	approximately 30 MB), e 2-IB, Ethernet of USB c a block continuously) 30, or infinite F key of HS Setting mer ommand NORMAL/OFF, Source: adge/Falling Edge/both off: 1 Hz to 1000 Hz, 1 I 00: 5 digits 4 digits 6, Matrix, ALL, Harmonic	external USB stora ommunication I/F nu Satisfy trigger co U1 to U6/I1 to I6/ edges, Level: ±100 Hz unit setting)	onditions after EXT, 0.0%
Samp	ppling rate colution uracy sperature coefficient ted is input to the A ction is detected, the ne A and B terminal ry encoder for elect at range quency asurement range dimum common de voltage uracy of the Z terminal input ection level se width monic measurement of surement.	16-bit ±(0.03% of reading + 0.03% of range) ±0.03% of range/°C terminal if the direction is not detected. If the e A and B phases of the rotary encoder are input s. The Z phase is input to the Z terminal of the ric angle measurement. ±12 Vpeak 2 Hz to 1 MHz ±42 Vpeak ±(0.03 + f/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + f/500)% of reading ±1 mHz The unit of f is kHz. Jut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Data measured time Data capturing start Trigger HS filter Display Numerical Display Display digit (display items Waveform Display Display format Sampling rate	PC through G (Every 1 s data 1 to 10000001 Turn on STAR received I/F or Mode: AUTO/ Slope: Rising OFF, ON (Cut ay resolution) less than 6000 6000 or more Select 4, 8, 16 and Custom Peak-to-peak If the time axis part lacking data	P-IB, Ethernet of USB of a block continuously) 0, or infinite 1, rkey of HS Setting merormand NORMAL/OFF, Source: edge/Falling Edge/both off: 1 Hz to 1000 Hz, 1 If 100: 5 digits 4 digits 5, Matrix, ALL, Harmonic	ommunication I/F nu Satisfy trigger co U1 to U6/I1 to I6/i edges, Level: ±100 Hz unit setting)	ext, 0.0%
Pulse Input (TORQUE, SPEED) Pulse Input (TORQUE, SPEED) Pulse Input (Input Input I	uracy sperature coefficient sed is input to the A ction is detected, the A and B terminal ry encoder for elect at range quency asurement range dimum common de voltage uracy of the Z terminal ing ection level se width monic measurement of surement.	±(0.03% of reading + 0.03% of range) ±0.03% of range/**C terminal if the direction is not detected. If the e A and B phases of the rotary encoder are input s. The Z phase is input to the Z terminal of the ric angle measurement. ±12 Vpeak 2 Hz to 1 MHz ±42 Vpeak ±(0.03 + f/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + f/500)% of reading ±1 mHz The unit of f is kHz. Jut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Trigger HS filter Display Numerical Display Display digit (display items) Waveform Display Display format	1 to 1000000 Turn on STAR received VF of Mode: AUTO/ Slope: Rising OFF, ON (Cut ay resolution) less than 6006 6000 or more Select 4, 8, 16 and Custom Peak-to-peak If the time axis part lacking di	o), or infinite If key of HS Setting merommand NORMAL/OFF, Source: adge/Falling Edge/both off: 1 Hz to 1000 Hz, 1 Hz 100: 5 digits 4 digits 6, Matrix, ALL, Harmonic	U1 to U6/I1 to I6// edges, Level: ±10(Hz unit setting)	EXT, 0.0%
Temp Pulse Input (TORQUE, SPEED)	sperature coefficient sed is input to the A ction is detected, the A and B terminal ry encoder for elect at range quency asurement range dimum common de voltage uracy of the Z terminal inguection level se width monic measurement of surement.	±0.03% of range/°C terminal if the direction is not detected. If the e A and B phases of the rotary encoder are input s. The Z phase is input to the Z terminal of the ric angle measurement. ±12 Vpeak 2 Hz to 1 MHz ±42 Vpeak ±(0.03 + f/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + f/500)% of reading ±1 mHz The unit of f is kHz. Jut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Trigger HS filter Display Numerical Display Display digit (display items) Waveform Display Display format	Turn on STAR received I/F or Mode: AUTO/ Slope: Rising OFF, ON (Cut are resolution) less than 6006 6000 or more. Select 4, 8, 16 and Custom Peak-to-peak If the time axis part lacking driven are received.	F key of HS Setting merommand NORMAL/OFF, Source: adge/Falling Edge/both off: 1 Hz to 1000 Hz, 1 Hz to 1000	U1 to U6/I1 to I6// edges, Level: ±10(Hz unit setting)	EXT, 0.0%
Pulse Input (TORQUE, SPEED)	ted is input to the A ction is detected, the A and B terminal ry encoder for elect at range quency asurement range dimum common de voltage uracy of the Z terminal input ection level se width monic measurement of surement.	terminal if the direction is not detected. If the e A and B phases of the rotary encoder are input s. The Z phase is input to the Z terminal of the ric angle measurement. ±12 Vpeak 2 Hz to 1 MHz ±42 Vpeak ±(0.03 + f/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + f/500)% of reading ±1 mHz The unit of f is kHz. Just and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Trigger HS filter Display Numerical Display Display digit (display items) Waveform Display Display format Sampling rate	received VF of Mode: AUTO/ Slope: Rising OFF, ON (Cut of Mode) ay resolution) less than 6006 6000 or more of Mode) and Custom Peak-to-peak If the time axis part lacking did	ommand NORMAL/OFF, Source: adge/Falling Edge/both off: 1 Hz to 1000 Hz, 1 Hz 100: 5 digits 4 digits 5, Matrix, ALL, Harmonic	U1 to U6/I1 to I6// edges, Level: ±10(Hz unit setting)	EXT, 0.0%
Auxiliary Input (/AUX Option Input terminal AUX Input type Anal Input type Anal Input type Anal Input connector type Insu Range 50 nr Input tine filter OFF Continuous maximum allowable input discharge for to the the rotary in the rotary input type Anal Input connector type Insu Range 50 nr Input type Anal Input connector type Insu Range 50 nr Input type Anal Input type Anal Input type Anal Input connector type Insu Range 50 nr Input type Anal Input type An	ction is detected, the A and B terminal ry encoder for elect at range quency assurement range dimum common de voltage uracy of the Z terminal inguection level se width monic measurement of surement.	e A and B phases of the rotary encoder are input s. The Z phase is input to the Z terminal of the ric angle measurement. ±12 Vpeak ±42 Vpeak ±42 Vpeak ±(0.03 + f/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + f/500)% of reading ±1 mHz The unit of f is kHz. Jut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	HS filter Display Numerical Display Display digit (displ Number of display items Waveform Display Display format Sampling rate	Mode: AUTO/ Slope: Rising OFF, ON (Cut ay resolution) less than 600 6000 or more Select 4, 8, 16 and Custorn Peak-to-peak If the time axis part lacking di	NORMAL/OFF, Source: edge/Falling Edge/both off: 1 Hz to 1000 Hz, 1 l off: 5 digits 4 digits 5, Matrix, ALL, Harmonic	edges, Level: ±100	0.0%
Auxiliary Input (/AUX Option Input terminal AUX Input type Anal Input resistance App Input connector type Insu Range 50 n Input range ±111 Line filter OFF Continuous maximum allowable input	at range quency asurement range dimum common de voltage uracy of the Z terminal inpection level se width monic measurement of surement.	±12 Vpeak 2 Hz to 1 MHz ±42 Vpeak ±(0.03 + f/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + f/500)% of reading ±1 mHz The unit of f is kHz. July and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Numerical Display Display digit (display digit (display items Waveform Display Display format Sampling rate	ay resolution) less than 6000 6000 or more Select 4, 8, 16 and Custom Peak-to-peak If the time axis part lacking di	00: 5 digits 4 digits 5, Matrix, ALL, Harmonic	-	onic Dual List,
Maxir mode Accur	asurement range kimum common de voltage uracy of the Z terminal ing ection level se width monic measurement of surement.	±42 Vpeak ±(0.03 + f/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + f/500)% of reading ±1 mHz The unit of f is kHz. ut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Numerical Display Display digit (display In the second of	less than 6000 6000 or more Select 4, 8, 10 and Custom Peak-to-peak If the time axis part lacking da	4 digits 6, Matrix, ALL, Harmonic	c Single List, Harm	onic Dual List,
Auxiliary Input (/AUX Option Input terminal AUX Input type Anal Input resistance App Input connector type Insu Range 50 n Input range ±111 Line filter OFF Continuous maximum allowable input	dimum common de voltage uracy of the Z terminal inpection level se width monic measurement of surement.	±(0.03 + f/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + f/500)% of reading ±1 mHz The unit of f is kHz. Jut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Display digit (display digit (display digit (display items Waveform Display Display format Sampling rate	less than 6000 6000 or more Select 4, 8, 10 and Custom Peak-to-peak If the time axis part lacking da	4 digits 6, Matrix, ALL, Harmonic	c Single List, Harm	onic Dual List,
Mode Accur	de voltage uracy of the Z terminal inpection level se width monic measurement of surement.	±(0.03 + f/10000)% of reading ±1 mHz Accuracy of the waveform display data ±(0.03 + f/500)% of reading ±1 mHz The unit of f is kHz. Jut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Number of display items Waveform Display Display format Sampling rate	less than 6000 6000 or more Select 4, 8, 10 and Custom Peak-to-peak If the time axis part lacking da	4 digits 6, Matrix, ALL, Harmonic	c Single List, Harm	onic Dual List,
Fall of Detection Pulses Harms measured Pulses Harms measured Pulses Harms measured Pulses Harms measured Pulses Harms Manual Input terminal AUX Input type Anal Input resistance App Input connector type Insu Range 50 m Input range ±111 Line filter OFF Continuous maximum allowable input 422	of the Z terminal inpection level se width monic measurement of surement.	Accuracy of the waveform display data ±(0.03 + 1/500)% of reading ±1 mHz The unit of f is kHz. ut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Waveform Display Display format Sampling rate	Select 4, 8, 16 and Custom Peak-to-peak If the time axis part lacking da	5, Matrix, ALL, Harmonic	Single List, Harm	onic Dual List,
Detect	ection level se width monic measurement of surement.	The unit of f is kHz. ut and electric angle measurement start time Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Waveform Display Display format Sampling rate	Peak-to-peak If the time axis part lacking da	compression data		
Detect	ection level se width monic measurement of surement.	Within 500 ns H level: Approximately 2 V or more L level: Approximately 0.8 V or less 500 ns or more	Display format Sampling rate	If the time axis part lacking da	compression data		
Pulse	se width monic measurement of surement.	L level: Approximately 0.8 V or less 500 ns or more			is set so that there will		
Auxiliary Input (/AUX Option Input terminal AUX Input type Anal Input resistance App Input connector type Insu Range 50 in Input range ±11i Line filter OFF Continuous maximum allowable input	monic measurement of surement.	500 ns or more			ata is filled with the preci	eding sampling da	ta.
Auxiliary Input (/AUX Option Input terminal AUX Input type Anal Input resistance App Input connector type Insu Range 50 in Input range ±11i Line filter OFF Continuous maximum allowable input	monic measurement of surement.			- '' '	05 ms to 2 s/div. Howe	ver. 1/10 or less of	the data update
Input terminal AUX Input type Anal Input resistance App Input connector type Insu Range 50 n Input range ±11t Line filter OFF Continuous maximum allowable input ±22	•			interval when Range from 0	Data update interval is s 05 ms to 5 ms/div wher	et to other than Au	uto.
Input terminal AUX Input type Anal Input resistance App Input connector type Insu Range 50 n Input range ±11t Line filter OFF Continuous maximum allowable input ±22	•		Triagar	Auto.	Edge type		
Input type Anal Input resistance App Input connector type Insu Range 50 n Input range ±11t Line filter OFF Continuous maximum allowable input	JX1/AUX2		Trigger	Trigger type	Edge type	A Normal Automat	inally turned OFF
Input resistance App Input connector type Insu Range 50 n Input range ±11 Line filter OFF Continuous maximum allowable input ±22				Trigger mode	Select OFF, Auto, and during integration.	i Normai. Automat	.cally turned OFF
Input connector type Insu Range 50 n Input range ±11t Line filter OFF Continuous maximum allowable input ±22	proximately 1 MΩ				Automatically OFF wh	nen the Data updat	e interval is set
Range 50 m Input range ±110 Line filter OFF Continuous maximum allowable input ±22	sulated BNC			Triagar agurag	to Auto.	ont input to the ing	urt alamant ar
Input range ±110 Line filter OFF Continuous maximum allowable input ±22		500 m, 1, 2, 5, 10, 20 V		rrigger source	Select voltage or curre external clock	ent input to the inp	ut element or
Line filter OFF Continuous maximum allowable input		500 HI, 1, 2, 0, 10, 20 V		Trigger slope	Select Rise, Fall, or Ri	ise/Fall	
Continuous maximum ±22 allowable input	F/100 Hz/1 kHz			Trigger Level Set the trigger level in the range of ±100% from the of the screen (from top to bottom of the screen) if trigger source is the voltage or current input to the element.)% from the cent	
Common mode voltage ±42	2 Vpeak				The set resolution is 0		
Sampling rate App	proximately 200 kS	/s			TTL level if the trigger	source is Ext Clk (external clock).
Resolution 16-b	-bit		Time axis zoom function	Not available			
Add		change in temperature after zero level			at up to approximately 100) kHz because the sa	.mpling rate is
	mpensation or rang	e change.	Data Store Function	1			
Temperature coefficient ±0.0	.03% of range/ C				n media. (Media: USB st	torage device, max	kimum 1 GB)
DA Output and Remote Con	ntrol (/DA Option)				n display is OFF) to 99 h		
DA Output	10 50				ry (Numerical Store an		
D/A conversion resolution		7510	Number of	Number o	measurement items	Storage interval	Storable time
		n approximately ±7.5 V) relative to each rated value	measurement chann	els (e	ach channel)	-	(Approximately
	Same as the data		3 ch		5	50 ms	5 days
<u> </u>		but parameter can be set for each channel)	3 ch	Each have	20 nic component data of	50 ms	56 hours
	±(Accuracy of eac	th measurement function +0.1% of FS) FS = 5 V	3 ch	DC to the 10	Oth order of voltage,	50 ms	4 hours
Minimum load Temperature coefficient	±0.05% of FS/°C			current, and			
Continuous maximum com			6 ch		5	1 s	86 days
	±42 Vpeak or less		6 ch		20	1 s	24 days
Remote Control Signal		STOP, EXT RESET, INTEG BUSY, EXT HOLD,	6 ch		iic component data 100th order of voltage, power	1 s	40 hours
Input level	EXT SINGLE, EXT	1 I IIIVI	6 ch	of DC to the	ic component data 500th order of voltage,	100 ms	49 minutes
Calculation and Event Funct	0 to 5 V		L	current, and			<u> </u>
User-defined function Comp					the number of store operations time might be shortened		nts.

Save

Read

Auxiliary I/O					
/O Section for Ma Connector type			cation Signals icable to both master and slave		
I/O level	TTL: Applica	able to bot	th master and slave		
Measurement s					
			rvals: Applicable to master ple intervals: Applicable to slave		
External Clock In Common	Connector 1	type	BNC connector		
	Input level		ΠL		
When a synchro	nization source Frequency r		Il measurement is used as the external clock for input Same as the measurement range of frequency measurement.		
	Input wavef	orm	Square waveform with a duty ratio of 50%		
When a PLL so	purce for harm Frequency r		urement is used as the external clock for input Harmonic measurement (/G5 or /G6) option: 0.5 Hz to 2.6 kHz		
	Input wavef	orm	Square waveform with a duty ratio of 50%		
Trigger	Minimum p	ulse width	1 μs		
	Trigger dela	y time	Within (1 µs + 15 sample intervals)		
RGB Output	Connector t	type	D-sub 15-pin (receptacle)		
(Option)	Output form	nat	Analog RGB output		
Computer Interfa GP-IB Interface	ice				
Compatible de	vices	PCI-GFPCIe-GPCMCIGPIB-L	Instruments IPB and PCI-GPIB+ IPIB and PCIe-GPIB+ A-GPIB and PCMCIA-GPIB+ JSB-HS and GPIB-USB-HS+ II-488.2M Version 1.60 or later driver		
Electrical and n	nechanical		s to the IEEE Standard 488-1978 (JIS C 1901-1987)		
Functional spec	cifications	SH1, AH	1, T6, L4, SR1, RL1, PP0, DC1, DT1, C0		
Protocol			s to the IEEE Standard 488.2-1992		
Encoding		ISO (ASC			
Mode		Addressa	able mode		
Address		0 to 30			
Clearing remote	e mode	Remote r	mode can be cleared by pressing the LOCAL key during Local Lockout)		
Ethernet Interface Number of com ports		1			
Connector type	9	RJ-45 cc	onnector		
Electrical and n specifications	nechanical	Conform	s to the IEEE802.3		
Transmission m	nethod	Ethernet	1000BASE-T, 100BASE-TX, 10BASE-T		
Communication	n protocol	TCP/IP			
Applicable serv	rices		er, DHCP, DNS, remote control (VXI-11), SNTP, FTP clien TCP server, Web server		
JSB PC Interface Number of port		1			
Connector		Туре В с	onnector (receptacle)		
Electrical and n specifications	nechanical	Conform	s to the USB Revision 2.0		
Applicable trans	sfer standards		Speed) mode (480 Mbps), Speed) mode (12 Mbps)		
Applicable prot	ocols	USBTMC	C-USB488 (USB Test and Measurement Class Version 1.0		
Applicable syst environment	em		nust run the Japanese or English version of Windows .1/10, and be equipped with a USB port.		
JSB for Peripher	al Devices				
Number of ports	2				
Connector type		A connect	or (receptacle)		
Electrical and me		cifications	5		
Applicable transf					

Paper width	80 mm
Effective recording widt	h 72 mm
Auto Print	Allows you to set the interval time for printing to automatically print the measured values. The start/stop time can also be set.
Current Sensor Power	(/PD2 Option)
Number of channel	6
Connector type	D-sub9 pin (Plug)
Output voltage	±15 V DC
Output current	1.8 A/1 channel
General Specifications	
147	

General Specifications			
Warm-up time	Approximately 30 minutes		
Operation environment	Temperature: 5 to 40°C Humidity: 20 to 80%RH (no condensation)		
Operating altitude	2000 m or less		
Installation location	Indoors		
Storage environment	Temperature: -25 to 60°C Humidity: 20 to 80%RH (no condensation)		
Rated power supply voltage			

100 to 240 VAC Allowable power supply voltage fluctuation range

Rated power supply frequency 50/60 Hz

Allowable power supply frequency fluctuation range 48 to 63 Hz

Maximum power consumption

Weight

150 VA (when using a built-in printer)

450 VA (when using a built-in printer and Current Sensor Power)


Approximately 426 mm (W) \times 177 mm (H) \times 459 mm (D) (Excluding the handle and other projections when the printer is stored in the cover) Dimensions Approximately 426 mm (W) × 221 mm (H) × 459 mm (D) (When the printer cover is not attached; Excluding the handle and other


protruding parts; /PD2 option is mounted.) Approximately 15 kg (including the main body, 6 input elements, and options without /PD2) $\,$ About 17 kg (main body, 6 input elements, and options including /PD2 are mounted)

Battery backup Setting information and built-in clock continue to operate with a lithium backup battery.

*Warning for Class A instruments
This is a Class A instrument based on Emission standards EN61326-1 and EN55011, and is designed for an industrial environment.

Operation of this equipment in a residential area may cause radio interference, in which case users will be responsible for any interference which they cause





Dedicated Cables and Shunt resistor BOXes for /PD2 option







A1589WL



A1628WL

 $5\,\text{V}$, 500 mA (for each port). However, devices that exceed the maximum current consumption of 100 mA cannot be connected to two ports simultaneously.

Available space: 2 TB, Partition format: MBR, Format type: FAT32/FAT16 109 and 104 keyboards conforming to USB HID Class Version 1.1

Built-in Printer (/B5 Option)		
Printing method	Thermal line dot method	
Dot density	8 dots/mm	

Applicable devices Mass storage device conforming to USB Mass Storage Class Version 1.1

Mouse conforming to USB HID Class Version 1.1

Power supply

A1325EZ */EX1 to /EX6 options must be installed in the WT1800E to be able to use of the Shunt Resistor Box.

Accessories

Related products

AC/DC Current Sensor



CT60/CT200/CT1000/CT2000A

AC/DC Current Sensors

- DC to 800 kHz/60 Apeak DC to 500 kHz/200 Apeak DC to 300 kHz/1000 Apeak
- DC to 40 kHz/2000 Arms (3000 Apeak)
- Wide dynamic range –2000 A to 0 A to +2000 A (DC)/2000 Arms (AC) • Wide measurement frequency range: DC and up to 800 kHz
- High-precision fundamental accuracy: ±(0.05% of reading + 30 μA)
- ±15 V DC power supply, connector, and load resistor required. For detailed information, see Current Sensors & Accessories Catalog Bulletin CT1000-00E.

Clamp on Probe



751552

Current Clamp on Probe

- AC 1000 Arms (1400 Apeak)
- Measurement frequency range: 30 Hz to 5 kHz
- Basic accuracy: ±0.3% of reading
- · Maximum allowed input:
- AC 1000 Arms, maximum 1400 Apeak (AC)
- Current output type: 1 mA/A

A separately sold fork terminal adapter set (758921), measurement leads (758917), etc. are required for connection to WT3000E. For detailed information, see Power Meter Accessory Catalog Bulletin CT1000-00E.

Current Sensor Unit



751522, 751524

Current Sensor Unit

Current Output

- DC to 100 kHz/1000 Apeak
- Wide dynamic range: -1000 A to 0 A to +1000 A (DC)/1000 Apeak (AC)
- Wide measurement frequency range: DC to 100 kHz (-3 dB)
- High-precision fundamental accuracy: ±(0.05% of reading + 40 μA)
- Superior noise withstanding ability and CMRR characteristic due to optimized casing design 751522/751524 do not conform to CE Marking

For detailed information, see Power Meter Accessory Catalog Bulletin CT1000-00E.

Adapters and Cables



758917

Measurement leads

Two leads in a set. Use 758917 in combination with 758922 or 758929. Total length: 75 cm Rating: 1000 V, 32 A



758922 Small alligator adapters

For connection to Rating: 300 V



758929

measurement leads (758917).



Large alligator adapters

For connection to measurement leads (758917). Two in a set. Rating: 1000 V



758923*1

Safety terminal adapter set

(spring-hold type) Two adapters in a set



Safety terminal adapter set

Screw-fastened adapters Two adapters in a set 1.5 mm Allen wrench included for tightening.



Current Output

Fork terminal adapter

Two adapters (red and black) in a set. Used when attaching banana plug to binding post.



758924

Conversion adapter

For conversion between male BNC and female banana plug



366924/25*2

BNC cable

(BNC-BNC 1 m/2 m) For simultaneous measurements with 2 units or for an external trigger signal.



B9284LK*3

External Sensor Cable

To connect the external input of the WT1800E to the current sensor Length: 50 cm



761902/03

Safety BNC cable

(BNC-BNC 1 m/2 m) To connect the Motor evaluation function to a torque sensor.




Power meter's current direct input terminal

Due to the nature of this product, it is possible to touch its metal parts. Therefore, there is a risk of electric shock, so the product must be used with caution.


- *1 Maximum diameters of cables that can be connected to the adapters 758923 core diameter: 2.5 mm or less; sheath diameter: 4.8 mm or less 758931 core diameter: 1.8 mm or less; sheath diameter: 3.9 mm or less
- *2 Use with a low-voltage circuit (42 V or less)
- *3 The coax cable is simply cut on the current sensor side. Preparation by the user is required.

Typical Voltage/Current Connections


Measurement using current sensor Connection example



Measurement using clamp-on probe



Measurement using voltage input terminal



^{*}A burden resistor is required for the CT1000, CT200 and CT60

Model and Suffix code

Precision Power Analyzer

Model	Suffix Code	Description	
One input elem	ent model		
WT1801E	-5A0-50A1	50 A × 1 Input Element	
	-5A1-50A0	5 A × 1 Input Element	
Two input elem	ents model	·	
WT1802E	-5A0-50A2	50 A × 2 Input Elements	
	-5A1-50A1	5 A × 1 Input Element	50 A × 1 Input Element
	-5A2-50A0	5 A × 2 Input Elements	
Three input ele			
WT1803E	-5A0-50A3	50 A × 3 Input Elements	
	-5A1-50A2	5 A × 1 Input Element	50 A × 2 Input Elements
	-5A2-50A1	5 A × 2 Input Elements	50 A × 1 Input Element
	-5A3-50A0	5 A × 3 Input Elements	CO TEXT INPUT Element
Four input elem		o / t it o input Elemente	
WT1804E	-5A0-50A4	50 A × 4 Input Elements	
*** 1 100 1L	-5A1-50A3	5 A × 1 Input Element	50 A × 3 Input Elements
	-5A2-50A2	5 A × 2 Input Elements	50 A × 2 Input Elements
	-5A3-50A1	5 A × 3 Input Elements	50 A × 1 Input Element
	-5A4-50A0	5 A × 4 Input Elements	30 A x 1 Input Element
Eivo input olom		3 A × 4 Input Lientents	
Five input elem WT1805E	-5A0-50A5	50 A v 5 Input Flomanta	
VV I 1003E		50 A × 5 Input Elements 5 A × 1 Input Element	50 A v 4 Input Flomanta
	-5A1-50A4 -5A2-50A3	5 A × 1 Input Element 5 A × 2 Input Elements	50 A × 4 Input Elements 50 A × 3 Input Elements
	-5A3-50A2	5 A × 3 Input Elements	50 A × 2 Input Elements
	-5A4-50A1	5 A × 4 Input Elements	50 A × 1 Input Element
0: :	-5A5-50A0	5 A × 5 Input Elements	
Six input eleme		50.4 01 15	
WT1806E	-5A0-50A6	50 A × 6 Input Elements	50 4 51 151
	-5A1-50A5	5 A × 1 Input Element	50 A × 5 Input Elements
	-5A2-50A4	5 A × 2 Input Elements	50 A × 4 Input Elements
	-5A3-50A3	5 A × 3 Input Elements	50 A × 3 Input Elements
	-5A4-50A2	5 A × 4 Input Elements	50 A × 2 Input Elements
	-5A5-50A1	5 A × 5 Input Elements	50 A × 1 Input Element
	-5A6-50A0	5 A × 6 Input Elements	
Standard Optio			
Menu Languag	e <u>-HC</u>	Chinese/English	
	-HE	English/Japanese	
	-HG	German/English	
	-HR	Russian/English	
Power Cord	-D	UL/CSA Standard PSE c	ompliant
	-F	VDE Standard	
	<u>-H</u>	GB Standard	
	-N	NBR Standard	
	-Q	BS Standard	
	-R	AS Standard	
Additional Opti	ons		
Option	/EX1*1	External Current Sensor	
	/EX2*1	External Current Sensor	
	/EX3*1	External Current Sensor	
	/EX4*1	External Current Sensor	Input for WT1804E
	/EX5*1	External Current Sensor	Input for WT1805E
	/EX6*1	External Current Sensor	Input for WT1806E
	/B5	Built-in Printer	
	/G5 ⁻²	Harmonic Measurement	
	/G6°2		onics (except for WT1801E
	/V1	RGB Output	
	/DA	20-Channel D/A Output	
	/MTR*3	Motor Evaluation Function	n
	/AUX*3	2-Channel Auxiliary Input	
	/PD2*4	6-Channel Current Senso	
	Chunt Posister Pa		1 to /EVS and /DD2 antions

^{*1, *4:} When use Shunt Resistor Box for measurement, both /EX1 to /EX6 and /PD2 options are required. *2, *3: When select these functions, please specify only one. *4: /PD2 option requires Firmware version Ver. 3.1 or later. Standard accessories

Power cord, Rubber feet, current input protective cover, User's manual, expanded user's manual, communication interface user's manual, printer roll paper (provided only with /B5), connector (provided only with /DA), Safety terminal adapter 758931 (provided two adapters in a set times input element number)

User's manuals [Start guide (booklet), function/operation, communication manuals (electric file)]

Accessory (sold separately)

Model number	Product	Description
366924	BNC-BNC Cable	1 m
366925	BNC-BNC Cable	2 m
701901	1:1 Safety BNC Adapter Lead	1000 Vrms-CAT II for /MTR, /AUX
701902	Safety BNC-BNC Cable	1000 Vrms-CAT II, 1 m for /MTR, /AUX
701903	Safety BNC-BNC Cable	1000 Vrms-CAT II, 2 m for /MTR, /AUX
751535-E4	Rack Mounting Kit	For EIA without /PD2 option model
751535-J4	Rack Mounting Kit	For JIS without /PD2 option model
751535-E5	Rack Mounting Kit	For EIA with /PD2 option model
751535-J5	Rack Mounting Kit	For JIS with /PD2 option model
758917	Test Lead Set	A set of 0.75 m long, red and black test leads
758921	Fork Terminal Adapter	Banana-fork adapter, Two adapters to a set
758922	Small Alligator-clip	Rated at 300 V two in a set
758923	Safety Terminal Adapter	Two adapters to a set (spring-hold type)
758924	Conversion Adapter	BNC-banana-Jack (female) adapter
758929	Large Alligator-clip	Rated at 1000 V and used in a pair
758931	Safety Terminal Adapter	Two adapters to a set (Screw-fastened type), 1.5 mm hex Wrench is attached.
CT60	AC/DC Current Sensor	Maximum 60 Apeak, DC to 800 kHz (-3 dB)
CT200	AC/DC Current Sensor	Maximum 200 Apeak, DC to 500 kHz (-3 dB)
CT1000	AC/DC Current Sensor	Maximum 1000 Apeak, DC to 300 kHz (-3 dB)
CT2000A	AC/DC Current Sensor	Maximum 2000 Arms, DC to 40 kHz (-3 dB)

	Parts number	Product	Description Order	Q'ty
	A1323EZ*2	Shunt Resistor Box	$5 \Omega \pm 0.05\%$	1
	A1324EZ ²	Shunt Resistor Box	10 Ω ±0.02%	1
	A1325EZ ²	Shunt Resistor Box	20 Ω ±0.02%	1
	A1559WL	Current Sensor Cable	Cable length 3 m for Shunt Resistor Box	1
	A1560WL	Current Sensor Cable	Cable length 5 m for Shunt Resistor Box	1
	A1589WL	Current Sensor Direct Cable	Cable length 3 m (Burden resistor 2.7 Ω)	1
	A1628WL	Current Sensor Direct Cable	Cable length 5 m (Without Burden resistor)	1
	B9284LK 🐴	External Sensor Cable	Current sensor input connector, Length 0.5 m	1
	B9316FX	Printer Roll Paper	Thermal paper, 10 m (1 roll)	10
			· · · · · · · · · · · · · · · · · · ·	

[⚠] Due to the nature of this product, it is possible to touch its metal parts. Therefore, there is a risk of electric shock, so the product must be used with caution.

*1: Use these products with low-voltage circuits (42 V or less).

■ Any company's names and product names mentioned in this document are trade names, trademarks or registered trademarks of their respective companies

NOTICE

• Before operating the product, read the user's manual thoroughly for proper and safe operation.

Yokogawa's Approach to Preserving the Global Environment -

- Yokogawa's electrical products are developed and produced in facilities that have received ISO14001 approval.
- In order to protect the global environment, Yokogawa's electrical products are designed in accordance with Yokogawa's Environmentally Friendy Product Design Guidelines and Product Design Assessment Criteria.

This is a Class A instrument based on Emission standards EN61326-1 and EN55011 and is designed for an industrial environment.

Operation of this equipment in a residential area may cause radio interference, in which case users will be responsible for any interference which they cause.

http://tmi.yokogawa.com/

YMI-KS-MI-SF05

YOKOGAWA TEST & MEASUREMENT CORPORATION

YOKOGAWA

Facsimile: +81-422-52-6462

Subject to Change without notice. Copyright © 2016, Yokogawa Test & Measurement Corporation [Ed: 03/b] Printed in Japan, 803(KP)

YOKOGAWA CORPORATION OF AMERICA YOKOGAWA EUROPE B.V. Phone: +31-88-4641000 YOKOGAWA SHANGHAI TRADING CO., LTD. YOKOGAWA ELECTRIC KOREA CO., LTD. Phone: +82-2-2628-3810 Phone: +65-6241-9933 YOKOGAWA ENGINEERING ASIA PTE. LTD. YOKOGAWA INDIA LTD. YOKOGAWA ELECTRIC CIS LTD. Phone: +7-495-737-78-68 YOKOGAWA AMERICA DO SUL LTDA. Phone: +55-11-5681-2400 YOKOGAWA MIDDLE EAST & AFRICA B.S.C(c) Phone: +973-17-358100

E-mail: tmi@us.yokogawa.com E-mail: tmi@nl.yokogawa.com Facsimile: +86-21-6880-4987 E-mail: TMI@kr.yokogawa.com Facsimile: +82-2-2628-3899 E-mail: TMI@sg.yokogawa.com Facsimile: +65-6241-9919 Phone: +91-80-4158-6396 E-mail: tmi@in.yokogawa.com Facsimile: +91-80-2852-1442 E-mail: info@ru.yokogawa.com Facsimile: +7-495-737-78-69

E-mail: help.ymatmi@bh.yokogawa.com Facsimile: +973-17-336100

^{*2: /}EX option must be installed in the WT1800E to be able to use the Shunt Resistor Box.