## 2. THERMOCOUPLES

Thermocouples sense temperatures based on the principle that an electrical current is generated when two different metals are combined in a closed circuit and subjected to a temperature difference; they are widely exploited in industry due to their simple construction and excellent reliability. There are many types of thermocouples in use. Those which are the most widely used, whose characteristics are understood, and which have demonstrated their reliability, have become the objects of standardization. This document deals primarily with those thermocouples standardized in the JIS, plus other typically used thermocouples that have been field-proven in particular applications.

### 2.1 Overview of the JIS '95 Revisions

JIS standards related to thermocouples were revised as of July 1, 1995. The major purpose of this revision is to make these JIS standards conform to the international standard IEC 584. Thermocouple codes, thermal EMF, and tolerance classes were revised to match IEC584, so JIS standard data are consistent with the standards used abroad now.

The major changes are "N thermocouple is newly stipulated" and "standard thermal EMFs revised". As shown in Figure 1, the difference between JIS'89 and JIS'95 thermal EMFs will have little effect on industrial temperature measurement.




Figure 1 Revised Value of Thermal EMF

# 2.2 Types of Thermocouples

In most cases, a thermocouple's type is indicated by a code. Since the codes specified in JIS conform to the IEC standards, they are shared with other international standards, in particular with DIN (Germany) and ANSI (United States) [See Table 10]. Table 8 shows the codes, component materials, operating limits, and other features of thermocouples standardized in JIS. Table 9 shows representative non-JIS-standard-thermocouples in practical use.

Table 7 Thermocouple Codes, Component Materials, Normal Operating Limits, and Overheat Operating Limits (JIS C 1602-1981)

Overheat Operating Limits (JIS C 1602-1981)									
Code	Old code	Component materials + side - side		Class	Element diameter (mm)	Normal operating limits (° C)	Overheat operating limits (° C)	Properties	
В	_	Contains 30% Rhodium. Platinum- Rhodium alloy	Contains 6% Rhodium. Platinum- Rhodium alloy	Class 2 Class 3	0.50	1500	1700	Thermal EMF is very small at room temperature. Large differences in characteristics sometimes seen. Otherwise the same as Type R.	
R	_	Contains 13% Rhodium, Platinum. Rhodium alloy	Platinum	Class 2	0.50	1400	1600	Very stable. Suitable as standard thermocouple. Suitable for corrosive environments. Sensitive to hydrogen,	
S	-	Contains 10% Rhodium. Platinum. Rhodium alloy	Platinum	- Class 2	0.50	1400	1600	metal vapors. Small thermal EMF. Very slight secular change. Large extension wire error.	
		Alloy, primarily Nickel, Chrome, and Silicon	Alloy, primarily Nickel, and Silicon	Class 1 Class 2 Class 3	0.65	850	900	Excellent corrosion	
					1.00	950	1000	resistance (several times that of Type K). No	
N					1.60	1050	1100	error generation due to short-range ordering.	
					2.30	1100	1150	Magnetic field	
					3.20	1200	1250	influence relatively small.	
	CA	Alloy, primarily Nickel and Chrome	Alloy, primarily Nickel	Class 1 Class 2 Class 3	0.65	650	850		
					1.00	750	950	Good EMF linearity. Suitable for corrosine	
K					1.60	850	1050	environment. Resistant	
					2.30	900	1100	to metal vapors. Some secular change.	
					3.20	1000	1200		
		Alloy, primarily Nickel and Chrome	Alloy, primarily Copper and Nickel	Class 1 Class 2 Class 3	0.65	450	500		
	CRC				1.00	500	550	Lower cost than Type K, larger thermal EMF.	
Е					1.60	550	650	Non-magnetic. Some	
					2.30	600	750	drift over time.	
					3.20	700	800		
	IC	Iron	Alloy, primarily Copper and Nickel	Class 1 Class 2 Class 3	0.65	400	500	Low cost, with fairly large thermal EMF.	
					1.00	450	550	Good EMF linearity. Suitable for reducing	
J					1.60	500	650	environments. Large sample-to-sample	
					2.30	550	750	variations in dharacteristics, quality.	
					3.20	600	750	Rusts easily. Drifts at high temperatures.	
	СС	Copper	Alloy, primarily Copper and Nickel	Class 1 Class 2 Class 3	0.32	200	250	Low cost, with good low-temperature	
Т					0.65	200	250	characteristics. Good linearity, Suitable for	
1					1.00	250	300	reducing environments.	
					1.60	300	350	Large extension wire error.	
					1	1	ı		

Table 8 Non-JIS Thermocouples in practical Use

Table 8 Non-JIS Thermocouples in practical Use								
Name	Componen	t materials	Operating temperature	Properties	Standard thermal EMF table, and authority			
	+ side	-side	range Overheat limit in ( )	,				
Platinum-	Contains 20% Rhodium. Platinum-Rho- dium alloy	Contains 5% Rhodium. Platinum-Rho- dium alloy	300 to 1500° C (1800° C)	Usable at high temperatures. Small thermal EMF.	Appendix Table B22			
Rhodium	Contains 40% Rhodium. Platinum-Rho- dium alloy	Contains 20% Rhodium. Platinum-Rho- dium alloy	1100 to 1600° C (1800° C)	Otherwise, same as Type R.				
	Contains 5% Rhodium. Platinum-Rho- dium alloy	Contains 26% Rhodium. Platinum-Rho- dium alloy			Appendix Tables B20 ASTM E988-84			
Tungsten- Rhenium	Contains 3% Rhodium. Platinum-Rho- dium alloy	Contains 25% Rhodium. Platinum-Rho- dium alloy	0 to 2400° C (3000° C)	Suitable for reducing environments, inert gasses, hydrogen gas. Fragile.	Appendix Table B22 ASTM E988-84			
	Tungsten	Contains 26% Rhodium. Platinum-Rho- dium alloy						
Platinel	Alloy, primarily Palladium, Platium, and Gold  Alloy, primarily Gold and Palladium  O to 1100° C (1300° C)		0 to 1100° C (1300° C)	High resistance to abrasion. Thermal EMF nearly the same as that of Type K.	Appendix Table B22 NBS Journal of Research, vol. 68C. N08			
Chromel/ Gold-Iron	Alloy, primarily Nickel and Chrome o4?0 (Chromel)	Contains 0.07 mole% Iron. Gold-Iron alloy	1 to 300K	Thermal EMF relatively large at 20 K and below. Good EMF linearity.	ASTM SPT430 Appendix Table B21			

### 2.3 Thermal EMF Characteristics

The standard thermal EMFs of the various thermocouple types are shown in Appendix Tables B1 through B19.

Because JIS C 1602-1995 was written to be consistent with the standards used in other countries, particularly IEC, ANSI, etc., this is beneficial when importing and exporting. However, attention is required since the DIN standard adopts its own unique specifications for Type U and Type L. Table 10 gives a list of the standard thermal EMF document selections for the individual national and international standards. Equations for interpolation of standard thermal EMFs are provided for reference at the end of this document.

Table 9 Thermal EMF Document Selection List

		Thermocou	ple standard	C. I I I I I I I I I I I I I I I I I I I			
Thermocouple generic name	Standard type					Standard thermal EMF document number	Remarks
	JIS	IEC	ANSI	BS	DIN		
Platinum-Rhodium/6-30			TYPE B			Appecdix Table-B1	
Di di Di . di /Di .di	TYPE R					Appendix Table-B2	
Platinum-Rhodium/Platinum	TYPE S					Appendix Table-B3	
Nichrosil/Nisil (N)	TYPE N					Appendix Table-B4	
Chromel/Alumel	ТҮРЕ К					Appendix Table-B5	
Chromel-Constantan	ТҮРЕ Е					Appendix Table-B6	
	ТҮРЕ Ј				Appendix Table-B7		
Iron-Constantan			_		Type L (Fe-CuNi)	Appendix Table-B19	
	ТҮРЕ Т				Appendix Table-B8		
Copper-Constantan	-			Type U (Cu-CuNi)	Appendix Table-B18		

#### Note:

<sup>1.</sup> A line drawn in the table indicates that the thermocouple in question is not covered in thet standard. Those for which the same document number is given have the same standard thermal EMFs even if their names are different.

<sup>2.</sup> ASTM'93 is a national standard of the U.S. which regulates thermocouple reference thermal E.M.F..: ASTM E230-93.