

EVALUATION YOKOGAWA WT310 FOR STANDBY POWER

Erik Kroon

Standards Laboratory Yokogawa Europe

Euroweg 2, 3825 HD Amersfoort, The Netherlands

erik.kroon@nl.yokogawa.com

Abstract

We have evaluated the Yokogawa WT310 Power meter performance using the IEC 62301 Ed. 2.0 standard. Using challenging signals the Yokogawa WT310 was checked if it would fulfill the requirements of the standard.

Introduction

The requirements of the IEC 62301 Ed. 2.0 states for the power values greater or equal to 1,0 W then the uncertainty should be less than 2% of the measured value. For measured power values less than 1,0 W the uncertainty should be better than 0,02 W while the Maximum Current Ratio (MCR) ≤ 10 . If the MCR > 10 an equation is used to calculate the required uncertainty. The Yokogawa WT310 is compared to a high speed sampling Wattmeter calibration system.

High Speed Sampling Wattmeter

A high speed sampling wattmeter was developed to calibrate from DC to 1 MHz power. This system is excellent in calibrating high frequency power, distorted waveforms and harmonics.

Generator

The generator for the signals is a Yokogawa FG 320. This is a two channel arbitrary waveform generator. The output of the generator drives wide band amplifiers (DC – 1 MHz). The amplifiers generate the reference Voltage and Current. The total harmonic distortion of the Voltage signal is smaller than 0,1% at 230 Volt. The current amplifier is able to drive from 0 to 5 A.

Front end

The front end is the part that converts the voltage and current to a 1 Volt signal that the sampling system uses for the A/D input. The 230 Volt is converted to a 1 Volt signal by using a capacitor compensated resistance divider. To convert the current into a 1 Volt signal a special wide band shunt was developed. The 1 Volt signals is fed to a differential amplifier to avoid common mode effects.

Sampling System

The core of the sampling system is the NI-5922 A/D converter. This is a high speed high resolution converter. Running on 500 kS/s the resolution is 24 bits. At a maximum of 15 MS/s the resolution is still 16 bits. There are two input channels using the same clock source. Using software we are able to calculate the voltage, current, power, etc. The accuracy of the total system is many times higher than needed for the IEC 62301 Ed. 2.0 standard. Therefore we are able to check the Yokogawa WT310 against the sampling system.

Measurements

We used the standby power software from Yokogawa to read out the values measured by the Yokogawa WT310 power meter. A minimum of five minutes was set and the averaged value was taken. During the five minutes the applied signals where stable. The voltage was sine wave of 230 Volt. The current range was set to auto. The WT310 measures the peak current and select the best current range.




Figure 1 Applied Voltage Signal

For the first measurement a sine waveform was used for the current range and a power factor of 1.

First measurement:

Current waveform : sine
 Voltage : 230 Volt
 Power factor : 1
 Phase : 0 °
 Crest factor : 1,41
 Apparent power : 2,2993 VA
 Reference Power : 2,2986 W
 WT310 Power : 2,2992 W
 Difference : 0,0006 W
 Relative difference : 0,026 %

Conclusion:

The power is > 1,0 W the 2% requirement is met.

Second measurement:

Current waveform : sine
 Voltage : 230 Volt
 Power factor : 0,1043
 Phase : 84,004 °
 Crest factor : 1,41
 Apparent power : 4,6074 VA
 Reference Power : 0,4809 W
 WT310 Power : 0,4806 W
 Difference : -0,0003 W
 Relative difference : -0,069 %

Conclusion:

The power is < 1,0 W so the 0,02 W requirement is met.

Next the current wave form is changed into a pulse shaped wave form with a very high crest factor.




Figure 2 Applied Current Signal

Third measurement:

Current waveform : pulse shape
 Voltage : 230 Volt
 Power factor : 0,0679
 Phase : 86,105 °
 Crest factor : 11
 Apparent power : 3,7210 VA
 Reference Power : 0,2526 W
 WT310 Power : 0,2520 W
 Difference : -0,0006 W
 Relative difference : -0,245 %

In this situation the MCR is bigger than 10.

$$MCR = \frac{\text{Crest Factor (CF)}}{\text{Power Factor (PF)}} = \frac{11}{0,0679} = 162$$

The permitted uncertainty is determined using the following equation:

$$U_{pc} = 0,02 \times [1 + (0,08 \times \{MCR - 10\})]$$

$$U_{pc} = 0,02 \times [1 + (0,08 \times \{162 - 10\})] = 0,2632$$

$$U_{pc} \times \text{measured value} = 0,2632 \times 0,252 = 0,0663 \text{ W}$$

Here the difference between the reference value and WT310 reading is only -0,0006 W it met the required uncertainty of 0,0663 W by far.

Fourth measurement:

Current waveform : pulse shape
 Voltage : 230 Volt
 Power factor : 0,06757
 Phase : 86,084 °
 Crest factor : 11
 Apparent power : 1,0004 VA
 Reference Power : 0,0676 W
 WT310 Power : 0,0678 W
 Difference : 0,0002 W
 Relative difference : 0,352 %

In this situation the MCR is bigger than 10.

$$MCR = \frac{\text{Crest Factor (CF)}}{\text{Power Factor (PF)}} = \frac{11}{0,0676} = 163$$

The permitted uncertainty is determined using the following equation:

$$U_{pc} = 0,02 \times [1 + (0,08 \times \{MCR - 10\})]$$

$$U_{pc} = 0,02 \times [1 + (0,08 \times \{163 - 10\})] = 0,2648$$

$$U_{pc} \times \text{measured value} = 0,0676 \times 0,2648 \\ = 0,0179 \text{ W}$$

Because the $U_{pc} < 0,02 \text{ W}$ the uncertainty requirement will be $0,02 \text{ W}$

Here the difference between the reference value and WT310 reading is $0,0002 \text{ W}$ it met the required uncertainty of $0,02 \text{ W}$.

Fifth measurement:

Current waveform	: pulse shape
Voltage	: 230 Volt
Power factor	: 0,5690
Phase	: 52.97 °
Crest factor	: 11
Apparent power	: 0,2299 VA
Reference Power	: 0,13717 W
WT310 Power	: 0,13710 W
Difference	: -0,00007 W
Relative difference	: 0,050 %

In this situation the MCR is bigger than 10.

$$MCR = \frac{\text{Crest Factor (CF)}}{\text{Power Factor (PF)}} = \frac{11}{0,569} = 19$$

The permitted uncertainty is determined using the following equation:

$$U_{pc} = 0,02 \times [1 + (0,08 \times \{MCR - 10\})]$$

$$U_{pc} = 0,02 \times [1 + (0,08 \times \{19 - 10\})] = 0,0344$$

$$U_{pc} \times \text{measured value} = 0,0344 \times 0,13710 \\ = 0,0047 \text{ W}$$

The $U_{pc} < 0,02 \text{ W}$ the uncertainty requirement will be $0,02 \text{ W}$

Because the difference between the reference value and WT310 reading is $-0,00007 \text{ W}$ it met the required uncertainty of $0,02 \text{ W}$.

Table 1. Summary

Measurement	Required Uncertainty	Measured Deviation
1	±2 %	0,026 %
2	±0,02 W	-0,0003 W
3	±0,0663 W	-0,0006 W
4	±0,02 W	0,0002 W
5	±0,02 W	-0,00007 W

Conclusion

Using the challenging and extreme signals the Yokogawa WT310 fulfills the requirements of the IEC 62301 Ed. 2.0 standard.

It is recommended to calibrate the Yokogawa WT310 at regular intervals.