

2558A

AC Voltage Current Standard

SIMPLE STANDALONE SOLUTION FOR CALIBRATING METERS, CLAMPS AND CTS



Easy Operation

for each function

High Accuracy

AC Voltage

Wide Output Range

00 mV to 1200.0 1.00 mA to 60.00 A

For more information, go to tmi.yokogawa.com **Test & Measurement Instruments**



Sweep (Voltage/Current/Frequency*)

With a flick of a switch, the output can be swept from 0% to

* The range of frequency sweep can be set.

Output Divider

Intuitive operation

Linearity tests can be simply performed by dividing the output into steps. For example, a setting of 4 will generate steps of 25, 50, 75 and 100% of the set output value.

Dials and switches are provided for each digit and function, and traditional 7-segment LEDs provide clear visibility.

120% of the main set value with sweep times of 16, 32 or 64

Direct readout of the deviation

When the deviation dials are adjusted to check the full scale value on the meter, the deviation from the main output setting is displayed as a % of full scale.

Digital display of output

The actual output value is displayed. It is therefore unnecessary to calculate the output value from the main, divider and deviation

You can confirm that the output is stable and how it corresponds to the target meter's reading.

Common current output terminals

The same output terminals are used for all current ranges. Test times are therefore reduced by avoiding the need to change the wiring for meters which have different ranges.

Reliable and Simple Operation

range selection

New AC Voltage Current Standard from "YOKOGAWA"

The wide output ranges of 1.00 mV to 1200.0 V* AC and 1.00 mA to 60.00 A* AC mean that the 2558A is the instrument of choice for the cost effective calibration of AC analog meters. Rotary controls and a range of computer interfaces enable the 2558A to be intuitively operated through the front panel or controlled by an ATE system.

* With the deviation function, the maximum output is 1440 V and 72 A.

Frequency / Phase Main set value Output divider Deviation Output Output ON/OFF switch Voltage/ Sweep execution switch Frequency

High accuracy

AC voltage: ±0.04 % AC current: ±0.05 %

More than sufficient to calibrate meters with class 0.1% accuracy.

10 to 120 % of range			
	± (% of setting + % of range)		
	50/60 Hz	$40 \le f \le 400 \text{ Hz}$	$400 < f \le 1 \text{ kHz}$
AC voltage	0.03 + 0.01	0.05 + 0.01	0.10 + 0.02
AC current	0.04 + 0.01	0.06 + 0.01	0.12 + 0.02

1 to 10 % of rar	nge		
		± (% of range)	
	50/60 Hz	$40 \le f \le 400 \text{ Hz}$	400 < f ≤ 1 kHz
AC voltage	0.013	0.015	0.03
AC current	0.014	0.016	0.032

High stability

AC voltage/current: ±50 ppm/h

± (20 ppm of range + 30 ppm of range)/h Perform measurements with high repeatability over time

Wide output range

Current range selection

AC voltage: 1.00 mV to 1200.0 V AC current: 1.00 mA to 60.00 A

6 voltage ranges (100 m/1/10/100/300/1000 ([V]) 4 current ranges (100 m/1/10/50 ([A])

The generation range is 0 to 144 % of range

Ex. Set for the output

- 1. Select the range
- 2. Main setting: Available for 0 to 120 % of the range
- 3. Output divider: n & m (n/m of main set value) m = The number of required calibration points if the main set value = 100V, m = 5 and n = 1, the output will
- 4. Deviation: Available for ± 20 % of the main setting

Max. output current is "72A" at the 50 A range

Main setting : 60 A Output divider : n = mDeviation

Wide frequency range

40 to 1000 Hz (Frequency accuracy: ±50 ppm)

The 2558A provides fixed frequencies of 50/60 Hz (commercial) and 400 Hz (marine and aviation), as well as variable frequencies from 40 to 1000 Hz.

The high frequency accuracy of the 2558A (50 ppm) also enables it to be used to calibrate frequency meters.

Multiple 2558As can be synchronized using the internal phase shifter. This means that two 2558As can be used as accurate sources of voltage and current for calibrating power meters.


AC Voltage Current Stan

Power calibration

A power calibration system can be created by using two 2558As (one each for AC voltage and AC current) together with a Yokogawa WT3000 power analyzer as the reference.

One of the 2558As acts as the master unit and provides the synchronizing oscillator signal. The required power factor is set by adjusting the phase shifter on the slave unit and monitoring the result on the WT3000.

A 3 phase power calibrator system can be simply built by adding further 2558As.




Higher current output

To generate higher current than 72 A, two 2558As can be connected to double the output to 144 A.

Condition:

- Accuracy, stability, temperature coefficient is the sum of the individual units.
- 50/60 Hz only.



Calibration and test for meters

The 2558A provides specific functions to enable meters to be calibrated accurately and efficiently.

Using the output divider and deviation

Calibrating two or more points is quick and simple. It is only necessary to preselect the number of required calibration points with the lower divider control and then use the upper control to step the output to the next calibration point. The deviation settings will then enable the output value and error of each calibration point to be displayed directly.

Using the output divider and deviation preset

Application

The deviation preset control can be used to move the output value in small increments (2 or 5% of the step between calibration points).

This means that it is possible to finely approach the target calibration point, either from a lower value or a higher one, without exceeding it. This is particularly useful when the friction (hysteresis) of the moving part needs to be taken into consideration. In this case the point is calibrated twice, once from a lower value and once more from a higher value and the final calibration result is the average of the two.


Using sweep


Needle sticking tests can be performed with high repeatability.

It is possible to stop at any point and sweep around it in fine detail.



311011





From a lower value

From a higher value









Use existing 2558 programs

The 2558A is backwardly compatible with the previous 2558 model. The new 2558A supports a 2558 command mode, which means that you can switch from the 2558 to the 2558A without modifying your program. It is also possible to mix 2558s and new 2558As in the same

* Programs may need to be modified due to the improvement in the response time etc.



Comparison with the 2558

		2558A	2558
	Output range of the specified accuracy	1.00 mV to 1200.0 V	1.00 mV to 1200.0 V
AC Voltage	Accuracy (50/60 Hz)	± 400 ppm	± 950 ppm
	Frequency of the specified accuracy	40 to 1000 Hz	50 / 60 / 400 Hz
	Output range of the specified accuracy	1.00 mA to 60.00 A	1.00 mA to 60.00 A
AC Current	Accuracy (50/60 Hz)	± 500 ppm	± 950 ppm
	Frequency of the specified accuracy	40 to 1000 Hz	50 / 60 / 400 Hz
Eroguopou	Output range	40 to 1000 Hz	40 to 500 Hz
Frequency	Accuracy	± 50 ppm	± 1%
	Max. output	Approx. 36 VA (60 A/0.6 V)	Approx. 36 VA (60 A/0.6 V)
	Stability	± (20 ppm of setting + 30 ppm of range)/h	± (0.03% of range)/h
	Dimension (mm)	426 (W) × 132 (H) × 400 (D)	439 (W) × 149 (H) × 415 (D)

Rear Panel



GP-IB interface (optional, /C1)

2 Ethernet

O USB interface (for PC connection)

Input terminals for synchronized operation

6 Output terminals for synchronized operation

Specification

Output

Range	Output range	Specified output range	Resolution	Maximum output
100 mV	0 to 144.00 mV	1 to 120.00 mV	10 uV	-
1 V	0 to 1.4400 V	0.01 to 1.2000 V	100 uV	0.5 A or more
10 V	0 to 14.400 V	0.1 to 12.000 V	1 mV	Approx. 3 A
100 V	0 to 144.00 V	1 to 120.00 V	10 mV	Approx. 0.3 A
300 V	0 to 432.0 V	3 to 360.0 V	100 mV	Approx. 0.1 A
1000 V	0 to 1440.0 V	10 to 1200.0 V	100 mV	Approx. 6 mA
100 mA	0 to 144.00 mA	1 to 120.00 mA	10 uA	Approx. 15 V
1 A	0 to 1.4400 A	0.01 to 1.2000 A	100 uA	Approx. 15 V
10 A	0 to 14.400 A	0.1 to 12.000 A	1 mA	Approx. 3 V
50 A	0 to 72.00 A	0.5 to 60.00 A	10 mA	Approx. 0.6 V

Condition Frequency Temperature/Humidity

: 23 ± 3 °C/20 to 80 %RH

Add the temp. coefficient at 5 to 20°C, 26 to 40°C

Accuracy

	Upper : 180 days Lower : 1 year					
		10% to 120% of range		1% to 10% of range		
	±	(% of setting + % of range	e)	± (% of range)		
Range	50/60 Hz	40 Hz ≤ f ≤ 400 Hz	400 Hz < f ≤ 1 kHz	50/60 Hz	40 Hz ≤ f ≤ 400 Hz	400 Hz < f ≤ 1 kHz
100 mV						
1 V						
10 V	0.03 + 0.01	0.05 + 0.01	0.10 + 0.02	0.013	0.015	0.030
100 V	0.04 + 0.01	0.06 + 0.01	0.11 + 0.02	0.014	0.016	0.031
300 V						
1000 V						
100 mA						
1 A	0.04 + 0.01	0.06 + 0.01	0.12 + 0.02	0.014	0.016	0.032
10 A	0.055 + 0.01	0.075 + 0.01	0.135 + 0.02	0.0155	0.0175	0.0335
50 A						

± (20 ppm of setting + 30 ppm of range)

Output: 1 to 120% of range Condition Frequency: Internal oscillator

> Temperature/Humidity: 23±3°C / 20 to 80%RH Time: 1 min. to 1 hour after output ON

Temperature Coefficient (5 to 20°C, 26 to 40°C)

50/60 Hz ±(30 ppm of setting/°C) Other ±(50 ppm of setting/°C)

Voltage output : 0.07% or less Current output : 0.18% or less Output: 40 to 120% of range

Load: Resistance only

20% of the max. output or less (Current at the voltage output,

or voltage at the current output)

Frequency: 40 to 1000 Hz

Specification

Frequency range

Accuracy (internal) : ± 50 ppm (180 days) ± 100 ppm (1 year)

Mode Internal / External / FREQUENCY METER

Internal: 50 / 60 / 400 Hz

VAR (40 to 1000 Hz, 0.001 Hz resolution)

External: EXT1 / EXT2

(Use the terminals for the synchronized operation)

FREQUENCY METER: MIN/MAX

Range: 20 to 1000 Hz

Resolution: 0.001 Hz

Sweep, output divider and deviation functions are used

for the frequency.

Target : Voltage / Current / Frequency Speed Approx. 16/32/64 sec. selectable During 0 to 100%, 100 to 0% of setting

Output divider

Target : Voltage / Current / Frequency

Denominator : m 4 to 15 : $n \ 0 \ to \ 15 \ (n \le m)$ Numerator

Deviation

: Voltage / Current / Frequency Target

Variable range : ±20.00% Operation

Resolution of the first dial: 0.2% of the main setting

Resolution of the second dial: 0.01% of the main setting Deviation preset : OFF / 0 / 2% / 5%

Output termina

Voltage: Plug-in terminal (safety terminal) Туре

Current: Large binding post

Selectable LO terminal to earth or floating. Max. floating voltage to earth: 12 Vpk

Display

Main setting : 5 digits LED Output Divider : 2 digits LED (m and n)

: 4 digits LED Deviation : 5 digits LED

: 6 digits LED Frequency/Phase

Setting : Communication, Beep sound, Sweep speed,

Status Self test, Error log, Product Information

Sync. Terminals (two input terminals and two output terminals)

I/O voltage: 3±0.1 Vrms, 2 phase sine wave Frequency: 40 to 1000 Hz

Input resistance: Approx. 1 MΩ Output resistance : Approx. 50 Ω

USB PC interface (for PC connection

: Type B connector (receptacle)

: Complies with USB Rev. 2.0 Electrical and mechanical specifications

Supported transfer modes: High Speed, Full Speed

Ethernet interface

Connector : RJ-45 connector

Electrical and mechanical specifications : Confirms to the IEEE 802.3

Transmission methods : 100 BASE-TX / 10 BASE-T

GP-IB interface (/C1 optiona

Electrical and mechanical specifications

Complies with IEEE St'd 488-1978

Functional specifications : SH1, AH1, T6, L4, SR1, RL1, PP0, DC1, DT1, C0

Address : 0 to 30

General specifications

Warm-up time Approx. 30 minutes Operating environment

: Temperature : 5 to 40°C

Humidity: 20 to 80%RH (no condensation)

: Attitude 2000 m or less

Installation locations

: Temperature -15 to 60°C Storage environment

Humidity 20 to 80%RH (no condensation)

Rated power supply voltage: 100 to 120 VAC / 200 to 240 VAC

Allowable power supply voltage fluctuation range : 90 to 132 VAC / 180 to 264VAC

Rated power supply frequency: 50/60 Hz

Allowable power supply frequency fluctuation range : 48 to 63 Hz

Max. power consumption: 200 VA

Weiaht · Approx 20 kg Dimensions : 426(W) x 132(H) x 400(D) mm

Accessories





Fork terminal adapter set

Two adapters (red and black) to a set, Used









701902 / 701903 758923 Safety BNC-BNC cable










Small Alligator clip adapter set

Safety terminal (banana female)-to-alligator

clip adapter 2 pieces (red and black) in 1 set Rating: 300 V CAT II Connected to the 758933, 758917, or 701901.





Large Alligator clip adapter set

Safety terminal (banana female)-to-alligator

with metal parts and receive electric shock Exercise caution when using the product.

Model and Suffix Codes Model Suffix code Description 2558A AC Voltage Current Standard -D UL/CSA standard, PSE -F VDE standard -R AS standard Power code -0 BS standard -H GB standard -N NBR standard GP-IB interface Option /C

Part name	Quantity
Power code	1
Measurement lead set (758933)	1 set (red and black)
Measurement lead set (B8506WA)	1 set (red and black)
Large alligator clip adapter set (758929)	1 set (red and black)
Rubber leg cap	1 set (2)
User's manual	1 set


Rack Mount Kits

Model	Suffix code	Description
751535-E3	Rack mount kit	For EIA
751535-J3	Rack mount kit	For JIS

Optional Accessories

Model	Part name	Description
758933	Measurement lead set	1 m, 2 leads in a set
B8506WA	Measurement lead set	1.5 m, 2 leads in a set
758917	Measurement lead set	75 cm, 2 leads in a set
758922	Alligator clip adapter set	Rating 300 V, 2 adapters in a set
758929	Alligator clip adapter set	Rating 1000 V, 2 adapters in a set
758921	Fork terminal adapter set	Banana-fork adapter, 2 adapters in a set
701902	Safety BNC-BNC cable	1.0 m
701903	Safety BNC-BNC cable	2.0 m
758923	Safety terminal adapter set	Spring-hold type, 2 adapters in a set
758931	Safety terminal adapter set	Screw-fastened type, 2 adapters in a set

External dimensions



Related Product



Low Power Factor Error

Power factor influence when cosø=0 0.03% of S

S is reading value of apparent power ø is phase angle between voltage and current

Current Range

Direct Input

0.5/1/2/5/10/20/30 [A] *

5m/10m/20m/50m/100m/200m/500m/1/2 [A] *

External Input

50m/100m/200m/500m/1/2/5/10 [V] *

Voltage Range

15/30/60/100/150/300/600/1000 M *

* Voltage range and current range are for crest factor 3

Model	Description
760301	WT3000 1 input element model
760302	WT3000 2 input elements model
760303	WT3000 3 input elements model
760304	WT3000 4 input elements model

Yokogawa's Approach to Preserving the Global Environment =

- · Yokogawa's electrical products are developed and produced in facilities that have received ISO14001 approval.
- · In order to protect the global environment, Yokogawa's electrical products are designed in accordance with Yokogawa's Environmentally Friendly Product Design Guidelines and Product Design Assessment Criteria.

YOKOGAWA



Yokogawa Meters & Instruments Corporation

NOTE

"Before operating the product, read the user's manual thoroughly for proper and safe operation."

YOKOGAWA METERS & INSTRUMENTS CORPORATION

Global Sales Dept.

YOKOGAWA AUSTRALIA PTY. LTD.

YOKOGAWA CORPORATION OF AMERICA

2 Dart Road, Newnan, GA. 30265-1094 U.S.A. Phone: +1-770-253-7000 Facsimile: +1-770-254-0928 YOKOGAWA EUROPE B. V.

Euroweg 2 3825 HD Amersfoort, THE NETHERLANDS Phone: +31-88-4641000 Facsimile: +31-88-4641111

YOKOGAWA ENGINEERING ASIA PTE. LTD. 5 Bedok South Road, Singapore 469270 SINGAPORE Phone: +65-6241-9933 Facsimile: +65-6241-2606

YOKOGAWA AMERICA DO SUL LTDA. Praca Acapulco, 31-Santo Amaro, Sao Paulo/SP, BRAZIL CEP-04675-190 Phone: +55-11-5681-2400 Facsimile: +55-11-5681-4434

YOKOGAWA ELECTRIC KOREA CO., LTD.

C&M Sales Seoul Office 1301-1305, 13rd floor, Kolon digital tower, 106-1, Yangpyongdong-5Ga, Yeongdeungpo-Gu, Seoul, 150-105,

Phone: +82-2-2628-3810 Facsimile: +82-2-2628-3899

Tower A/112-118 Talavera Road Macquarie Park, NSW 2113 Australia

Phone: +61-2-8870-1100 Facsimile: +61-2-8870-1111

YOKOGAWA INDIA LTD.

Plot No. 96. Electronic City Complex, Hosur Road, Bangalore 560100, INDIA Phone: +91-80-4158-6000 Facsimile: +91-80-2852-1442

YOKOGAWA SHANGHAI TRADING CO., LTD.

4F Tower D, Cartelo Crocodile Building, No.568 West Tianshan Road, Shanghai, CHINA Phone: +86-21-6239-6363 Facsimile: +86-21-6880-4987

YOKOGAWA MIDDLE EAST B. S. C.(C)

P.O.BOX 10070, Manama, Building 577, Road 2516, Busaiteen 225, Muharraq, BAHRAIN Phone: +973-17-358100 Facsimile: +973-17-336100

YOKOGAWA ELECTRIC CIS LTD.

Grokholskiy per. 13, Build. 2, 4th Floor, 129090, Moscow RUSSIAN FEDERATION Phone: +7-495-737-7868 Facsimile: +7-495-737-7869 Represented by:

Tachihi Bld. No.2, 6-1-3 Sakaecho, Tachikawa-shi, Tokyo, 190-8586 Japan Phone: +81-42-534-1413 Facsimile: +81-42-534-1426

l -----