



High-Speed Data Acquisition Unit

Acquisition Software V2.10

SL1000 is an excellent replacement for legacy pen and data recorder applications.

Recording is simplified by intuitive, home video like, features to START and STOP recording. In addition, you can also START/STOP based on conditions like alarms. The built-in HDD can record up to 28 days of data (8-ch @ 1KS/s) equivalent to eight pen recorder.

Enhanced software interface,

Easy operation,


Longer Recording Times,

SL1000 supports all these demands.




■ Displaying X-Y Waveforms

You can view both T-Y waveform Display and X-Y waveform Display. Using its fast update feature you can evaluate data quickly and easily.



Accumulating Waveforms


Using the accumulation feature you easily view unevenness of repetitive data.



Setting Marks

You can enter comments in the Mark area when monitoring over long periods of time (Free run mode).





Display of Waveform


High-Speed Data Acquisition Unit $\,SL1000\,$

Ver 2.10 meets the demands of high channel count and easy data operation.

Max 128ch Synchronized (16ch x 8 units)

Data files recorded my multiple units, in synchronized mode, are all inked together by a common LINK file, thereby facilitating batch processing

Using this LINK file, data from all units can be processed and analyzed, as one, at the same time.




File convert

The File Utility tool allows you to save data in either ASCII or binary formats. This facilitates loading data in other analysis program, like MatLAB etc.



Xviewer (Ver.1.44)


New version of Xviewer supports displaying many channels and marker display.



Application examples


Evaluation and Testing of commercial transportation

Testing commercial transportation equipment like Trains, Planes, Elevators etc. demand high reliability and accuracy from the measuring devices. The SL1000 can measure a wide variety of signals over long periods of time.



Environment test of ECU

Testing of ECUs is performed under harsh environments, and demands high reliability. Using Synchronized operation mode several SL1000s can measure different ECUs at high-speeds over long periods of time.



Specifications (Acquisition Software)

Display Functions

Accumulation display: Accumulates T-Y and X-Y waveforms

Waveform that is currently being displayed can be retained on the Snapshot:

screen. As a snapshot waveform. Display color setting and

snapshot waveform deletion

X-Y Display: X-axis channel settings, selection of main or zoomed waveform (in

Triggered mode), and selection of the number of data points to

draw (2K, 10K, 100K)

Mark display (Free run mode): Setting of marks (up to 128 marks, each mark can

display up to 16 characters), display color setting, mark editing, deletion of marks, mark list, collectively saving mark data with the same file name as the waveform data, and loading mark data into

File format: Converts waveform data files (.wdf extension) to ASCII (.csv

extension) or binary (.bin extension) files

Recommended PC System

Windows XP (Service Pack 2 or higher), or Windows Vista OS:

CPU: Pentium 4, 1 GHz or better At least 1 GB Memory

Hard Disk: At least 500 MB of free space (at least 40 GB recommended when

using the auto recording function)

Communication Interface: USB2.0, Ethernet 1000BASE-T (If the /C10 option is installed in the SL1000)

Other: CD-ROM Drive, CRT (XGA or better, Color: 65536 colors or better)

and Mouse

Specifications (Unit)

Synchronous Operati

Synchronized items: Measurement and recording start and stop, internal

sampling clock, external sampling clock, time, trigger,

Maximum connections: 8 Unit (Synchronization connection cable (720901) is

necessary.)

Maximum sync cable length: 10 m or less total

Sampling error between units:

Triggered mode: Max. ±10 ns or one sampling clock,

whichever is longer Free run mode: Max. ±20 ns or one sampling clock,

whichever is longer

Accessories

Product	Model No.	Discripiton
Synchronized connection cable	720901-01	For SL1000(1m)
	720901-02	For SL1000(3m)
Ruck mounting kit	751541-E4	EIA
	751541-J4	JIS



YOKOGAWA ELECTRIC CORPORATION

Communication & Measurement Business Headquarters / Phone: (81)-422-52-6768, Fax: (81)-422-52-6624 E-mail: tm@cs.jp.yokogawa.com

YOKOGAWA CORPORATION OF AMERICA YOKOGAWA EUROPE B.V.

Phone: (1)-770-253-7000, Fax: (1)-770-251-6427 Phone: (31)-88-4641000, Fax: (31)-88-4641111 YOKOGAWA ENGINEERING ASIA PTE. LTD. Phone: (65)-62419933, Fax: (65)-62412606

Change Sheet

For Bulletin 7201-20V21E Ed: 01/b

Please Change the mention contests of this catalogue as follows,

■P.2 [Replace] System requirements in the Main Specifications (Acquisition Software is Standard)

False: "Windows XP (Service Pack 2 or higher), or Windows Vista"

True: "Windows XP (SP2 or later)/Windows 7(32bit/64bit)/Windows 8(32bit/64bit)"

False: "Pentium 4, 1 GHz or better" True: "Core2 Duo 2GHz or better"