#### Test&Measurement



### YOKOGAWA 🔸

## **MY600**

**Digital Insulation Tester** 

# Improve your inspection and regular maintenance efficiency with MY600!

MY600 Digital Insulation Tester has enhanced operation compared to the conventional model by using a shortened measurement time and color indicating judging function. This is a new concept in insulation testers with a communication function to enhance the affinity with a PC or tablet.

#### **Major Features**

#### Two colors for judging measurement results

Set a desired reference value with the comparator function, and it will judge PASS (Green) or FAIL (Red) of a measurement result.



## Approximately 0.5 s high-speed measurement\*

Measurement time of insulation resistance is approx. 0.5 s, which contributes to reducing the operation time.

\*Under the conditions specified by Yokogawa, it may take time to measure due to the influence of capacitive component of a measuring target.



Time comparison of measured value display

#### USB communication and memory function

PC communication is possible with the dedicated USB communication adaptor (91030). Users can save as many as 1000 measurements to the internal memory from which data required for report generation, such as measurement data/time, measured value and range can be transmitted to a PC via communication.



Image figure

## Insulation deterioration diagnosis (PI and DAR measurement\*)

The increase and decrease of resistance value can be measured by continuously measuring the insulation resistance for a prescribed time. The insulation deterioration of the unit under test can be diagnosed by this increase/ decrease. This parameter is useful for preventive maintenance of industrial automation equipment such as Magnetic Flow Meters or electrical equipment.

\*PI: Polarization Index (Resistance after 1 minute/Resistance after 10 minutes)
DAR: Dielectric Absorption Rate (Resistance after 15 seconds/Resistance after
1 minute)

#### Auto lighting backlight and LED light

MY600 has a backlight that automatically lights up in a dark place, as well as an LED light to illuminate objects.



## Line probe with switch is provided as a standard accessory

Users can turn measurement on/ off with the hand switch on the line probe, allowing them work more efficiently.



Bulletin MY600-01EN

#### **Precision Making**

#### Main Specifications Accuracy (tolerance): Within 1 year of shipment

Rated measuring voltage	50 V	100 V*	125 V*	250 V	500 V	1000 V
Maximum effective reading	100 ΜΩ	200 ΜΩ	250 ΜΩ	500 ΜΩ	2000 ΜΩ	4000 ΜΩ
First effective measurement range	0.100 to 10.00 $\text{M}\Omega$	0.100 to 20.00 $\text{M}\Omega$	0.100 to 25.00 MΩ	0.100 to 50.0 $\text{M}\Omega$	0.100 to 500 $\text{M}\Omega$	0.100 to 1000 $\text{M}\Omega$
Accuracy	±2% reading ±2 digit					
Second effective measurement range	10.01 to 100.0 $\text{M}\Omega$	20.01 to 200.0 MΩ	25.01 to 250.0 MΩ	50.1 to 500 $\mbox{M}\Omega$	501 to 2000 $\mbox{M}\Omega$	1001 to 4000 $\mbox{M}\Omega$
Accuracy	±5% reading					
	0.050 to 0.099 MΩ: ±2% reading ±4 digit					
Other ranges accuracy	0.000 to 0.049 M $\Omega$ : ±2% reading ±6 digit					

<sup>\*</sup>Switching method

#### Major functions Accuracy (tolerance): Within 1 year of shipment

major ranc	,	Accuracy (tolerance). Within 1 year of Shipment	
Voltage Measurement	AC	2.0 to 600 Vrms (45 to 65 Hz)	
	DC	±(2.0 to 600) V	
	Accuracy	±1% reading ±4 digit	
		AC/DC auto detection (2 V or more)	
Low resistance Measurement	Range	40.00/400.0/4000 Ω (Auto range)	
	Accuracy	$\pm 2.5\%$ reading $\pm 8$ digit (0.20 to 4000 $\Omega)$ $\pm 8$ digit (0.00 to 0.19 $\Omega)$	
Display		Bar graph, 4000 digital count display	
Functions		Automatic discharge, Live-line alarm, Pass/Fail judgement by comparator, Buzzer warning, USB communication, Battery check, Measured values strage, Elapsed time display, PI/DAR display, Serial No. display, Data hold, Auto LED light	
Measurement categories		CAT III 600 V	
Protection grade		IP40	
Standard		JIS C 1302: 2018 compliant (Planned) EN61557-1, 2, 4, 10 EN61326-1 ClassB, EN61326-2-2 EN61010-1, EN61010-031, EN61010-2-30, IEC61010-2-034	

#### **General Specifications**

Test condition	23±5°C, 80% RH or less (no condensation)			
Operating temperature/ humidity range	-10 to +50°C, 80% RH or less (no condensation)			
Storage temperature/ humidity range	-20 to +60°C, 75% RH or less (no condensation)			
Auto-power off	The tester is automatically turned off when no key operations are performed for 10 minutes.			
Battery Life	Approx. 1300 tries (500 V/0.5 MΩ)			
Power source	Four size AA batteries			
Dimensions	Approx. 156 (W) × 46 (H) × 97 (D) mm			
Weight	Approx. 490 g (with battery)			
Standard accessories (attached)	Instruction manual, Four size AA batteries, 93045: Soft case, 98008: Line probe, 98009: Earth probe set, 99018: Shoulder strap			
Accessories (sold separately)	91030: USB Communication Adaptor, 99012: Probe tip (extended type), 99013: Probe tip (hook type)			

This is a Class B instrument based on Emission standards EN61326-1 and EN55011, and is designed for an industrial environment.

Operation of this equipment in a residential area may cause radio interference, in which case users will be responsible for any interference which they cause.

#### 91030 USB Communication Adaptor Specification

Communication cable	Infrared communication adaptor and Communications cable (USB) 1 set
Cable length	1.9 m
Interface	USB ver. 1.1
Supported model	MY600
Included accessories (attached)	CD Packing contents: Communication driver, User's manual, Install manual

#### Model code and suffix


Model code	Notes
MY600	Digital Insulation Tester

#### **Accessories**

710000001100				
Model code	Model name	Notes		Attached
91030	USB communication adaptor	USB communication dedicated cable between PC and the main unit		No
93045	Soft case	Main baby and accessory- housing		Yes
98008 🐴	Line probe with remote switch	Length: 1.4 m, MY600 only		Yes
98009 🐴	Earth probe set	Length: 2.0 m, Earth probe and alligator clip adapters	4178	Yes
99012 🐴	Probe tip (hook type)	Size: 61.9 × 26 mm		No
99013 🐴	Probe tip (extended type)	Length: 115.4 mm	-	No
99018	Shoulder strap	For hanging the main body during measurement	=0	Yes

Due to the nature of this product, it is possible to touch its metal parts. Therefore, there is a risk of electric shock, so the product must be used with caution.

#### **Outline drawing**



YMI-KS-MI-SF05

#### NOTICE

Before operating the product, read the user's manual thoroughly for proper and

## YOKOGAWA

#### YOKOGAWA TEST & MEASUREMENT CORPORATION

Facsimile: +81-422-52-6462

YOKOGAWA CORPORATION OF AMERICA YOKOGAWA EUROPE B.V. YOKOGAWA SHANGHAI TRADING CO., LTD. YOKOGAWA ELECTRIC KOREA CO., LTD. YOKOGAWA ENGINEERING ASIA PTE. LTD. YOKOGAWA INDIA LTD. YOKOGAWA ELECTRIC CIS LTD. YOKOGAWA AMERICA DO SUL LTDA.

Phone: +31-88-4641000 Phone: +86-21-6239-6363 Phone: +82-2-2628-3810 Phone: +65-6241-9933 Phone: +7-495-737-78-68 Phone: +55-11-5681-2400 YOKOGAWA MIDDLE EAST & AFRICA B.S.C(c) Phone: +973-17-358100

Subject to Change without notice. Copyright © 2018, Yokogawa Test & Measurement Corporation [Ed: 01/b] Printed in Japan, 807(KP)

E-mail: tmi@us.yokogawa.com E-mail: tmi@nl.yokogawa.com Facsimile: +86-21-6880-4987 E-mail: tech@ysh.com.cn E-mail: TMI@kr.yokogawa.com Facsimile: +82-2-2628-3899 E-mail: TMI@sg.yokogawa.com Facsimile: +65-6241-9919 Phone: +91-80-4158-6396 E-mail: tmi@in.yokogawa.com Facsimile: +91-80-2852-1442 Facsimile: +7-495-737-78-69 E-mail: info@ru.yokogawa.com

http://tmi.yokogawa.com/

E-mail: help.ymatmi@bh.yokogawa.com Facsimile: +973-17-336100