

Please make the following alterations to the User's Manual IM 701240-01E.


■ 18-21 page “High-Voltage 100 kS/s, 16-Bit Isolation Module (with RMS) (701267) Specifications”

Please change the followings


Withstand voltage	<u>2210 Vrms</u> for 1 minute (across each terminal and earth) (60 Hz)
Allowable transient surge voltage (instantaneous)	<u>±3100 Vpeak</u> (across each input terminal and earth)

■ 18-22 page

With the 758933 and 701954



Direct input (cable that does not comply with the safety standards)



Withstand voltage: **2210 Vrms** for 1 minute

Allowable transient surge voltage (between earth and input): **±3100 Vpeak**