WE7121

10 MHz Function Generator Module

GENERAL

The WE7121 10-MHz function generator module is complete with all of the basic features of a function generator.

The module contains in its flash memory the graphic data for screens used to set such data items as the waveform, output voltage and frequency necessary for module operation. When connected to a personal computer, the module is actuated once it transfers the graphic data to the computer. The module can generate simplified arbitrary waveforms.

FEATURES

- 1-µHz to 10-MHz oscillation frequency range
- Can generate simple arbitrary waveforms
- Operates in sync with an adjacent WE7121 module

■ Performance Specifications

The following performance specifications are attained under standard operating conditions ("General Specifications").

Waveform output

Number of output channels: 1 channel

Standard output waveforms: Sine wave/square wave (duty cycle fixed at 50%)/triangular wave/ramp wave/pulse wave (duty cycle variable), and inversions of each waveform

Arbitrary waveform

Output amplitude resolution: 12 bit

Memory length: 16384 points (some points are not generated when the repetitive frequency is 2.4 kHz of higher.)

Output operation

Continuous oscillation (CONT): Outputs the waveform continuously

Trigger oscillation (TRIG): Outputs the specified count (integer) of burst waveforms in sync with the trigger.

Gate oscillation (GATE): Outputs the integer count of burst waveforms while the gate is enabled.

DC output (DC): Outputs a DC voltage.

Oscillation frequency range

Sine/Square wave: 1 μHz to 10 MHz Triangular/Pulse wave: 1 μHz to 200 kHz

Ramp wave: 1 µHz to 200 kHz Arbitrary waveform: 1 µHz to 200 kHz

Oscillation frequency resolution: 1 μHz or 9 digits

maximum

Oscillation frequency accuracy: ±20 ppm

Oscillation frequency stability: ±20 ppm (when ambient

temperature is 5 to 40°C)
Oscillation reference clock; 40.2107 MHz





WE7121

Output characteristics

Maximum output voltage (see Note 1): $\pm 10 \text{ V}$

Amplitude setting range (see Note 1): 20 Vp-p (resolution: 1 mVp-p)

Amplitude accuracy (see Note 1) (for 1 kHz sine wave): $\pm (0.5\% \text{ of set value} + 14 \text{ mV})$

Oscillation frequency characteristics (see Note 2)

Sine wave

 $\leq 100 \text{ kHz} \pm 0.1 \text{ dB}$

 $\leq 1 \text{ MHz} \pm 0.2 \text{ dB}$

 $\leq 10 \text{ MHz} \pm 0.5 \text{ dB}$

Square/Pulse wave (duty cycle 50%): $\leq 10 \text{ kHz } \pm 2\%$

Triangular wave: $\leq 10 \text{ kHz } \pm 3\%$ Ramp wave: $\leq 10 \text{ kHz } \pm 3\%$

Offset voltage setting range (see Note 1): ±10 V (resolu-

tion: 1 mV)

Offset voltage accuracy (see Note 1): $\pm (0.3\% \text{ of set value} + 0.2\% \text{ of set amplitude} + 20 \text{ mV})$

DC output setting range (see Note 1): ± 10 V (resolution: 1 mV)

DC output accuracy (see Note 1): $\pm (0.3\%$ of set value + 20 mV)

Output impedance: 50 Ω ±1%, except open when the output is turned OFF

Maximum output current: ±200 mA Output format: Non-isolated unbalanced

Connector type: BNC

Note 1: Value under high impedance load.

Note 2: Amplitude 20 Vp-p, offset voltage 0 V, 50 Ω load, measures RMS value with 1 kHz as a reference.

Sine wave purity

Harmonics (see Note) (Maximum value of the 2nd to 5th order harmonic components)

100 kHz: -55 dBc or less 1 MHz: -45 dBc or less 10 MHz: -35 dBc or less

Harmonic distortion (see Note) (RMS value of 2nd to 5th

order harmonic components)

100 kHz: 0.3% or less

Spurious response (see Note) (frequency range 1 kHz to 100 MHz)

100 kHz: -55 dBc or less

Note: Measured with 20 Vp-p amplitude, 0 V offset voltage, 50 Ω load.

Characteristics of sine, pulse, triangular waves

Rise time (see Note)

Square wave: 30 ns or less (10% - 90%) Pulse wave: 100 ns or less (10% - 90%)

Overshoot (see Note): ±5% or less of the output p-p value

Duty cycle setting (pulse wave only)

Setting range: 0 to 100% (resolution: 0.01% or 25 ns) Time accuracy (\leq 10 kHz): \pm 0.2% of (1/set frequency)

Jitter: 1 clock cycle

Note: Measured with 20 Vp-p amplitude, 0 V offset voltage, 50 Ω load

Phase

Target: Start/stop phase when using trigger/gate

oscillation
Setting range: -10000 deg to +10000 deg (resolution: 0.01

Trigger/Gate

Trigger source: Internal trigger, Bus trigger (BUSTRG1/BUSTRG2) signal on WE bus

Setting range of internal trigger frequency: 1 mHz to 50 kHz (resolution: 1 mHz)

Bus trigger (BUSTRG1/BUSTRG2) signal output source:
Able to output waveform synchronization
output (SYNC) signal

Setting range of burst count: 1 to 65535 counts (step: 1) Gate source: Bus trigger (BUSTRG1/BUSTRG2) signal on the WE bus

Synchronous operation

Skew between modules (when modules are linked and outputting the pulse wave): 70 ns per module (Typical value (see Note 1))

Isolation between channels (see Note 2) (when modules are linked): -65 dB (Typical value (see Note 1))

Note 1: Typical value represents a typical or average value. It is not strictly guaranteed.

Note 2: Output waveform: Cross talk for a 10 MHz sine wave with 20 Vp-p amplitude, 0 V offset voltage, 50 Ω load.

■ Specifications of the Auxiliary Output

Waveform synchronization signal output (SYNC OUT)

Output level: TTL level, under high impedance load

Output impedance: Approx. $50~\Omega$ Maximum output current: $\pm 3.2~mA$ Output format: Non-isolated unbalanced

Connector type: BNC

■ General Specifications

Standard operating conditions

Ambient temperature: $23 \pm 2^{\circ}\text{C}$, Ambient humidity: 50 $\pm 10\%$ RH, Error on supply voltage/ frequency: within 1% of rating, after the warm-up time has passed

Warm-up time: At least 30 minutes

Operating conditions: Same as that of the measuring station

Storage conditions

Temperature: -20°C to 60°C

Humidity: 20% to 80% RH (no condensation)

Power consumption: 7 VA (Typical value at 100 V/50 Hz

(see Note))

External dimensions: Approx. 33 (W) \times 243 (H) \times 232 (D)

mm (projections excluded)

Weight: Approx. 0.7 kg Number of dedicated slots: 1

Standard accessory: User's Manual (1)

Optional accessory

366924 BNC cable (1 m) 366925 BNC cable (2 m)

366926 BNC alligator clip cable (1 m)

366921 Adapter (BNC plug-banana terminal jack)

366927 Adapter (BNC plug-RCA jack) 366928 Adapter (BNC jack-RCA plug)

Note: Typical value represents a typical or average value. It is not strictly guaranteed.

AVAILABLE MODEL

Model	Description
707121/HE	10 MHz Function Generator Moule

■ Dimensions

Unit: mm (inch)



